


Right-Angle Cat6 Gigabit Molded UTP Ethernet Cable (RJ45 Right-Angle M to RJ45 M), Blue, 20 ft.

MODEL NUMBER: N204-020-BL-RA



Cat6 cable connects Gigabit Ethernet network components like routers, servers, and switches in high-density data centers.

Features

Right-Angle Cat6 UTP Cable Connects Equipment in Data Centers and VoIP Networks

This Cat6 Ethernet cable is ideal for connecting network components, such as printers, computers, copiers, routers, servers, modems and switches, in high-density data centers. Designed for fast transmission and excellent signal quality, this RJ45 cable ensures data transfer speeds up to 1 Gbps throughout your Gigabit Ethernet or VoIP network.

Right-Angle RJ45 End Makes Connecting and Disconnecting Easier

One RJ45 connector is designed at a 90-degree right angle, which prevents excessive bending and reduces stress on the cable. This makes the space-saving cable easy to plug into patch panels, switches and other devices located in a confined area or behind a desk.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime

This long Ethernet cable features a blue PVC jacket and molded blue ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

Highlights

- Cat6 Ethernet patch cable delivers fast transmission speeds up to 1 Gbps in your LAN
- Right-angle RJ45 connector is easy to plug into switch or panel pressed against a wall
- Designed for home or office 10/100/1000Base-T Gigabit Ethernet networks
- Color-coded blue for fast, easy identification in a crowded rack or workstation

Applications

- Build a Gigabit Ethernet or VoIP network through the connection of routers, modems, switches and servers in a high-density data center
- Connect a workstation computer to the company server to gain access to printers, scanners and copiers
- Combine with other Tripp Lite patch cables to set up a color-coded system in a crowded rack
- Create a connection in a tight space, such as a repurposed server room or behind furniture

Package Includes

- N204-020-BL-RA Right-Angle Cat6 Ethernet Cable - 20 ft., M/M, Blue



OVERVIEW	
UPC Code	037332252067
INPUT	
Cable Length (ft.)	20
Cable Length (m)	6.1
Cable Length (in.)	240
Cable Length (cm)	609
PHYSICAL	
Cable Jacket Rating	CM
Cable Outer Diameter (OD)	6.2mm
Cable Shielding	UTP
Color	Blue
Material of Construction	PVC
Snagless Connector	No
Wire Gauge (AWG)	24
Wire Type	Stranded
ENVIRONMENTAL	
Operating Temperature Range	14 to 122 F (-10 to 50 C)
Storage Temperature Range	5 to 140 F (-15 to 60 C)
Relative Humidity	0% to 90% RH, Non-Condensing
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE) - RIGHT ANGLE
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
Technology	Cat5/5e; Cat6
CERTIFICATIONS	
Certifications	Tested to RoHS, REACH



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>