

# SONY



## 3LCD Laser Projectors

### VPL-FHZ131L

13,000lm, WUXGA

### VPL-FHZ101L

10,000lm, WUXGA

### VPL-FHZ91L

9,000lm, WUXGA

## Features

- High brightness, high contrast and sRGB 100%\* wide color 13,000 / 10,000 / 9,000 lumen images  
\*sRGB 100% color space is only for VPL-FHZ131L.
- Reality Creation  
// Advanced picture refinement technologies
- Intelligent Setting  
// Highly automatic control of multiple parameters to maximize laser performance
- Installation flexibility  
// Very wide range of lens shift adjustment and a wide choice of interchangeable lenses
- Supports wide range of major control interfaces
- Slim, attractive blend-in design

Combining spectacular image quality with easy set-up and minimal maintenance needs, these high-brightness 3LCD laser projectors are ideal for installation in larger spaces.



Auditoriums/Halls



Classrooms/Conference Rooms



Museums

Z-Phosphor  
LASER LIGHT SOURCE

3LCD

BrightEra  
Long Lasting Optics

CHDBT<sup>TM</sup>

# SPECIFICATIONS

		VPL-FHZ131L	VPL-FHZ101L	VPL-FHZ91L
Display system		3 LCD system		
Display device	Size of effective display area	1" x 3 BrightEra LCD Panel, Aspect ratio: 16:10		
	Number of pixels	6,912,000 (1920 x 1200 x 3) pixels		
Projection lens	Focus, Zoom	Powered / Manual (Depend on lens)		
	Lens shift	Powered / Manual	Powered	
Light source	Type	Laser diode		
Auto filter cleaning / Auto color calibration		Yes / Yes		
Light output*1 (Mode: Standard / Middle)		13,000 lm / 10,000 lm	10,000 lm / 8,800 lm	9,000 lm / 8,000 lm
Constant ratio*1 (full white / full black)		∞ : 1		
Color space	Picture mode: sRGB	sRGB 100%	-	
Displayable scanning frequency	Horizontal / Vertical	15 kHz to 92 kHz / 48 Hz to 92 Hz		
Display resolution	Computer signal input	Maximum display resolution: 1920 x 1200 dots		
	Video signal input	480/60i, 576/50i, 480/60p, 576/50p, 720/60p, 720/50p, 1080/60i, 1080/50i The following items are available for digital signal only; 1080/60P, 1080/50p, 1080/24p, 1080/30p*3		
Keystone correction (Max.)	Horizontal / Vertical	+/- 30 degrees / +/- 30 degrees		
OSD language		24-language (English, French, German, Italian, Spanish, Portuguese, Japanese, Simplified Chinese, Traditional Chinese, Korean, Russian, Dutch, Norwegian, Swedish, Thai, Arabic, Turkish, Polish, Vietnamese, Farsi, Indonesian, Finnish, Hungarian, Greek) with Sony sales co. customizable		
Input / Output (Computer / Video / Audio / Control)	INPUT A	RGB / Y PB PR input connector: 5BNC (female)		
	INPUT B	RGB input connector: Mini D-sub 15-pin (female)		
	INPUT C	DVI input connector: DVI-D 24-pin (single link), HDCP support		
	INPUT D	HDMI input connector: HDMI 19-pin, Digital RGB / Y PB PR, HDCP support		
	INPUT E	HDBaseT interface connector: RJ45, 3 play (Video, LAN, Control)		
	INPUT F	Optional adaptor slot (For 3G-SDI Input Adaptor BKM-PJ20)		
	INPUT G	HTML Viewer		
	OUTPUT	Monitor output for Input A / Input B Connector: Mini D-sub 15-pin (female)		
	USB	Type-A x 1, Type-B x 1 (for service)		
	REMOTE	D-sub 9-pin (male) / RS232C		
LAN	RJ45, 10BASE-T / 100BASE-TX / 1000BASE-T			
Acoustic noise (Mode: Standard)*2		42 dB	39 dB	
Operating temperature / Operating humidity		0°C to 45°C (32°F to 109°F) / 20% to 80% (no condensation)		
Storage temperature / Storage humidity		-10°C to +60°C (14°F to +140°F) / 20% to 80% (no condensation)		
Power requirements		AC 100 V to 240 V, 10.8 A to 4.4 A, 50 Hz to 60 Hz	AC 100 V to 240 V, 8.4 A to 3.4 A, 50 Hz to 60 Hz	
Power Consumption (Maximum)	AC 100 V to 120 V	1076 W	840 W	
	AC 220 V to 240 V	1033 W	814 W	
Power Consumption (Standby mode)	AC 100 V to 120 V	0.50 W (when "Standby mode" is set to "Low")		
	AC 220 V to 240 V	0.50 W (when "Standby mode" is set to "Low")		
Power Consumption (Networked Standby mode)	AC 100 V to 120 V	21.6 W (LAN) / 26.5 W (HDBT) / 26.6 W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")		
	AC 220 V to 240 V	21.3 W (LAN) / 26.5 W (HDBT) / 26.6 W (ALL Terminals and Networks Connected, when "Standby Mode" is set to "Standard")		
Standby Mode (Networked Standby Mode Activated)		Networked Standby Mode Activated Approx. 2 Minutes		
Heat dissipation	AC 100 V to 120 V	3671 BTU / h	2866 BTU / h	
	AC 220 V to 240 V	3524 BTU / h	2777 BTU / h	
Dimensions (W x H x D) (without protrusions)		Approx. 544 x 205 x 564 mm (21 13/32 x 8 1/16 x 22 7/32 inches)		
Mass (without optional projection lens)		Approx. 27 kg (58 lb)	Approx. 26 kg (58 lb)	
Supplied accessories	Remote commander	RM-PJ30		
Optional accessories	Projection Lens	VPLL-Z4107 / 4008 / Z4111 / Z4015 / Z4019 / Z4025 / Z4045		

\*1 Value is in accordance with ISO 21118, and may differ depending on the actual unit. Brightness and contrast vary depending on use conditions and environments.

\*2 The figures are approximate. They vary depending on the environment or how the projector is used. \*3 When using BKM-PJ20



## OPTIONAL LENS INFORMATION

	Throw ratio	Lens shift range	
		Vertical	Horizontal
VPLL-Z4107	0.75:1 to 0.94:1	+/- 50%	+/- 24%
VPLL-4008	1.00:1	+/- 32%	+/- 15%
VPLL-Z4111	1.30:1 to 1.96:1	+/- 99%	+/- 51%
VPLL-Z4015	1.85:1 to 2.44:1	+/- 98%	+/- 51%
VPLL-Z4019	2.41:1 to 3.07:1	+/- 107%	+/- 57%
VPLL-Z4025	3.02:1 to 5.58:1	+/- 107%	+/- 57%
VPLL-Z4045	5.56:1 to 7.5 :1	+/- 107%	+/- 57%

### LASER NOTICES

For the U.S.A.  
IEC 60825-1:2007 CLASS 3R  
LASER PRODUCT

For other countries  
IEC 60825-1:2014 CLASS 1 LASER PRODUCT  
As with any bright light source,  
do not stare into the beam,  
RG2 IEC 62471-5:2015.



©2019 Sony Electronics Asia Pacific Pte Ltd. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for mass and dimension are approximate. "SONY" is a registered trademark of Sony Corporation. "Z-Phosphor", "BrightEra" and "Remote Commander" are trademarks of Sony Corporation. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. HDBaseT and the HDBaseT Alliance logo are the trademarks of the HDBaseT Alliance. All other trademarks are the property of their respective owners. Please visit Sony's professional website or contact your Sony representative for specific models available in your region.