Full-HD USB 2.0 PTZ Camera



FEATURES

- 5 Megapixel SONY 1/2.8-inch CMOS HD Sensor
- USB 2.0 with UVC1.5 (USB video class) protocol control
- Full-HD Resolution: 1920x1080p, 1280x720p & 640x480p
- Frames per second: 30fps, 15fps, 8fps
- 12x Digital Zoom / 10x Optical Zoom 4.7~47mm (F1.8~F14)
- Angle of View (AOV): 62.5 degree (wide) to 6.5 degree (tele)
- Pan-Tilt range: 340° Pan, 120° Tilt
- Mount on ceiling or upside down with flipable video image
- PTZ control via RS232 and USB2.0 (UVC1.5)
- Easily integrates into common teleconference, UC, and huddle space software
- Up to 128 preset location saves, adjustable Pan-Tilt speeds between presets

The Marshall CV610-U2 Full-HD USB 2.0 PTZ Camera is designed to easily integrate into common software platforms for Teleconference, Unified Communications (UC), and Huddle Spaces.

At a small footprint (148 x 132 x 161mm), the CV610-U2 is a high performing USB 2.0 camera at an affordable price point.



REAR I/O FUNCTIONS

1. RS-232 Port

2. USB 2.0 Port

3. DC12V Power Input



Mounting Options

CV610-U2-CM Ceiling Mount



CV610-U2-WM Wall Mount

