

AXIS Q9216-SLV Network Camera

Impact-resistant anti-ligature camera

AXIS Q9216-SLV is a compact and robust ligature-resistant (anti-ligature) corner-mount camera that delivers 4 MP video quality. It covers 125 degrees horizontally and 95 degrees vertically, with no blind spots. Featuring invisible IR illumination, it's ideal for covert video surveillance in complete darkness. With an IK10+/IP66 rated casing, it also includes a removable built-in microphone and an indication LED. The camera has polygonal privacy masking, which allows for flexible coverage and helps ensure occupant privacy is respected. Furthermore, signed firmware and a Trusted Platform Module (TPM, FIPS 140-2 level 2 certified) help prevent unauthorized access and safeguard your system.

- > **Anti-ligature, robust (IK10+)**
- > **Corner camera – no blind spots**
- > **WDR and invisible IR (940 nm)**
- > **Compact design – easy to install**
- > **Zipstream supporting H.264 and H.265**



AXIS Q9216-SLV Network Camera

| | | |
|--|--|---|
| Models | AXIS Q9216-SLV Network Camera Steel AXIS Q9216-SLV Network Camera White | Notification: HTTP, HTTPS, TCP and email Audio clips, day-night mode, guard tours, I/O, IR illumination, overlay text, power saving mode, preset positions, prioritized text, recordings, SNMP trap messages, status LED, WDR mode |
| Camera | | |
| Image sensor | 1/2.5" progressive scan RGB CMOS | |
| Lens | 2.4 mm, F2.0 Horizontal field of view: 125° Vertical field of view: 95° Fixed focus, fixed iris, M12 mount | |
| Day and night | Automatically removable infrared-cut filter | |
| Minimum illumination | Color: 0.23 lux at F2.1 B/W: 0.05 lux at F2.1 0 lux with IR illumination on | |
| Shutter speed | 1/32500 s to 1/5 s | |
| Video | | |
| Video compression | H.264 (MPEG-4 Part 10/AVC) Main and High profile H.265 (MPEG-H Part 2/HEVC) Main Profile Motion JPEG | |
| Resolution | 2304 x 1728 to 320x 240 | |
| Frame rate | Up to 30/25 fps (60/50 Hz) in all resolutions | |
| Video streaming | Multiple, individually configurable streams in H.264, H.265 and Motion JPEG Axis Zipstream technology in H.264 and H.265 Controllable frame rate and bandwidth VBR/ABR/MBR H.264/H.265 HDMI | |
| Multi-view streaming | 2 individually cropped out view areas | |
| HDMI output | HDMI 1080p (16:9) @25/30 fps (50/60 Hz) HDMI 720p (16:9) @50/60 fps (50/60 Hz) | |
| Pan/Tilt/Zoom | Digital PTZ | |
| Image settings | Saturation, contrast, brightness, sharpness, WDR, white balance, day/night threshold, exposure mode, compression, rotation: 0°, 90°, 180°, 270° including Corridor Format, mirroring, text and image overlay, polygon privacy mask | |
| Audio | | |
| Audio streaming | Two-way, full duplex | |
| Audio encoding | 24bit LPCM, AAC-LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz Configurable bit rate | |
| Audio input/output | External microphone input or line input, line output, built-in microphone (removable) Balanced audio in and audio out is supported | |
| Network | | |
| Security | Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1x (EAP-TLS) ^a network access control, digest authentication, user access log, centralized certificate management, brute force delay protection, signed firmware, protection of cryptographic keys with FIPS 140-2 certified TPM 2.0 module | |
| Supported protocols | IPv4, IPv6 USGv6, HTTP, HTTP/2, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, SFTP, CIFS/SMB, SMTP, Bonjour, UPnP [®] , SNMP v1/v2c/v3(MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, SFTP, TCP, UDP, IGMPv1/v2/v3, RTCP, ICMP, DHCPv4/v6, ARP, SOCKS, SSH, LLDP, SIP, MQTT v3.1.1, Syslog | |
| System integration | | |
| Application Programming Interface | Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF [®] Profile G, ONVIF [®] Profile S, and ONVIF [®] Profile T, specification at onvif.org Support for Session Initiation Protocol (SIP) for integration with Voice over IP (VoIP) systems, peer to peer or integrated with SIP/PBX | |
| Event conditions | Analytics, shock detection, casing open, edge storage events, supervised external input, audio level, time scheduled | |
| Event actions | Calls: answer, end SIP calls, make SIP calls Upload of images or video clips: FTP, HTTP, HTTPS, SFTP, email and network share | |
| Data streaming | Event data | |
| Built-in installation aids | Pixel counter, adjustable IR illumination intensity | |
| Analytics | | |
| Applications | Included AXIS Video Motion Detection, AXIS Motion Guard, AXIS Fence Guard, and AXIS Loitering Guard active tampering alarm Supported AXIS Digital Autotracking Support for AXIS Camera Application Platform enabling installation of third-party applications, see axis.com/acap | |
| General | | |
| Casing | Anti-ligature and anti-grip stainless steel casing and polycarbonate hard-coated dome. IP66-, IP69-, IP6K9K- and NEMA 4X-rated IK10+ 50 joules impact-resistant Steel: Color: Stainless steel White: Color: White NCS S 1002-B For repainting instructions of casing and impact on warranty, contact your Axis partner. | |
| Sustainability | PVC free, BFR/CFR free | |
| Memory | 1024 MB RAM, 512 MB Flash | |
| Power | Power over Ethernet IEEE 802.3af/802.3at Type 1 Class 3 Max. 10.8 W Typical 4.7 W (default IR) Typical 3.9 W (power-saving mode with limited IR) | |
| Connectors | RJ45 10BASE-T/100BASE-TX PoE I/O: 4-pin 2.5 mm (0.098 in) terminal block for 1 supervised digital input and 1 digital output (12 V DC output, max. load 25 mA) 3.5 mm mic/line in, 3.5 mm line out HDMI type D | |
| IR illumination | Power-efficient, long-life and invisible 940 nm IR LED. Range of reach up to 15 m (49 ft) depending on the scene Optional power-saving mode to minimize IR LED power consumption | |
| Storage | Support for microSD/microSDHC/microSDXC card Support for SD card encryption (AES-XTS-Plain64 256bit) Recording to network-attached storage (NAS) For SD card and NAS recommendations see axis.com | |
| Operating conditions | -20 °C to 50 °C (-4 °F to 122 °F) Maximum temperature (intermittent): 55 °C (131 °F) Start-up temperature: -20 °C (-4 °F) to 55 °C (131 °F) Humidity 10-85% RH (condensing) | |
| Storage conditions | -40 °C to 65 °C (-40 °F to 149 °F) Humidity 5-95% RH (non-condensing) | |
| Approvals | EMC EN 50130-4, EN 55032 Class A, EN 55035, IEC/EN 61000-6-1, IEC/EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-3(A)/NMB-3(A), VCCI Class A, KC KN-32 Class A, KC KN-35, RCM AS/NZS CISPR 32 Class A, CISPR 24, CISPR 35 Safety IEC/EN/UL 62368-1, CAN/CSA C22.2 No. 62368-1, IEC/EN 62471, IS 13252 Environment EN 50130-5 Class I, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78, IEC/EN 60529 IP66, EN 60529 IP69, ISO 20653 IP6K9K, IEC/EN 62262 IK10+, NEMA 250 Type 4X Network NIST SP500-267 | |
| Dimensions | Height: 131 mm (5.16 in) Width: 209 mm (8.23 in) Depth: 176 mm (6.93 in) Height when corner-mounted: 116 mm (4.57 in) Depth when corner-mounted: 148 mm (5.83 in) | |

| | |
|----------------------------------|---|
| Weight | 1.6 kg (3.5 lb) |
| Included accessories | Installation guide, Windows® decoder 1-user license, AVHS Authentication key, AXIS Device Microphone A, AXIS Connector A 4-pin 2.5 straight, cable gaskets, RESISTORX® 20 bit |
| Optional accessories | AXIS TQ9601 Conduit Top Box, AXIS T8645 PoE+ over Coax Compact AXIS Surveillance Cards For more accessories, see axis.com |
| Video management software | AXIS Companion, AXIS Camera Station, video management software from Axis Application Development Partners available at axis.com/vms |

Languages English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Polish, Traditional Chinese

Warranty 5-year warranty, see axis.com/warranty

- a. *This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).*

Environmental responsibility:

axis.com/environmental-responsibility