

CHERRY MC 2000



Models may vary from the image shown

Infra-red mouse with tilt-wheel technology

Single-handed control and efficient navigation. The CHERRY MC 2000 infra-red mouse with tilt-wheel offers top quality processing, precision and reliability. Unique in its class.

Key Benefits

- 3-button mouse
- Tilt-wheel for horizontal/vertical scrolling
- GS certification
- Resolution 1,600 dpi
- Infra-red sensor
- Suitable for both right-handed and left-handed operation
- Symmetrical design
- Standard size

Technical Data:

Housing Color:

Product dependant, see table "Models"

Key Color:

Product dependant, see table "Models"

Weight (product):

118 g / 4.16 oz

Total Weight (with packaging):

156 g / 5.50 oz

Cable Length:

approx. 1.80 m / approx. 5.91 ft

Storage Temperature:

-15°C to 60°C / -5° F to 140° F

Operating Temperature:

0°C to 40°C / 32° F to 104° F

Current Consumption:

max. 50 mA

Interface:

- USB

Product Approvals:

- CE
- TÜV-Süd/GS



System Requirements:

- USB connection

Box Contents:

- CHERRY MC 2000
- Operating instructions in hard copy

Dimensions (product):

109 x 62 x 37 mm / 4.29 x 2.44 x 1.46 in

Packaging Dimensions:

130 x 100 x 43 mm / 5.12 x 3.94 x 1.69 in

Reliability:

- Standard keys: >3 mill. operations

Mouse:

- Scanning: Infrared
- Resolution: 1600 dpi
- Number of Keys: 3
- Mouse Wheel Design: Tilt-Wheel
- Design: Symmetrical
- Connection: USB

Packaging Unit:

- Number of products in the master package: 10
- Number of master packages per pallet: 125

Warranty:

2 years

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product Name	Order Number	EAN Code	Housing Color	Key Color
1	CHERRY MC 2000	JM-0600-0	4025112086182	pale grey	pale grey
2	CHERRY MC 2000	JM-0600-2	4025112083334	black	black