

ThinkCentre M625 Tiny Thin Client 10TL002BUS

Product

ThinkCentre M625 Tiny Thin Client

Region

NA

Country/Region

USA

Machine Type

10TL

TopSeller

TopSeller

Processor

AMD A4-9120e (2C / 2T, 1.5 / 2.2GHz, 1MB L2)

Chipset

AMD SoC platform

Graphics

Integrated AMD Radeon R3 Graphics

Memory

1x 4GB DDR4-2666

Storage

32GB SSD M.2 2242 SATA

Optical

None

Speaker

1.5Wx1

Ethernet

Integrated 100/1000M

WLAN + Bluetooth

QCA6174A 11ac, 2x2 + BT4.2

Optional Rear Ports

1x VGA + 1x Serial

Chassis Intrusion Switch

Chassis Intrusion Switch

Kensington Cable Lock

None

Adapter Cage

None

Toolless Chassis Screw

None

Dust Filter

None

VESA Mount

None

Color

Black

Stand

Stand

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse

Power Supply

65W 88% Adapter

TUV Low Noise

None

Monitor Cable

None

System Management

None

Operating System

LeTOS V2, English

Bundled Software

None

Base Warranty

1-year, Onsite

Bundled Service

None

EAN / UPC / JAN

194778608992

End of Support

2026-04-03

Announce Date

2020-03-03

Recommended Services**Best**

4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PS0N73136)

Good

3Y Premier Support Upgrade from 1Y Onsite (5WS0T36147)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



ThinkCentre M625 Tiny Thin Client Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD E2 series APU						Keyboard Mouse	<i>Some:</i> Fullsize USB Keyboard (USB connector), black, Lenovo logo <i>Some:</i> USB Optical Wheel Mouse, black, Lenovo logo
	APU	Cores	Frequency Base/Max	L2 Cache	Memory Support (Up to)	Integrated Graphics	Mechanical	Tiny (1L), fan-less design, black color, metal case <ul style="list-style-type: none"> • Toolless chassis open (for models with optional toolless chassis screw) • Toolless SSD, memory, Wi-Fi removal M625 Tiny Thin Client only: 7.05" W X 7.20" D X 1.36" H 179mm W X 182.9mm D X 34.5mm H 2.9 lb (1.3 kg), weight may vary by configuration Optional VESA mount bracket kit, supports VESA 75mm and 100mm Optional system floor stand for vertical orientation
Memory	8GB max, DDR4-2666, one 260-pin SO-DIMM socket * System frequency automatically clocks down for the lower capability of memory controller in processor						VESA mount Floor Stand	65 watts AC/DC adapter, autosensing, 88% PSU (not included for TIO models)
Disk	<i>Some:</i> 32GB M.2 Solid State Drive (SSD) / SATA interface <i>Some:</i> 128GB M.2 Solid State Drive (SSD) / PCIe NVMe interface						Limited warranty ³	<i>Some:</i> 1-year, depot service / service upgrades available <i>Some:</i> 1-year, limited onsite service / service upgrades available
Optical Onboard SATA Media reader	None one SATA 6.0Gb/s connector on planar None						Preload	Preloaded operating system <i>Some:</i> Windows Embedded Standard 7 V2 (WES 7 V2) <i>Some:</i> Windows 10 IoT Enterprise <i>Some:</i> LeTOS V2 (Lenovo Terminal Operating System, Linux-based)
Graphics	AMD Radeon™ Graphics in processor, uses main memory, DirectX® 12, two DisplayPort™, one optional port (VGA or USB 2.0 Type-C with DisplayPort Alternate Mode), supports up to 2 independent displays; <i>Max resolution:</i> 3840x2160 (DP) @60Hz; 2048x1280 (VGA) @60Hz; 3840x2160 (USB 2.0 Type-C) @60Hz						Environment	ENERGY STAR® 6.1*, EPEAT™ Silver rating* (*Not for non-OS models), ErP Lot 3, RoHS-compliant, WEEE, TCO
Monitor cable	Optional DP to VGA, DP to DVI-D (single link), or DP to HDMI 1.4 dongle						MIL-SPEC test	MIL-STD-810G military certification (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation)
Chipset	AMD SoC platform						Accessories	For compatible accessories, please go to http://smartfind.lenovo.com
Front ports*	Two USB 3.1 Gen1 (one is Always On and fast charge), one microphone (3.5mm), one headphone / microphone combo jack (3.5mm)							
Rear ports*	One USB 3.1 Gen1, three USB 2.0, ethernet (RJ-45), two DisplayPort, two optional ports (Port 1 for VGA / serial / USB 2.0 Type-C (with DisplayPort Alternate Mode), Port 2 for serial) * Depending on many factors, actual data transfer speed may be lower than theoretical speed							
I/O box	None							
Audio support	High Definition (HD) Audio, Realtek ALC233-VB2-CG / internal speaker (1.5 watt)							
WLAN ¹³	<i>Some:</i> 11ac wireless, M.2 Card, Realtek RTL8821CE (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA9377 (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 1x1 <i>Some:</i> 11ac wireless, M.2 Card, Realtek RTL8822BE (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Qualcomm Atheros QCA6174A (dual band), Wi-Fi + Bluetooth 4.2* combo adapter, 2x2 <i>Some:</i> 11ac wireless, M.2 Card, Intel Wireless-AC 9260 (dual band), Wi-Fi + Bluetooth 5.0 combo adapter, 2x2							
Bluetooth™	<i>Some:</i> Bluetooth 4.2/5.0* wireless, integrated in Wi-Fi + BT combo adapter * Win 10 RS3 and Win10 earlier version only support Bluetooth 4.1							
Ethernet Modem	Gigabit ethernet, Realtek RTL8111HN, Wake on LAN® None							
Manageability Security chip Security features	None Discrete TPM 2.0, TCG Certified <ul style="list-style-type: none"> • Security slot (in rear for optional Kensington® MicroSaver® cable) • Smart USB protection, allows keyboard/mouse only, blocks all storage devices • Power-on password • Administrator password • Hard disk password • Boot sequence control • Boot without keyboard and mouse • Individual USB port disablement • Chassis intrusion switch 							



ThinkCentre M625 Tiny Thin Client

