



DURASCAN® D755



Medical Grade Barcode Scanner for Healthcare

The D755 is a powerful, laser-free barcode scanner built for the demanding standards of healthcare environments. Built with [medical grade plastic](#), it's tough enough to withstand frequent cleaning with harsh disinfectant solutions. Plus, it's built with the signature toughness of our DuraScan line. It's IP54-rated for dust, liquid and bacteria protection, designed to be dropped frequently.

With a safe and effective LED aimer, it offers high-performance scanning of 1D, 2D barcodes, PDF 417, OCR fonts, and DotCode. Accurately captures patient information and personal identification documents, such as passport, and drivers' licenses for check-in or admissions. It scans barcodes as small as 3 millimeters and allows omni-directional scanning, ideal for scanning vials and syringes. Also scans barcodes displayed on a screen or printed, and barcodes on curved and reflective surfaces and poor quality and challenging barcodes, for first-time, every-time scanning. The motion tolerance feature offers faster scanning and extended scanning range up to 24 inches away which provides a larger scanning 'sweet spot' to capture barcodes.

From patient admissions to bedside point of care, from the pharmacy to suite number who-knows-where, the D755 is a perfect solution for applications that are used in hospitals, blood banks, pharmacies, residential care facilities and home care organizations.



Patient ID



Pharmacy Inventory



Patient Tracking



Features

- **Medical Grade Housing** – IP54 sealing and designed to resist the harmful effects of harsh cleaning agents. Allows safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.
- **Scanning** – Fast 2D and 1D barcode scanning with highly visible and safe LED aimer and omni-directional ability. Scans on paper or screen. Scans DotCode, OCR A&B fonts and OCR passport fonts for accurately capturing visitors and patient Identification information.
- **Scan performance** – Scans poor quality and challenging barcodes. Captures barcodes farther, up to 24"/60 cm away. Larger 'sweet spot' to decrease the need to repositioning the scanner when scanning. Scans extremely small barcodes as small as 3 millimeter. Motion tolerant to capture barcodes when moving.
- **Certified by Apple® for iOS devices** – Guaranteed Compatibility.
- **Native App Support** – Socket Mobile's Capture SDK enables easy native app integration in your applications to improve business productivity.
- **Exceptional Ergonomics** – Small, light and fits perfectly in the hand for comfortable use over extended periods of time.
- **User Feedback** - Audible tones and hand pulsation. Set the scanner hand pulsation only when you do not want to disturb others with scanning sounds.
- **User Indicators** – Intuitive LEDs, Bluetooth connection, battery level and scanning status.
- **Long-Lasting, Replaceable, Rechargeable Battery** - Designed to last over an entire busy 12-hour shift, with an LED indicator that alerts the user when a battery charge is needed.
- **Rugged Design** - withstands 2,500 drops to Linoleum from 5' and 5,000,000 scan presses.
- **Bluetooth Wireless Technology** - Dependable Bluetooth connection to iOS, Android and Windows 10 devices. Auto-reconnection maintains connection even in different environments.
- **Wearable** - Wrist strap included. Optional: Holster and Durable Retractable Clip available.
- **Designed and Made in the USA.**
- **1-Year Warranty.**
- **Extended Warranty** - Our optional flexible service plans keeps your scanner up and running in like-new condition with coverage for accidental damage and everyday wear-and-tear.

Physical Characteristics

1.5 in. (37.1 mm)

1.6 in. (40.1 mm)

Weight/Mass
3.8 oz. (109g)

5.2 in.
132.2 mm



Single Package includes

- (1) DuraScan D755, 2D/1D Barcode Imager
- (1) Charging Cable
- (1) Wrist Strap
- (1) Get Started Insert



**Socket Mobile
Companion App
Download for easy setup!**

The D755 is available in 2 packages:

Scanner (SKU# CX3799-2559)
Scanner w/ Charging Cradle (SKU# CX3558-2882)

Optional Accessories

Charging Stand



Great for using AutoScan Mode

Medical Grade Charging Cradle



Perfect for wall mounting

Charging Dock



Ideal as a desktop charger

Durable Retractable Clip



Provides quick access to scanner

Holster



Safe and accessible placement

Wrist Strap or Lanyard



Default Barcode Symbologies:

1D Symbologies: Codabar, Code 39, Code 93, Code 128, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, UPC A, UPC EO
2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, PDF417
Postal Codes: Australia Post

Supported Barcode Symbologies:


1D Symbologies: Bookland EAN, Chinese 2 of 5, Codabar, Code 11, Code 39, Code 93, Code 128, Composite CC-A/B, Composite CC-C, Composite TLC, Discrete 2 of 5, EAN-13/JAN, EAN-8/JAN, GS1 Databar, GS1 Databar Expanded, GS1 Databar Limited, GS1-128, Interleaved 2 of 5, ISBT 128, ISSN EAN, Matrix 2 of 5, MSI, UPC/EAN/JAN, UPC A, UPC EO
2D Symbologies: Aztec, Data Matrix, Maxicode, Micro PDF417, MicroQR, PDF417, QR Code
Postal Codes: Australia Post, Han Xin, Japan Postal, KIX Code, Maxicode, Netherlands, UPU FICS Posta, US Planet, US Postnet, USPS 4CB/One Code/Intelligent Mail

Scan Angle: 48° (Horizontal) - 30° (Vertical)

Sensor Resolution: 1280 horizontal x 800 vertical pixels

Print Contrast: Down to 25%-20%

Reading Distance:



2.8 to 91.7 cm (1.1 to 36.1 in.) Depends on barcode size, symbology, label media

Decode Ranges:

	Near	Far
3 mil Code 39	3.0 in/5.8 cm	7.6 in/14.7 cm
5 mil Code 128	2.3 in/5.8 cm	9.8 in/24.9 cm
5 mil PDF 417	3.0 in/7.6 cm	7.9 in/20.1 cm
6.67 mil PDF 417	2.5 in/6.3 cm	10.1 in/25.7 cm
10 mil DataMatrix	2.1 in. / 5.3 cm	11.0 in. / 27.8 cm
100% UPC A	1.6 in/4.1 cm*	24.9 in/63.2 cm
15 mil Code 128	2.4 in. / 6.1 cm	27.8 in. / 70.6 cm
20 mil Code 39	1.6 in/4.1 cm*	36.1 in/91.7 cm
20 mil QR Code	1.1 in. / 2.8cm	17.5 in. / 44.5 cm

Battery Type:	Replaceable 1400 mAh Lithium - Ion Battery
Charge Time:	6 Hours
Battery Life - Per Full Charge:	Standby time: over 20 hours Active Scan Time: 85,000 scans within 9 hours (based on 2 scans every 1 second) 17,000 scans within 19 hours (based on 1 scan every 4 seconds)
Note:	Battery life varies depending on ambient temperature, ambient light and age of battery. <i>For more battery information click here.</i>
Number of Batteries Used:	1
Weight of Battery:	35g
Percentage Lithium:	26.5%
Battery mAh:	1400 mAh
Number of Cells Per Battery:	1
Watt Hours Per Battery:	5.55
Type of Cell (ex. AA):	Proprietary
Chemical Composition (ex. Alkaline):	Lithium-polymer
Lithium Content:	9.32g
Battery Voltage:	3.7v
Hazmat UN Number:	UN3481, P.I. 967
ROHS Compliance Indicator:	Yes, included with scanner
Battery Country of Origin:	China
Commodity Code:	8507.60.0000

Bluetooth (wireless connection)

Bluetooth Radio:	Class 2 Bluetooth, version 2.1 + EDR (Enhanced Data Rates) with 56-bit data encryption
Bluetooth Range:	Up to 10 meters (33 ft.) depending on environment, range limit is usually due to the Host Device (phone, tablet or notebook)
Bluetooth Profiles:	Basic Mode - Human Interface Device (HID) ,Application Mode - Serial Port Profile (SPP) and iOS Application Mode*. Some Operating Systems or smartphone/tablet models may support only one profile. <i>*By default, the scanner is set to iOS Application Mode.</i>

Apple, Android and Windows PC with Bluetooth Classic HID are compatible with all Socket Mobile scanners.

*Chromebook and Linux supports HID mode only.

Scanner Type

Technology:	2D/1D Barcode Imager
Light Source:	one (1) warm-white LED
Aimer:	525 nm green LED

User Environment

Ambient Light:	From 0 to 100 000 lux, From pitch black to direct sun light
Operating Temperature:	0° to 45° C (32° to 113° F)
Storage Temperature:	-5° to 70° C (-22° to 158° F)
Relative Humidity:	95% at 60° C (140° F) (non-condensing)
Sealing:	IP54 (Ingress Protection rating for dust and water) EN60529
Drop Specifications:	6 drops to concrete - 1 on each side at 6.6 ft. (2 m)
Tumble Specifications:	2,500 cycles at 3.3 ft. (1 m) to metal plate, IEC6008-2-31, IEC60068-2-32 3)

Operating System Compatibility

Android OS - Basic Mode (HID) and App Mode (SPP)

Mac OS and Linux - Basic Mode (HID) only

Apple iOS - Basic Mode (HID) and iOS Application Mode*

Windows OS 10 - Basic Mode (HID) and App Mode (SPP)

Compatible with devices supporting Basic Mode (HID) protocol. Supported keyboard languages - ANSI, English UK, English, French, German, Italian, Japanese, Polish, Spanish and Swedish

*By default, the factory settings of the Socket Mobile Scanners are set to iOS Application Mode. In order to use the scanner with an application using Capture SDK, the scanner must be configured in Application Mode (Bluetooth Serial Port Profile: SPP)

Certified by Apple® for iOS devices (iPad®, iPhone®, iPod Touch®) and compatible with Android and Windows®.



Certification & Regulatory

Bluetooth SIG: Declaration ID: D030473 QD ID: 82009

Electrical Safety: Certified to IEC 60950-1, UL 60950-1, CAN/CSA C22.2

Environmental: Environmental: RoHS EN 50581

EMI / RFI: FCC Part 15 Class C, RSS 210, iCES 003, C-Tick, CISPR 22, CE EN55022, EN55024, TELEC
 FCC ID: T9J-RN41-3
 IC ID: 6514A-RN413
 Telec ID: 201-135280

LED Safety: IEC 62471, EN 62471 (EXEMPT GROUP)



Warranty

Scanner: Standard one year limited warranty

Accessories: 90 days (batteries, charging cable, wrist strap)

Extended Warranty: www.socketmobile.com/socketcare
 (sold separately)



Common Uses

Admitting / Discharge Specimen Collection / Tracking Patient ID Wristbands

Medication Administration Pharmacy Inventory Document Tracking

Retail/Point of Sale Warehouse management Transportation

Office use Shipping & Receiving Mobile Tracking

Healthcare Field Sales/Service Inventory

socketmobile.com

Worldwide: +1 510 933 3000

North America: +1 800 552 3300

EMEA & Russia: +41 62 834 07 80

France: +33 (801) 840504

Malaysia (Toll Free) +60 (1800) 818234

sales@socketmobile.com

Asia Pacific: +1 510 933 3122

Germany: +41 62 834 07 80

Switzerland: +41 62 834 07 80

Switzerland (Toll Free): +41 (800) 898003

UK/Ireland/South Africa: +44 (800) 0487363

sales-japan@socketmobile.com

Japan: +8190 9808 0518

Japan (Toll Free): +81 (800) 9190303

Latin America: +1-510-933-3153

Taiwan (Toll Free) +886 00801491497

©2022 Socket Mobile, Inc. All rights reserved.Socket®, the Socket Mobile logo, SocketScan®, DuraScan®, Battery Friendly® are registered trademarks or trademarks of Socket Mobile, Inc. Microsoft® is a registered trademark of Microsoft Corporation in the United States and other countries. Apple®, iPad®, iPad Air®, iPad mini®, iPad Pro®, iPhone®, iPod touch®, Objective-C®, Swift™, and Xcode® are registered trademarks of Apple, Inc., registered in the U.S. and other countries. The Bluetooth® Technology word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by Socket Mobile, Inc. is under license. Other trademarks and trade names are those of their respective owners.