

DATA SHEET

VS-2002-ENC, VS-2004-ENC

2- AND 4-PORT HDMI OVER IP H.264 ENCODERS

24/7 TECHNICAL SUPPORT AT 877.877.2269 OR VISIT BLACKBOX.COM



BLACK BOX®

OVERVIEW

2- AND 4-PORT HDMI OVER IP H.264 ENCODERS (VS-2002-ENC, VS-2004-ENC) DATA SHEET

INTRODUCTION

The VS-2002-ENC or VS-2004-ENC is a 2- or 4-port live streaming media encoder that interfaces with HDMI signals for delivering media over IP networks. The VS-2002-ENC or VS-2004-ENC can be used with the VS-2001-DEC Decoder to deliver an A/V signal over a LAN or WAN.

The Encoder also works with a third-party decoder such as a set-top box, VLC, or Kodi media player on PCs to provide complete end-to-end streaming systems. It features two or four HDMI inputs and one Ethernet output for simplified integration into AV systems.

FEATURES

- HAS TWO OR FOUR STANDARD HDMI 1.4 INPUTS
- SUPPORTS RESOLUTIONS FROM COMMON STANDARD DEFINITION, THROUGH ALL RESOLUTIONS INCLUDING 1080P60, UP TO AND INCLUDING 1920 X 1200 AT 60 HZ
- USES STANDARDS-BASED HIGH-PROFILE H.264/MPEG-4 AVC VIDEO COMPRESSION IN REAL TIME
- FEATURES ADJUSTABLE VIDEO BANDWIDTH TARGETS FROM 1 MBPS THROUGH 10 MBPS
- OFFERS ASSIGNABLE PROGRAM NUMBER AND CHANNEL NAME INSERTED IN AN ENCODED STREAM
- OUTPUT RESOLUTION CAN TRACK INPUT RESOLUTION, OR BE FIXED AT A STATIC SIZE

FEATURES (CONTINUED)

- SUPPORTS AUDIO INPUT AS A COMPONENT OF HDMI INPUT
- OPERATES AT LPCM, AC3, MPEG1 LAYER 2
- SUPPORTS ANALOG AUDIO AND/OR COMPOSITE VIDEO FOR CLOSED CAPTIONS. CC REQUIRES USE OF A COMPATIBLE COMPOSITE CABLE
- OUTPUT HAS ONE STANDARD 10/100/1000BASE-T ETHERNET PORT
- COMMON COMMUNICATIONS PROTOCOLS/METHODS SUPPORTED INCLUDE TCP/IP, ARP, DHCP, ICMP (PING), IGMP, HTTP, RTP, UDP, RTMP, AND HLS
- OUTPUT STREAM CAN BE SET TO RTP, UDP, USING EITHER UNICAST OR MULTICAST ADDRESSING; OR TO RTMP OR HLS UNICAST
- SUPPORTS UP TO FOUR SIMULTANEOUS HLS SESSIONS PER VIDEO INPUT
- UDP/RTP VIDEO STREAM CAN BE DECODED BY ANY NUMBER OF ETHERNET ATTACHED RECEIVING DEVICES, INCLUDING PC/MAC, VLC, IP SET-TOP BOX, IPSTB-ENABLED TELEVISION, OR CUSTOM APPLIANCE
- OUTPUTS AUDIO IN MP2, AC3 OR AAC FORMAT
- MANAGE THE UNIT VIA A MAESTRO WEB GUI BROWSER
- SUPPORTS POWER-OVER-ETHERNET (POE), ALLOWING FOR VS-2002-ENC OR VS-2004-ENC TO BE POWERED BY AN APPROPRIATE SWITCH OR POWER INJECTOR
- UPGRADE THE SOFTWARE THROUGH THE MAESTRO WEB MANAGEMENT APPLICATION



SPECIFICATIONS

2- AND 4-PORT HDMI OVER IP H.264 ENCODERS (VS-2002-ENC, VS-2004-ENC) DATA SHEET



VS-2002-ENC



VS-2002-ENC

WHAT'S INCLUDED WITH THE VS-2002-ENC

- (1) HDMI OVER IP H.264 ENCODER, 2-PORT (VS-2002-ENC)
- (1) POWER ADAPTER (12 VDC, 1 A)

WHAT'S INCLUDED WITH THE VS-2004-ENC

- (1) HDMI OVER IP H.264 ENCODER, 4-PORT (VS-2004-ENC)
- (1) POWER ADAPTER (12 VDC, 1 A)

HDMI OVER IP H.264 ENCODER, 2-PORT AND 4-PORT (VS-2002-ENC, VS-2004-ENC) SPECIFICATIONS

VIDEO	
INPUT VIDEO PORT	(2) or (4) HDMI, Type A, 19-pin, female
INPUT VIDEO TYPE	HDMI 1.4 with HDCP 2.2
SUPPORTED INPUT VIDEO RESOLUTIONS	720 x 480i/p at 60 Hz, 1280 x 720i/p at 60 Hz, 1920 x 1080i/p at 60 Hz, 720 x 576i/p at 50 Hz, 1920 x 1080i/p at 50 Hz, 1280 x 720p at 30 Hz, 1920 x 1080p at 25 Hz, 1920 x 1080p at 24 Hz
INPUT VIDEO SIGNAL	0.5 – 1.2 V p-p
INPUT DDC SIGNAL	5 V p-p (TTL)
VIDEO ENCODING BIT RATE	1 Mbps to 10 Mbps (configurable)
OUTPUT VIDEO PORT	(1) LAN (PoE), 10/100/1000BASE-T
OUTPUT VIDEO TYPE	H.264/MPEG-4 AVC, HLS (low/high data rate)
OUTPUT VIDEO RESOLUTIONS	720 x 480i/p at 60 Hz, 1280 x 720i/p at 60 Hz, 1920 x 1080i/p at 60 Hz, 720 x 576i/p at 50 Hz, 1920 x 1080i/p at 50 Hz, 1280 x 720p at 30 Hz, 1920 x 1080p at 25 Hz, 1920 x 1080p at 24 Hz Audio: Encoding: LPCM, AAC; Sampling Rate: 48 kHz; Bitrate: 1.6 Mbps (LPCM), < or = 240 kbps (AAC) Delivery: Encapsulation Format: MPEG-2 transport stream Transmission Format: TS over UDP, TS over RTP Transmission Method: unicast, multicast, RTP
AUDIO	
INPUT AUDIO PORT	(2) or (4) HDMI Type A, 19-pin, female, (4) 3.5-mm mini-jack (analog audio)
SAMPLING RATE	48 kHz
OUTPUT CONNECTORS	(1) 3.5-mm 3-pin Phoenix connector, (1) RJ-45
SUPPORTED OUTPUT	Unbalanced stereo audio; Encoding: stereo LPCM/AAC; Sampling Rate: 48 kHz; Bit rate: 1.6 Mbps (LPCM), ≤ 240 kbps (AAC)
OUTPUT AUDIO PORT	(1) LAN (PoE), 10/100/1000BASE-T



SPECIFICATIONS


2- AND 4-PORT HDMI OVER IP H.264 ENCODERS (VS-2002-ENC, VS-2004-ENC) DATA SHEET

HDMI OVER IP H.264 ENCODER, 2-PORT AND 4-PORT (VS-2002-ENC, VS-2004-ENC) SPECIFICATIONS (CONTINUED)	
CONTROL	
CONTROL CONNECTORS	(1) RJ-45, 10/100/1000BASE-T Ethernet port
CONTROL METHOD	Web UI
GENERAL	
OPERATING TEMPERATURE	32 to 113° F (0 to 45° C)
STORAGE TEMPERATURE	-4 to +158° F (-20 to +70° C)
OPERATING HUMIDITY	10 to 90%, noncondensing
STORAGE HUMIDITY	10 to 90%, noncondensing
POWER	12 VDC, 1 A
POWER CONSUMPTION	12 W (max.)
PRODUCT DIMENSIONS	VS-2002-ENC, VS-2004-ENC: 4.41" H x 7.09" W x 1.34" D (11.2 x 18 x 3.4 cm)
CERTIFICATION	CE, FCC



APPLICATION DIAGRAM

2- AND 4-PORT HDMI OVER IP H.264 ENCODERS (VS-2002-ENC, VS-2004-ENC) DATA SHEET



ORDERING INFORMATION

ITEM	CODE
HDMI over IP H.264	
Encoder, 2-Port	VS-2002-ENC
Encoder, 4-Port	VS-2004-ENC

NOTES _____

DISCLAIMER

Black Box Corporation shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Corporation may revise this document at any time without notice.

ABOUT BLACK BOX

Black Box® is a trusted IT solutions provider delivering cutting-edge technology products and world-class consulting services to businesses across the globe in every industry. The breadth of our global reach and depth of our expertise accelerate customer success by bringing people, ideas, and technology together to solve real-world business problems.