

## **AXIS P3925-R Network Camera**

## Best-in-class dome for advanced onboard surveillance

Specifically designed for onboard surveillance, AXIS P3925-R complies with all relevant transportation industry regulations including EN50155, EN45545, and NFPA 130. Featuring Axis Lightfinder and Axis Forensic WDR, it delivers true colors and great detail in challenging light or near darkness. Enclosed in an IK10-, IP66-, IP67-rated metal casing, this robust, vandal-resistant camera offers extended capabilities for analytics. Furthermore, enhanced security features prevent unauthorized access and safeguard your system.

- > Vandal-resistant, metal casing
- > Complies with EN50155, EN45545, and NFPA 130
- > Lightfinder and Forensic WDR
- > Electronic image stabilization
- > Enhanced security features









Models	AXIS P3925-R RJ45 AXIS P3925-R M12		Video: average bitrate degradation, day-night mode, live strea open, tampering	
Camera Image sensor	1/2.9" Progressive scan RGB CMOS	Event actions	Day-night mode Defog	
Lens	2.8 mm, F1.6 Horizontal field of view: 110° Vertical field of view: 62° M12 mount, fixed iris See <b>Optional accessories</b> for exchangeable lenses		Guard tours Upload images or video clips: FTP, HTTP, HTTPS, SFTP, email an network share Notification: HTTP, HTTPS, TCP and email Overlay text Preset positions	
Minimum illumination	Color: 0.06 lux at 30 IRE F1.6 B/W: 0.01 lux at 30 IRE F1.6 Color: 0.12 lux at 50 IRE F1.6 B/W: 0.02 lux at 50 IRE F1.6		Record video: SD card and network share SNMP trap messages WDR mode	
Shutter speed	1/33500 s to 2 s	Data streaming Built-in	Event data Pixel counter	
Camera angle	Pan: ±30°	installation aids	Fixel Counter	
adjustment	Tilt: 15-90° Rotation: ±175°	Analytics	Included	
Video		Applications	AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard	
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles H.265 (MPEG-H Part 2/HEVC) Main Profile Motion JPEG		AXIS Video Motion Detection, active tampering alarm <sup>d</sup> , blocke view detection <sup>e</sup> , shock detection Supported Support for AXIS Camera Application Platform enabling	
Resolution	1280x960 to 160x120 1920x1080 to 160x90		installation of third-party applications, see axis.com/acap	
Wide dynamic	Forensic WDR	General		
range Frame rate	Up to 25/30 fps (50/60 Hz) in all resolutions	Casing	IP66/67-, NEMA 250 4X- and IK10-rated aluminum casing, polycarbonate clear dome	
Traine rate	45 fps in 720p	Sustainability	PVC free	
	Capture mode 2MP 1920x1080 (16:9) @25/30 fps Capture mode 1MP 1280x720 (16:9) @45 fps	Mounting	Inside vehicles and rolling stock	
Video streaming	1 7 7 1	Memory	1 GB RAM, 512 MB Flash	
video streaming	Motion JPEG  Axis Zipstream technology in H.264 and H.265	Power	Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 2 Typical 4.2 W, max 6.4 W	
	Controllable frame rate and bandwidth VBR/ABR/MBR H.264 and H.265 Video streaming indicator	Connectors	RJ45: male, 10BASE-T/100BASE-TX M12: female, rugged, D-coded with rotatable coupling nut All connectors support PoE	
Multi-view streaming Image settings	Up to 8 individually cropped out view areas  Compression, brightness, sharpness, contrast, white balance,	Storage	Support for microSD/microSDHC/microSDXC card with UHS Speed Class U1 Support for SD card encryption (AES-XTS-Plain64 256bit) Support for recording to network-attached storage (NAS)	
	Forensic WDR, exposure control, exposure zones, fine tuning of behavior at low light, rotation: 0°, 90°, 180°, 270° including Corridor Format, dynamic overlay, 20 individual polygonal privacy mask, mirroring of images, defogging, electronic image stabilization <sup>a</sup> Scene profiles: forensic, vivid, traffic overview	Operating conditions	For SD card and NAS recommendations see axis.com  Normal: -40 °C to 55°C (-40 °F to 131°F)  Maximum (intermittent): 70 °C (158 °F)  Arctic Temperature Control: start-up at -40 °C (-40 °F)  Humidity: 10-95% RH (non-condensing)	
Pan/Tilt/Zoom	Digital PTZ, preset positions, guard tour, control queue	Storage	-40 °C to 65 °C (-40 °F to 149 °F)	
Network		conditions		
Security	Password protection, IP address filtering, HTTPS <sup>b</sup> encryption, IEEE 802.1x (EAP-TLS) <sup>b</sup> network access control, digest authentication, user access log, centralized certificate management, brute force delay protection, signed firmware, secure boot, firmware with Long Term Support (LTS) firmware <sup>C</sup>	Approvals	EMC EN 55032 Class A, EN 55035, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-3(A)/NMB-3(A), VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35, EN 50121-4, EN 50121-3-2, IEC 62236-4, ECE R10 rev.05 (E approval), EN 50498	
Supported protocols	IPv4, IPv6 USGv6, HTTP, HTTPS <sup>b</sup> , HTTP/2, SSL/TLS <sup>b</sup> , QoS Layer 3 DiffServ, FTP, SFTP, CIFS/SMB, SMTP, Bonjour, UPnP*, SNMP v1/v2c/v3 (MIB-II), DNS, DynDNS, NTP, RTSP, RTP, SRTP, TCP, UDP, IGMPv1/v2/v3, RTCP, ICMP, DHCPv4/v6, ARP, SOCKS, SSH, LLDP, MQTT v3.1.1, Syslog		Safety IEC/EN/UL 62368-1, CAN/CSA C22.2 No. 62368-1, EN 45545, UN ECE R118, NFPA 130, IS 13252 Environment IEC/EN 61373 Category 1 Class B,	
System integra	rtion		IEC/EN 60529 IP66, IEC/EN 60529 IP67, parts of	
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform; specifications at <i>axis.com</i> AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF® Profile G, ONVIF® Profile S and ONVIF® Profile T, specification at <i>onvif.org</i>		NEMA 250 Type 4X (ingress of water and gasket test), IEC/EN 62262 IK10, IEC 60721-3-5 Class 5M3 (vibration and shock), EN 50155:2017 OT2/ST2, IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-27, IEC 60068-2-64, IEC 60068-2-78 Network	
Event conditions	Device status: above operating temperature, above or below operating temperature, IP address		NIST SP500-267	
	removed, network lost, new IP address, shock detected, storage	Dimensions	Height: 49.4 mm (1.94 in), ø 110 mm (4.33 in)	
	failure, system ready, within operating temperature Edge storage: recording ongoing, storage disruption I/O: manual trigger, virtual input	Weight	RJ45: 400 g (0.88 lb) M12: 410 g (0.90 lb)	

T10137578/EN/M11.3/2101 www.axis.com

Included accessories	Installation guide, Windows® decoder 1–user license, drill hole template, lens tool, Resistorx® L–key		Languages	English, German, French, Chinese, Japanese, Korea
Optional accessories	Lenses Lens M12 2.1 mm F1.8 IR: horizontal field of view 145° Lens M12 3.6 mm F1.8 IR: horizontal field of view 87° Lens M12 6 mm, F1.9 IR: horizontal field of view 56° Lens M12 8 mm F1.8 IR: horizontal field of view 40° Other AXIS T94D01S Mount Bracket, AXIS T94D02S Curved Mount Bracket, Network coupler IP66, network cable coupler indoor For more accessories, see axis.com	a. b. c.	vehicle This product inc OpenSSL Toolkit (eay@cryptsoft. In the LTS track and stability. Ne	5-year warranty, see axis nonly when camera is direc ludes software developed by (openssl.org), and cryptogr com). for firmware upgrades, impresse for dirmware upgrades in tampering attempts in statitampering attempts in onbot
Video management software	AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available at axis.com/vms		nvironmental resp xis.com/environm	oonsibility: ental-responsibility

Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese
Warranty	5-year warranty, see axis.com/warranty
vehicle	n only when camera is directed to capture scenes outs cludes software developed by the OpenSSL Project for t. (openssl.org), and cryptographic software written by

provements are focused on cybersecurity n the firmware from the Active track titic and non-crowded scenes. board environments.

