



Overview

Model Name	APC Back-UPS 400, 230V, Korea
Includes	User Manual , Wall-mounting template
Standard Lead Time	Usually in Stock
Product Distribution	KOREA, REPUBLIC OF

Output

Output Power Capacity	240 Watts / 400 VA
Max Configurable Power (Watts)	240 Watts / 400 VA
Nominal Output Voltage	230V
Nominal Output Voltage	Standby
Waveform Type	Stepped approximation to a sinewave
Output Connections	(4) Schuko CEE 7 (Battery Backup) , (4) Schuko CEE 7 (Surge Protection)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz
Input Connections	Schuko CEE 7/7P
Cord Length	1.83 meters
Maximum Input Current	10 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	16 hour(s)
Replacement Battery	APCRBC106
RBC Quantity	1

Communications & Management

Control panel	LED Status display with On Line : On Battery
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	310 Joules
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data Line Protection	Analog phone line for phone/fax/modem/DSL (RJ-45 connector) , Network line - 10/100 Base-T Ethernet (RJ-45 connector)

Physical

Maximum Height	86.0 mm
Maximum Width	230.0 mm
Maximum Depth	285.0 mm
Net Weight	5.4 kg
Shipping Weight	5.6 kg
Shipping Height	132.0 mm
Shipping Width	300.0 mm
Shipping Depth	366.0 mm
Master Carton Units	2.0
Master Carton Dimensions (Length x Width x Height)	15.0 inches
Master Carton Weight	12.2 kg
Color	Charcoal
SCC Codes	1073130425590 8
Units per Pallet	80.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-15000 meters
Storage Temperature	0 - 40 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	45.000 dB

Conformance

Approvals	CE , GOST , NEMKO
Standard warranty	2 years repair or replace
Equipment protection policy	--

Sustainable Offer Status

RoHS	Compliant
------	-----------