

4-Port HDMI over Cat6 Presentation Switch/Extender Kit - 4K 60 Hz, UHD, 4:4:4, HDR, PoC, 125 ft., TAA

MODEL NUMBER: **B320-4X1-HH-K2**



Allows you to switch between 4 HDMI sources transmitting 4K video with audio to one HDMI monitor located up to 125 ft. away.

Features

4-Port Presentation Switch Connects 4 Audio/Video Sources to One 4K HDMI Display

This HDMI presentation switch connects four separate HDMI source devices to your 4K television, projector or monitor's HDMI input and switches between them. For instance, connect up to four cable boxes, media servers, Blu-ray players, video game consoles, Roku boxes or other sources with HDMI outputs. Switch from one source to another using the manual push buttons, RS-232 commands or the included remote control.

Suitable for a Wide Range of Audio/Video Applications for Work or Play

This switch is recommended anywhere a variety of video signals is transmitted to a hi-def display. It is suitable for home theaters, video and multimedia presentations, security applications or digital signage in classrooms, bars, restaurants, conference rooms, lecture halls, exhibition centers and trade shows.

Transmits Crystal-Clear 4K Video with HDR, 4:4:4 Color and 7.1-Channel Audio

The B320-4X1-HH-K2 supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as well as HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This switch also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Full, rich, uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital surround sound ensure your ears receive the same treat as your eyes.

Remote Receiver Works Up to 125 ft. Away

The HDMI presentation switch connects to the included passive remote receiver with a user-supplied Cat6 cable (sold separately). The receiver extends 4K video and digital audio signals to an HDMI display up to 125 feet away from the switch.

Built-In PoC Technology Provides Receiver Power to Avoid Bulky External Power Bricks

Power over Cable (PoC) technology powers the remote receiver over Cat6 cable. Green and orange LEDs will light up to indicate the system is receiving sufficient power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to place the receiver away from an AC outlet.

Plug-and-Play Operation for Quick Setup and Immediate Use

The included switch and receiver work right out of the box with no software required. Mounting hardware

Highlights

- Connects up to 4 HDMI sources to an HDMI display up to 125 ft. away via Cat6 cable
- Push buttons, IR remote or RS-232 commands allow quick switching between sources
- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) with 7.1-channel surround sound
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Switch between your cable box, Blu-ray player, video game console, Roku or other HDMI sources in your home theater
- Connect multiple desktop computers and laptops to one monitor to save desk space
- Monitor the premises with multiple security cameras connected to a single display
- Create up to 4 different digital signage messages to appear at various times on a 4K HDMI display

System Requirements

- Up to 4 source devices with HDMI output
- Display device with HDMI input

Package Includes

- B320-4X1-HH-K2 4-Port HDMI



is included for installing the switch and receiver on a wall, pole or 19-inch rack. Connect your devices to the switch's HDMI ports with user-supplied HDMI cables (sold separately), and plug the switch's external power supply into an AC power source.

TAA-Compliant for GSA Schedule Purchases

The B320-4X1-HH-K2 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

over Cat6 Presentation
Switch/Extender

- IR remote control
- IR receiver cable, 5 ft.
- External power supply with 4.5 ft. cord (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, U.K., Europe, Australia)
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332256294
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V~50/60Hz, 0.6A
External Power Supply Output Specs (V / A)	24V/1A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
External Power Supply Certifications	CCC; CE; FCC; GS; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), Orange (Input 1-4); RX: Green (Power), Orange (Signal Link)
PHYSICAL	
Color	Black
Material of Construction	Metal
Receiver Unit Dimensions (hwd / in.)	3.74 x 2.36 x 0.73
Receiver Unit Weight (lbs.)	0.17



Transmitter Unit Dimensions (hwd / in.)	9.25 x 3.94 x 1.17
Transmitter Unit Weight (lbs.)	1.43
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	
Signal Range (ft.)	125
Signal Range (m)	38
CONNECTIONS	
Ports	4
Side A - Connector 1	3.5MM (FEMALE); DB9 (FEMALE); (4) HDMI (FEMALE); RJ45 (FEMALE)
Side B - Connector 1	HDMI (MALE); RJ45 (MALE)
Connector Plating	Nickel
FEATURES & SPECIFICATIONS	
Port Selection	Pushbutton; Remote Selector
Max Supported Video Resolution	4K x 2K (3840 x 2160) @60Hz
HDMI Specification	2.0
HDCP Specification	2.2
Driver Required	No
Recommended Category Cable	Cat6
Power Over Cable (PoC) Support	Yes
3D Video Supported	Yes
Technology	Cat5/5e; Cat6; HDMI; HDR
Chroma Sub Sampling	4:4:4
SPECIAL FEATURES	
HDR Support	Yes
Wall Mountable	No
DIN Mountable	No
Integrated/Removable Cable	No
MST Support	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Included Mounting Accessory	No
Multi-Resolution Support	No
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>