

Key Features

All-in-One Solution | ViewBoard Interactive Flat Panel |

Faster WiFi | Slim Trolley Cart



Product Description

Ideal for education environments, this all-in-one ViewBoard Bundle includes a 98" ViewBoard IFP9850 4K interactive flat panel, a wireless AC adapter, and a VB-STND-005 slim trolley cart.



98"
DISPLAY

RESOLUTION

20-Point
TOUCH
INTERACTIVE

Contact Sales

- call: 888.881.8781
- email: salesinfo@viewsonic.com
- visit: viewsonic.com

Display:

Display Size (in.):	98
Viewable Area (in.):	97.5
Light Source:	LED
Resolution:	3840 x 2160
Refresh Rate (Hz):	60
Aspect Ratio:	16:9
Static Contrast Ratio:	1,200:1
Dynamic Contrast Ratio:	5,000:1
Backlight Life (Hours):	50,000
Brightness:	350 cd/m ²
Response Time (Typical GTG):	8ms
Viewing Angles:	178° horizontal, 178° vertical
Panel Surface:	9H
Operation Rating:	16/7

Networking:

Ethernet LAN:	10/100/1000 Mbps
---------------	------------------

Embedded Player:

OS:	ViewBoard OS (embedded Android 8)
GPU:	ARM Mali0G51
CPU:	ARM Quad Core A73 + A53
CPU Processor Speed:	A73: 1.1GHz, A53: 1.5GHz
Memory:	3GB
Storage:	32GB

Audio:

Internal Speakers:	10W (x2)
Subwoofer:	15W (x1)

Connector:

HDMI 2.0 In(3), VGA(1), 3.5mm Audio In(1), 3.5mm Audio Out(1), SPDIF Audio Out(1), USB 3.0(4), USB 2.0(3), Slot-in PC Slot(1), USB B Touch Port(2), RS232(1), Ethernet LAN (RJ45)(1), WIFI Module Slot(1)

Power:

Voltage:	100-240 VAC
Consumption (max):	350W
Consumption (typical):	171W
Stand-by:	<0.5W

Controls:

On Screen Display:	Input, Volume, Backlight, Audio, Screen, Display, Adjust
Remote Control:	Volume, Channel, Source, Mute, Back, Input, Menu

Operating Conditions:

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	10-90%

Touch:

Touch Technology:	Infrared
Touch Points:	20-Point Touch
Tip Detection:	Dual tips, 3mm and 8mm

Weight (Imperial):

Net (lbs):	263.9
Gross (lbs):	358.2

Weight (metric):

Net (kg):	119.7
Gross (kg):	162.5

Dimensions (Imperial) (WxHxD):

Packaging (in.):	97.8 x 58.8 x 14.8
Physical (in.):	88.4 x 52.1 x 3.6

Dimensions (metric) (WxHxD):

Packaging (mm):	2483.0 x 1493.0 x 376.0
Physical (mm):	2245.0 x 1323.0 x 91.0

Mount:

VESA Compatible:	800 x 600 mm
------------------	--------------

General:

Warranty: 3-year limited warranty on parts, labor and backlight, onsite warranty

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

PACKAGE CONTENTS: IFP9850 display, stylus pen x 2, power cable, remote control with batteries, ViewSonic Wizard CD (User Guide), Quick Start Guide

Regulations: cTUVus, FCC, ENERGY STAR, Mexico Energy, CE, CB, RoHS, ErP, WEEE

Accessories:

LB-WIFI-001, MVBM_ADV_1Y01, MVBM_ADV_3Y01, MVBM_ADV_5Y01, MVBM_ADV_7Y01, NMP 760, PD-IFP-001, PD-IFP-002, PD-IFP-003, PD-IFP-004, SW-071, SW-072, SW-073, SW-074, SW-075, SW-101, VB-BLF-001, VB-BLF-002, VB-BLF-003, VB-BLM-001, VB-BLM-002, VB-BLM-003, VB-BLW-001, VB-BLW-002, VB-BLW-003, VB-CAM-001, VB-CAM-002, VB-CAM-201, VB-EBM-001, VB-EBS-001, VB-EBT-001, VB-EBV-001, VB-EBV-002, VB-EBW-001, VB-STND-001, VB-STND-002, VB-STND-003, VB-STND-004, VB-STND-005, VB-VIS-001, VB-WIFI-001, VB-WKB-001, VPC15-WP-4, VPC15-WP-6, VPC16-WP-4, VPC17-WP-6, VPC25-W33-P1, VPC25-W53-P1, VPC25-W53-P2, VPC27-W55-P2, WMK-047-2