

## PERFORMANCE

### Processor

Intel® Celeron® N4020 (2C / 2T, 1.1 / 2.8GHz, 4MB)

### Graphics

Integrated Intel UHD Graphics 600

### Chipset

Intel SoC Platform

### Memory

4GB Soldered DDR4-2400

### Memory Slots

Memory soldered to systemboard, no slots

### Max Memory

4GB soldered memory, not upgradable

### Storage

64GB eMMC 5.1

### Storage Support

- 64GB eMMC 5.1 on systemboard
- microSD card, supports FAT32 file up to 128GB

### Storage Slot

eMMC on systemboard, no slots

### Card Reader

microSD Card Slot

### Optical

None

### Audio Chip

High Definition (HD) Audio

### Speakers

Stereo speakers, 1W x2, optimized with Dolby® Audio™

### Camera

Front 2.0MP / Rear 5.0MP

### Microphone

2x, Array

### Battery

Integrated 30Wh

### Max Battery Life

MobileMark® 2014: 9.3 hr

Local video (1080p) playback@150nits: 10.7 hr

### Power Adapter

45W USB-C® (3-pin)

## DESIGN

### Display

10.3" WUXGA (1920x1200) IPS 340nits Glossy, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

Non-backlit, English

### Case Color

Graphite Grey

### Surface Treatment

Painting (Pad), Magnesium-Aluminium Painting (Kickstand)

### Case Material

PC-ABS + Magnesium-aluminium (Kickstand)

### Pen

Lenovo® Digital Pen

### Dimensions (WxDxH)

Pad: 253 x 166 x 9.9 mm (9.96 x 6.53 x 0.38 inches)

Folio case: 252 x 165 x 6.0 mm (9.92 x 6.49 x 0.23 inches)

### Weight

Pad: around 597 g (1.32 lbs)

Folio: around 269 g (0.59 lbs)

Total: around 866 g (1.91 lbs)

### Others

- Buttons: power key with LED, volume key
- Kick-stand hinge: free stop

## SOFTWARE

### Operating System

Windows® 10 Pro 64, English

### Bundled Software

Office Trial

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth®

11ac 2x2 + BT5.0

### WWAN

None

### NFC

None

### Standard Ports

- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)
- 1x microSD card slot
- 1x USB-C 3.2 Gen 1 (support data transfer and DisplayPort 1.2)
- 1x Headphone / microphone combo jack (3.5mm)

### Docking

IdeaPad® Duet Folio Keyboard

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0

### Fingerprint Reader

None

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ErP Lot 3
- RoHS compliant
- ENERGY STAR® 8.0

## MODEL

TopSeller : Yes

Announce Date : 2020-08-05

EAN / UPC / JAN : 195348009775

End of Support : 2026-06-25



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.


## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Digital Pen

GX80U45010

The Lenovo Digital Pen with 4096 levels of pressure sensitivity, provides a natural pencil-like and paper experience when you sketch and jot down notes. Users will also enjoy easy access to short-cut functions through...

## Recommended Services

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K78452)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

**PSREF**  
Product Specifications  
Reference