

# PowerLite® L200SW Wireless WXGA 3LCD Short-throw Laser Display

Projectors

Education



Bring bright, easy-to-read images up to 120" to your classroom with this WXGA display.

**Ultra bright** — 3,800 lumens of color/white brightness<sup>1</sup>

**Large, easy-to-read images** — 16:10 WXGA resolution for true-to-life images up to 120" diagonal

**Laser light source life** — virtually maintenance-free 20,000-hour laser light source with no lamps to replace<sup>2</sup>

**Large display size** — provides up to 2.5 times larger images than 75" flat panels

**Time-saving operation** — display in seconds with Instant On laser light source

**Convenient short-throw design** — greatly reduces shadowing

**Built-in split screen<sup>3</sup>** — allows simultaneous display of up to 4 connected devices

**Built-in 5GHz wireless** — supports Miracast® and wireless displays via Epson iProjection™ software to connect; display and share content simultaneously to/from up to 50 connected devices<sup>4</sup>

**Easily replace the PowerLite 525W/535W** — with compatible mounts

**Powerful 16 W speaker** — fill rooms with rich sound



**Specifications**

**Projection System** RGB liquid crystal shutter projection system  
**Driving Method** Poly-silicon TFT Active Matrix  
**Pixel Number** 1,024,000 dots (1280 x 800) x 3 chips  
**Color Brightness<sup>1</sup>** Color Light Output: 3,800 lumens  
**White Brightness<sup>1</sup>** White Light Output: 3,800 lumens  
**Aspect Ratio** 16:10  
**Image Size** 53" to 120" (540 mm to 1260 mm)  
**Display Resolution** WXGA (1280 x 800 x 3)  
**Light Source** Laser Diode  
**Light Source Life<sup>2</sup>**  
 Normal Mode: Up to 20,000 hours  
 Extended Mode: Up to 30,000 hours  
**Throw Ratio Range** 0.48 (Zoom: Wide), 0.65 (Zoom: Tele)  
**Size (Projected Distance)** 87" [2.2 m]  
**Keystone Correction Manual**  
 Vertical: ± 15 degrees  
 Horizontal: ± 15 degrees  
**Dynamic Contrast Ratio** Over 2,500,000:1  
**Color Reproduction** Up to 1.07 billion colors

**Projection Lens**

**Type** No Optical Zoom, Focus (Manual)  
**F-number** 1.6  
**Focal Length** 6.4mm  
**Zoom Ratio** 1 – 1.35 (Digital zoom)

**Other**

**Operating Temperature** 41 ° to 104 °F (0 ° to 40 °C) (low altitude), 41 ° to 95 °F (0 ° to 35 °C) (high altitude)  
**Power Supply Voltage** 100 – 240 V AC ± 10%, 50/60 Hz  
**Power Consumption**  
 Normal Mode: 265 W  
 Quiet Mode: 201 W  
 Standby Mode: 2.0 W  
 Energy-saving Mode: 0.5 W  
**Fan Noise**  
 Normal Mode: 36 dB  
 Quiet Mode: 26 dB  
**Security** Enterprise Level Security Encryption  
**Country of Origin** China

**Dimensions (W x D x H)**

**Projector (Including Feet)** 12.8" x 3.6" x 13.3"  
**Weight** 9.9 lb

**Interfaces**

2x HDMI®  
 1x Analog D-sub 15-pin (In)  
 1x Analog D-sub 15-pin (In/Out)  
 1x RCA Composite  
 2x Stereo Mini In  
 1x Stereo Mini Out  
 1x RS232C Control Port  
 1x USB-A Type for Wireless Adapter and Document Camera (DC-07)  
 1x USB Connector Type B  
 1x Wired LAN RJ-45  
 1x Microphone

Wireless support with optional LAN Adapter: Wireless 802.11b/g/n (2.4GHz), 802.11a/n/ac (5GHz)

**Remote Control**

**Features** Power, HDMI, LAN, Source Search, USB, Auto, menu, arrow buttons, enter, color mode, aspect, split, home, user, volume, default, ID, ESC, freeze, Num, e-Zoom, A/V Mute

**Operating Angle**  
 Front to Rear: 0 – 60 degrees  
 Right to Left: 30 – 30 degrees

**Operating Distance** 20 ft (6 m)

**Eco Features**

RoHS compliant  
 Epson America, Inc. is a SmartWay® Transport Partner®  
 Recyclable product<sup>6</sup>

**Support**

**Epson Connection<sup>SM</sup>**  
 Pre-sales Support: U.S. and Canada (800) 463-7766  
 Internet Website: [www.epson.com](http://www.epson.com)  
**Service Programs** 3-year projector limited warranty or 20,000 hours, whichever comes first.  
 Epson Road Service program, dedicated toll-free support (U.S. and Canada only)



\*Maximum speed and range are achievable when used with same enhanced mode technology. Actual features and performance may vary depending on your computer system, the environment and other factors.

**What's in the Box**

PowerLite L200SW, User's Guide Kit, Projector Remote Control, 2x AA Batteries, Projector Feet, 6' Power Cord, 6' HDMI Cable

**Ordering Information**

PowerLite L200SW V11H993020  
 Short-throw Wall Mount (ELPMB64) V12HA39010



Projector shown with mount, sold separately

1 Color brightness (color light output) and white brightness (white light output) will vary depending on usage conditions. Color light output measured in accordance with IDMS 15.4; white light output measured in accordance with ISO 21118. | 2 No required maintenance for the light source for up to 20,000 hours. Approximate time until brightness decreases 50% from first usage. Measured by acceleration test assuming use of 0.04 - 0.20 mg/m<sup>3</sup> of particulate matter. Time varies depending on usage conditions and environment. Replacement of parts other than the light source may be required in a shorter period. | 3 Split Screen feature requires remote control. Consult your user manual for input combinations. | 4 For wireless functionality, including via the Epson iProjection App, the projector must be configured on a network, either through the Ethernet port on the projector (check model specifications for availability) or via a wireless connection. Check your owner's manual to determine if a wireless LAN module must be purchased separately to enable a wireless connection. Not all Epson projectors are able to be networked. The Epson iProjection App does not support all files and formats. See [www.epson.com](http://www.epson.com) for details. | 5 SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency. | 6 For convenient and reasonable recycling options, visit [www.epson.com/recycle](http://www.epson.com/recycle)

See the latest innovations from Epson Business Solutions at [www.epson.com/foreducation](http://www.epson.com/foreducation)

Better Products for a Better Future™  
[eco.epson.com](http://eco.epson.com)



Epson America, Inc.  
 3131 Katella Avenue, Los Alamitos, CA 90720

Epson Canada Limited  
 185 Renfrew Drive, Markham, Ontario L3R 6G3

[www.epson.com](http://www.epson.com)  
[www.epson.ca](http://www.epson.ca)

EPSON and PowerLite are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future and Epson iProjection are trademarks of Seiko Epson Corporation. Epson Connection is a service mark of Epson America, Inc. Miracast® is a registered trademark of Wi-Fi Alliance®. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2020 Epson America, Inc. CPD-59396 8/20

**Contact:**

