

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

1-Port Industrial USB over Cat5/6 Extender Kit with ESD Protection - USB 2.0, 150 ft., Black, TAA

MODEL NUMBER: B203-101-IND



Industrial-grade transmitter/receiver combo connects your office laptop or PC to a webcam or other USB peripheral up to 150 ft. away.

Features

Industrial-Grade Extender Connects Your Computer to a USB Device up to 150 ft. Away

This plug-and-play extender kit with heavy-duty all-metal housings is ideal for connecting your office computer's USB-A port to a printer, 1080p webcam, external hard drive or other USB device located up to 150 feet (45 meters) away. The B203-101-IND includes a local transmitter and a remote receiver that extends USB 2.0 signals over user-supplied Cat5/6 cabling (such as Tripp Lite's N202-Series Cat6 Ethernet cables).

Protects Your Devices against Electrostatic Discharge (ESD)

Machines on the shop floor can generate electrostatic discharges, wiping out data and damaging sensitive electronics. This extender kit provides ESD protection to ± 15 kV, reducing potential static damage to your connected USB peripherals. The durable metal transmitter and receiver units withstand harsh physical conditions in industrial and commercial applications, such as factories, construction sites, supply rooms and warehouses.

With Great Distance Comes Great Flexibility

By extending the USB connection beyond the standard 16-foot distance limitation to 150 feet, the B203-101-IND provides workstation flexibility to place your computer and the USB device where they are best suited. This extender kit supports USB 2.0 data transfer rates up to 480 Mbps and is backward compatible with USB 1.1 technology, allowing you to connect legacy devices. No network connectivity is needed.

Plug-and-Play Kit Offers Flexible Power and Installation Options

With user-supplied USB cables, connect the transmitter to your computer and the receiver to your USB peripheral. Connect the transmitter and receiver with a user-supplied Cat5/6 cable (all cables sold separately). The extender kit requires no software to download and install. The metal chassis rest easily on any flat surface or mount to a wall or DIN rail using the included hardware. A power supply with international plug adapters as well as a RS-232 Phoenix adapter supporting a DC voltage range from 9-36V is included for connecting external power to the unit as needed.

TAA-Compliant for GSA Schedule Purchases

The B203-101-IND is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers
- ESD protection to ±15 kV cuts potential static damage to your connected peripherals
- Industrial-grade metal housings withstand harsh warehouse and factory environments
- Compatible with all major operating systems, including Windows, Mac OS and Chrome
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Connect an impact printer or 1080p webcam using existing in-wall Cat5/6 wiring to a computer, laptop or server located in another room
- Place the computer or server in a locked cabinet or closet to protect against tampering
- Mount to a wall or DIN rail in a harsh environment, such as a factory, construction site, supply room or warehouse

System Requirements

- Computer, laptop or server with USB-A port
- Cat5/5e/6/6a cabling
- Any major operating system, including Windows, Mac OS and Chrome



Package Includes

- Transmitter
- Receiver
- (2) DIN rail mounts
- (4) M4 screws
- RS-232 Phoenix adapter
- International power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- (4) Plug adapters (North America, Europe, U.K., Australia)
- Owner's manual

Specifications

OVERVIEW		
UPC Code	037332256072	
INPUT		
Product Length (in.)	4.528	
Product Length (cm.)	11.501	
Product Length (ft.)	0.377	
Product Length (m.)	0.115	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Transmitter: 1x Green (Connection); 1x Orange (Signal) Receiver: 1x Green (Connection); 1x Orange (Activity)	
CHARGING		
USB Power Delivery (PD) Charging Support	No	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Receiver Unit Dimensions (hwd / cm.)	11.501 x 6.240 x 2.700	
Receiver Unit Dimensions (hwd / in.)	4.528 x 2.457 x 1.063	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

[
Receiver Unit Weight (lbs.)	1	
Transmitter Unit Dimensions (hwd / cm.)	11.501 x 6.240 x 2.700	
Transmitter Unit Dimensions (hwd / in.)	4.528 x 2.457 x 1.063	
Transmitter Unit Weight (lbs.)	1	
Unit Packaging Type	Box	
Unit Weight (kg)	0.45	
Unit Weight (lbs.)	1	
ENVIRONMENTAL		
Operating Temperature Range	32 - 104 °F (0 - 40 °C)	
Storage Temperature Range	5 - 122 °F (-15 - 50 °C)	
Operating Humidity Range	0 - 85% RH, NON-CONDENSING	
Storage Humidity Range	0 - 85% RH, NON-CONDENSING	
ESD Protection	15KV	
COMMUNICATIONS		
Signal Range (ft.)	150	
Signal Range (m)	46	
CONNECTIONS		
Ports	4	
Side A - Connector 1	USB B (FEMALE)	
Side A - Connector 2	RJ45 (FEMALE)	
Side B - Connector 1	USB A (FEMALE)	
Side B - Connector 2	RJ45 (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
Recommended Category Cable	Cat5e/Cat6	
Technology	USB; USB 2.0 (High Speed)	
Transmission Distance	45m (150 ft)	
STANDARDS & COMPLIANCE		
Certifications	RoHS, REACH, CE, FCC, NOM, ISO9001	
WARRANTY		



Product Warranty Period (Worldwide)

1-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies