

#### **SPOS G86-61411**



Models may vary from the image shown

# Programmable POS Keyboard With Touchpad, Mouse Keys, and Magnetic Card Reader

The fully programmable keyboard with extended alphanumeric layout and replaceable keys is for POS and Commercial applications.

### **Key Benefits**

- Full QWERTY key layout in a compact 14' form factor, maximal space efficiency with uncompromised alphanumeric data entry
- IP 54 spill and dust resistant key field
- Plug and Play for all common POS features
- Accessory Kit Available to Reconfigure Key Layout
- Touchpad with 2 mouse buttons
- 3-Track Magnetic Stripe Reader
- Integrated memory

### **Magnetic Stripe Reader**

- Freely-programmable header and terminator per magnetic card track
- Dual insertion and bidirectional swipe of Magnetic Stripe Card
- Audible and visual indication of MSR Good Read
- Flexible parsing and configuration of magnetic stripe data including start/stop sentinels

#### **Technical Data:**

#### Layout (country or language):

(possible country/layout versions, others available on request) US English with EURO symbol

#### **Housing Color:**

Product dependant, see table "Models"

#### **Key Color:**

Product dependant, see table "Models"

### Weight (product):

approx. 1400 g / 3.09 lb

#### Total Weight (with packaging):

approx. 1600 g / approx. 3.53 lb

#### Cable Length:

approx. 1.85 m / approx. 6.07 ft

#### **Storage Temperature:**

-20°C to 60°C / -4° F to 140° F

#### **Operating Temperature:**

0°C to 50°C / 32° F to 122° F

#### **Current Consumption:**

max. 100 mA

#### Interface:

• USB

#### **Product Approvals:**

• cURus



C-TickVCCI



• CE

 $\epsilon$ 

• FCC

F©

• BSMI

 $\Theta$ 

• RCM

#### **System Requirements:**

USB plug and USB supporting operating system

#### **Box Contents:**

- SPOS G86-61411
- Printed instructions
- Keycap puller
- 2 Plug-in feet

#### **Dimensions (product):**

approx. 360 x 198 x 38 mm / approx. 14.17 x 7.80 x 1.50 in

#### **Packaging Dimensions:**

approx. 415 x 260 x 50 mm / approx. 16.33 x 10.24 x 1.97 in

#### Reliability:

- Standard keys (1x1): >25 mill. operations
- Touchpad keys: > 300,000 operations

#### Touchpad:

Resolution: 1000 dpiNumber of Keys: 2



#### **Keyboard:**

Key Technology: ATKProtection Class: IP54

• Service life, standard key: > 25 million key operations

• Inscription Technology: Laser

• Number of Keys: 123

Number of Programmable Keys: 123Number of Relegendable Keys: 60

#### Magnetic Stripe Reader:

• Magnetic Card Tracks: Track 1, Track 2, Track 3

Magnetic Card Standards: ISO 7811/-12, JIS 1/2, AAMVA
Magnetic Card Reading Speed: 6.3 - 250 cm/s (75 - 210 bpi)

Magnetic Card Reading Cycles: > 1 million reading cycles

• Magnetic Card Swipe Direction: both directions

#### **Packaging Unit:**

• Number of products in the master package: 22

• Number of master packages per pallet: 8

#### Warranty:

3 years

Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided.



## Models:

(possible country/layout versions, others available on request)

I		<b>Product Name</b>	Order Number	Housing Color	Key Color
ſ	1	SPOS G86-61411	G86-61411EUADAA	black	black
	2	SPOS G86-61411	G86-61411EUAEAA	light grey	light grey