



Let's Talk R400 Camera Specs

Ideal for entryways and parking lots



Camera starts at \$1299

Rhombus 10-year Warranty included

- 8MP image sensor
3840 x 2160 resolution
- 4K, Ultra-HD video
- 102° - 44° Diagonal FoV
94° - 39° Horizontal FoV
62° - 22° Vertical FoV
- 3.6mm - 11mm motorized varifocal lens
- Up to 60 days of on-camera storage
- IP66 weather resistance
IK10 impact resistance
- Optional unlimited cloud storage available

About the R400

Constructed with a fully weatherproof and vandal-resistant exterior shell, the R400 is a powerful enterprise security camera, delivering sharp 4K video and amazing performance. With a varifocal lens and 3X motorized zoom with autofocus, users can manually adjust camera settings for optimal video from far or close distances.

Paired with the Enterprise Console License, the R400 camera provides proactive security powered by Artificial Intelligence and Computer Vision.

Camera Specs

- Night Vision:** Infrared illuminators (130ft in low light)
- Aperture:** F/1.5
- Pan / Tilt / Zoom:** 3X optical zoom + up to 3X digital PTZ
- Ethernet:** 10 / 100Mbps, MDI/MDI-X Auto Sensing
- Power-over-Ethernet:** Standard 802.3af for one-cable installation
- Power Consumption:** Max 11.7 watts
- Onboard Storage Included:** 512GB, 1TB
- Dimensions:** 134mm (5.27in) x 118mm (4.64in)
- Operating Temperature:** -55° to 55° C (-67° to 131° F)
- Operating Humidity:** <90% RH
- In the Box:** Torx key, mounting screws, anchors
- Baseline Steady State:** 10 - 30 Kbps per camera
- HD WAN Live Streaming:** 530 - 720 Kbps per camera
- CE, FCC, NDAA, TAA Compliant**