


EP2410-B1 - 24" DISPLAY, 1920 X 1080 RESOLUTION, 250 CD/M2 BRIGHTNESS, 16/7

## Key Features


- FRAMELESS DISPLAY DESIGN
- POWERFUL OCTA-CORE SOC
- OPTIONAL AUTOMATIC HAND SANITIZING DISPENSER
- OPTIONAL CONTENT MANAGEMENT SOFTWARE
- LOADED WITH CONNECTIVITY



24  
DISPLAY



IPS  
PANEL



Up to 1920x1080 non-interlaced  
RESOLUTION

## Product Description

The ViewSonic® EP2410-B1 is a Health Flex Hand Sanitizing Station bundled with a 24" display, media player, and hand sanitizer dispenser holder. With a sleek and slim design, and optional touchless dispenser for hands-free sanitizing, the EP2410-B1 makes displaying health notices, business information, and promotions easier than ever. Featuring Full HD 1080p resolution, 178°/178° wide-angle viewing, 250-nit brightness, 1,000:1 contrast ratio, and dual stereo speakers, the EP2410-B1 delivers customized multimedia messaging with vivid clarity. Photo and video files can be played back using the external Octa-core media player and 16GB of internal memory, or you can add your own media player using the convenient media player cradle inside the lockable security door. Highlight your commitment to your customers' health with the ViewSonic Health Flex Hand Sanitizing Station bundle.

## Specifications

	More Information
Screen Size	24
Viewable Area (in.)	23.8

<b>Display Resolution</b>	1920 x 1080
<b>Light Source</b>	LED
<b>Static Contrast Ratio</b>	1,000:1
<b>Dynamic Contrast Ratio</b>	20,000,000:1
<b>Brightness</b>	250 cd/m2
<b>Viewing Angles</b>	178° horizontal, 178° vertical
<b>Backlight Life (Hours)</b>	30,000
<b>Response Time (Typical GTG)</b>	14ms
<b>Response Time (GTG w/OD)</b>	7ms
<b>Panel Surface</b>	Anti-glare, hard-coating (3H)
<b>Panel Type</b>	IPS
<b>Operation Rating</b>	16/7
<b>PC Resolution (max)</b>	Up to 1920x1080 non-interlaced
<b>Mac® Resolution (max)</b>	Up to 1920x1080
<b>3.5mm Audio Out</b>	1
<b>DisplayPort</b>	1
<b>DisplayPort Out</b>	1
<b>USB 3.0 Type B</b>	1
<b>HDMI 1.4 In</b>	2
<b>USB 3.0 Type A</b>	4
<b>Media Player Type</b>	Yes
<b>Voltage</b>	AC 100-240V (universal), 50-60Hz
<b>Consumption (typical)</b>	22W
<b>Eco Mode (optimized)</b>	19W
<b>Eco Mode (Conserve)</b>	17W
<b>Temperature</b>	32-104° F (0 - 40° C)
<b>Humidity (non-condensing)</b>	20-90%
<b>Frequency Horizontal</b>	15~90kHz
<b>Frequency Vertical</b>	24~75Hz
<b>VESA Compatible</b>	100 x 100 mm
<b>Gross (lbs)</b>	67.1
<b>Net (lbs)</b>	54.5
<b>Gross (kg)</b>	30.4
<b>Net (kg)</b>	24.7
<b>Packaging (in.)</b>	65.0 x 20.0 x 20.0
<b>Physical (in.)</b>	60.0 x 16.0 x 16.0

<b>Packaging (mm)</b>	1651.0 x 508.0 x 508.0
<b>Physical (mm)</b>	1524.0 x 406.4 x 406.4
<b>Regulations</b>	UL, FCC-B, EPEAT, ENERGY STAR
<b>PACKAGE CONTENTS</b>	STND-059 x 1, VP2468 x 1, NMP520-W x 1
<b>Recycle/Disposal</b>	Please dispose of in accordance with local, state or federal laws.
<b>Warranty</b>	One-year limited warranty on parts and labor

## Contact Sales

[ViewSonic.com](http://ViewSonic.com)

888.881.8781

email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)