

# ThinkStation P620 30E00049US

**Product**

ThinkStation P620

**Region**

NA

**Country/Region**

USA

**Machine Type**

30E0

**TopSeller**

TopSeller

**Processor**

AMD Ryzen Threadripper PRO 3955WX (16C / 32T, 3.9 / 4.3GHz, 8MB L2 / 64MB L3)

**Discrete Graphics**

NVIDIA Quadro P2200 5GB

**Chipset**

AMD WRX80

**Memory**

2x 16GB RDIMM DDR4-3200 ECC

**HDD Controller**

Integrated SATA controller

**M.2 SSD RAID Controller**

Integrated NVMe controller

**Internal Disk Drive**

None

**M.2 SSD Drive**

1x 512GB SSD M.2 PCIe 4.0 NVMe Opal (available later)

**Optical**

9.0mm DVD±RW

**Media Reader**

15-in-1 Card Reader

**Onboard Ethernet**

1x 10GbE RJ-45

**Additional Ethernet**

None

**WLAN + Bluetooth**

None

**Optional Rear Ports**

None

**Chassis Intrusion Switch**

Chassis Intrusion Switch

**Cover Lock**

Lock Kit with Common Key

**Keyboard**

USB Traditional Keyboard, Black, English

**Mouse**

USB Calliope Mouse

**Power Supply**

1000W Platinum Fixed

**Diagnostic**

Front 4-Digit Diagnostic LED

**System Management**

AMD PRO

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

None

**Base Warranty**

3-year, Onsite

**Bundled Service**

3Y Premier Support Upgrade from 3Y Onsite (5WS0U26649)

**EAN / UPC / JAN**

195348228930

**End of Support**

2028-10-04

**Announce Date**

2020-09-04

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

**L** [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# ThinkStation P620 Platform Specifications

Product Specifications Reference (PSREF)

|                                                 |                                                                                                                                                                                   |                                        |              |                     |              |         |              |
|-------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|--------------|---------------------|--------------|---------|--------------|
| Form factor                                     | 33L Tower                                                                                                                                                                         |                                        |              |                     |              |         |              |
| Dimensions                                      | 165mm/6.5" W x 460mm/18.1" D x 446mm/17.6" H (with feet)                                                                                                                          |                                        |              |                     |              |         |              |
| Weight                                          | Maximum configuration: 52.91 lb (24kg)                                                                                                                                            |                                        |              |                     |              |         |              |
| Processor Support                               | Processor                                                                                                                                                                         | # of Cores                             | # of Threads | Base Frequency      | Cache        | TDP     | Memory Types |
|                                                 | AMD Ryzen Threadripper PRO 3995WX                                                                                                                                                 | 64                                     | 128          | 2.7GHz              | 256MB L3     | 280W    | DDR4-3200    |
|                                                 | AMD Ryzen Threadripper PRO 3975WX                                                                                                                                                 | 32                                     | 64           | 3.5GHz              | 128MB L3     | 280W    | DDR4-3200    |
|                                                 | AMD Ryzen Threadripper PRO 3955WX                                                                                                                                                 | 16                                     | 32           | 3.9GHz              | 64MB L3      | 280W    | DDR4-3200    |
|                                                 | AMD Ryzen Threadripper PRO 3945WX                                                                                                                                                 | 12                                     | 24           | 4.0GHz              | 64MB L3      | 280W    | DDR4-3200    |
| Processor Sockets                               | 1x Socket sWRX4                                                                                                                                                                   |                                        |              |                     |              |         |              |
| Chipset                                         | AMD WRX80                                                                                                                                                                         |                                        |              |                     |              |         |              |
| Memory Sockets                                  | 8 DIMM sockets with 8 channels                                                                                                                                                    |                                        |              |                     |              |         |              |
| Memory Types                                    | DDR4-3200 RDIMM ECC, 8GB / 16GB / 32GB / 64GB available                                                                                                                           |                                        |              |                     |              |         |              |
| Memory Capacity                                 | 512GB with 8 x 64GB DDR4-3200 RDIMMs                                                                                                                                              |                                        |              |                     |              |         |              |
| Memory Protection                               | ECC                                                                                                                                                                               |                                        |              |                     |              |         |              |
| Expansion slots                                 | Slot 1 (CPU)                                                                                                                                                                      | PCIe 4.0 x16, full height, full length |              |                     |              |         |              |
|                                                 | Slot 2 (CPU)                                                                                                                                                                      | PCIe 4.0 x8, full height, full length  |              |                     |              |         |              |
|                                                 | Slot 3 (CPU)                                                                                                                                                                      | PCIe 4.0 x16, full height, full length |              |                     |              |         |              |
|                                                 | Slot 4 (CPU)                                                                                                                                                                      | PCIe 4.0 x16, full height, full length |              |                     |              |         |              |
|                                                 | Slot 5 (CPU)                                                                                                                                                                      | PCIe 4.0 x16, full height, full length |              |                     |              |         |              |
|                                                 | Slot 6 (IOH)                                                                                                                                                                      | PCIe 4.0 x8, full height, full length  |              |                     |              |         |              |
| Discrete Graphics Offering                      | Graphics                                                                                                                                                                          | Memory                                 | Pow-er       | Connector           | SLI / NVlink | Max Qty |              |
|                                                 | Quadro P620                                                                                                                                                                       | 2GB GDDR5                              | 40W          | 4xminiDP            | -            | 4       |              |
|                                                 | Quadro P1000                                                                                                                                                                      | 4GB GDDR5                              | 50W          | 4xminiDP            | -            | 4       |              |
|                                                 | Quadro P2200                                                                                                                                                                      | 5GB GDDR5                              | 75W          | 4xDP                | -            | 4       |              |
|                                                 | Quadro RTX 4000                                                                                                                                                                   | 8GB GDDR6                              | 160W         | 3xDP, 1xVirtualLink | -            | 4       |              |
|                                                 | Quadro RTX 5000                                                                                                                                                                   | 16GB GDDR6                             | 265W         | 4xDP, 1xVirtualLink | NVLink       | 2       |              |
|                                                 | Quadro RTX 6000                                                                                                                                                                   | 24GB GDDR6                             | 295W         | 4xDP, 1xVirtualLink | NVLink       | 2       |              |
|                                                 | Quadro RTX 8000                                                                                                                                                                   | 48GB GDDR6                             | 295W         | 4xDP, 1xVirtualLink | NVLink       | 2       |              |
|                                                 | Quadro GV100                                                                                                                                                                      | 32GB HBM2                              | 250W         | 4xDP                | NVLink       | 2       |              |
| Storage Controller                              | Storage Controller                                                                                                                                                                | Type                                   | Interface    | RAID                | Cache        |         |              |
|                                                 | Integrated SATA controller                                                                                                                                                        | Std                                    | SATA 6Gb/s   | 0/1/10/5            | -            |         |              |
|                                                 | Integrated NVMe controller                                                                                                                                                        | Std                                    | PCIe NVMe    | 0/1/10/5            | -            |         |              |
| Storage Type                                    | Disk Type                                                                                                                                                                         | Interface                              | RPM          | Offering            |              |         |              |
|                                                 | 3.5" SATA HDD                                                                                                                                                                     | SATA 6Gb/s                             | 7.2K         | 1TB/2TB/4TB         |              |         |              |
|                                                 | M.2 PCIe SSD                                                                                                                                                                      | PCIe 3.0 NVMe                          | -            | 256GB/512GB/1TB/2TB |              |         |              |
|                                                 | M.2 PCIe SSD                                                                                                                                                                      | PCIe 4.0 NVMe*                         | -            | 256GB/512GB/1TB     |              |         |              |
| * M.2 PCIe 4.0 SSD is available later this year |                                                                                                                                                                                   |                                        |              |                     |              |         |              |
| Storage Support                                 | Up to 5x 3.5" SATA HDD:<br>• 4x 3.5" HDD bay<br>• 1x Flex Bay ( Front Access Storage Enclosure or 5.25" Slim ODD and HDD cage)                                                    |                                        |              |                     |              |         |              |
|                                                 | Up to 11x M.2 SSD:<br>• 2 via onboard M.2<br>• 8 via two quad M.2 to PCIe adapter (only supports PCIe 3.0 SSD)<br>• 1 via Single M.2 to PCIe adapter (only supports PCIe 3.0 SSD) |                                        |              |                     |              |         |              |
| Power supply                                    | One fixed 1000W, autosensing, 92%, 80 PLUS Platinum qualified                                                                                                                     |                                        |              |                     |              |         |              |
| Optical                                         | Optional one slim optical, DVD or DVD±RW                                                                                                                                          |                                        |              |                     |              |         |              |
| Media reader                                    | Optional UHS-II 15-in-1 USB 3.2 Gen 1 reader on flex module                                                                                                                       |                                        |              |                     |              |         |              |
| Network interfaces                              | Integrated one 10GbE ethernet (Marvell AQtion AQN-107). Optional PCIe ethernet or wireless adapters are available                                                                 |                                        |              |                     |              |         |              |
| WLAN + Bluetooth                                | Optional Intel Wireless-AC 9260, 2x2, 2.4GHz/5GHz, 802.11ac, Bluetooth 5.1                                                                                                        |                                        |              |                     |              |         |              |

|                              |                                                                                                                                                               |                                               |
|------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Security features            | Power-on and admin password. Trusted Platform Module, TCG 2.0 compliant. Chassis intrusion switch. Optional access panel lock, Kensington lock                |                                               |
| System Mgmt                  | AMD Pro Manageability                                                                                                                                         |                                               |
| Diagnostic                   | Front panel warning LED. Front 4-digit diagnostic. ThinkStation Diagnostics for Windows. Photo-audio transfer with Lenovo PC Diagnostics for Android and iOS. |                                               |
| Base warranty                | Most models comes with 3-year limited onsite service with 9x5/NBD                                                                                             |                                               |
| HD Audio                     | Realtek ALC4050H codec                                                                                                                                        |                                               |
| Front ports                  | 2x USB-A 3.2 Gen 2 (includes one 11W charging), 2x USB-C 3.2 Gen 2 (15W), 1x combo audio / microphone jack (3.5mm)                                            |                                               |
| Rear ports                   | 2x USB-A 2.0, 4x USB-A 3.2 Gen 2, 1x 10GbE RJ-45, 3x analog audio ports (line-in, line-out, mic-in), 2x PS/2                                                  |                                               |
| Optional ports               | Optional one COM port                                                                                                                                         |                                               |
| Environmental specification  | Temperature - operating                                                                                                                                       | 50 °F to 95 °F (10 °C to 35 °C)               |
|                              | Temperature - storage (no package)                                                                                                                            | 14 °F to 140 °F (-10 °C to 60 °C)             |
|                              | Temperature - storage (with package)                                                                                                                          | -40 °F to 140 °F (-40 °C to 60 °C)            |
|                              | Altitude - operating                                                                                                                                          | (Unpressurized): -50ft-10000ft (-15.2m-3048m) |
|                              | Humidity - operating                                                                                                                                          | 10%~80%, non-condensing                       |
|                              | Humidity - storage (with package)                                                                                                                             | 10%~90%, non-condensing                       |
| Environmental Certifications | RoHS-compliant. GREENGUARD. EPEAT Silver rating. ENERGY STAR 8.0 qualified                                                                                    |                                               |
| ISV certifications           | Please visit <a href="http://www.thinkworkstations.com/isv-certifications/">www.thinkworkstations.com/isv-certifications/</a>                                 |                                               |

Note: Depending on many factors, actual data transfer speed mentioned on this page may be lower than theoretical speed.

Lenovo

# ThinkStation P620

