# **INDUSTRIAL VACUUMS**

## QUICKKLEENTM COMMERCIAL **UPRIGHT VACUUM**

• 50 ft. Power cord

#### Amperage: 7 Air Flow: 145 CFM

#### IH548

- Ideal choice for Supermarkets and Building Cleaning contractors
- Clear dust cup allows the operator to see when it needs to be emptied
- 6 Position carpet height
- Wide clear furniture guard will not leave color marks on baseboards

#### JH549 & JH550

- Ideal for large areas of carpet cleaning
- Bag Release System with metal bag clip makes emptying easy and saves money on bags
- Replaceable Bristle Strips for continuous, deep cleaning every time



La Licettoiax			
Model	Cleaning Path	Capacity	Price
No.	Width"		/Each
JH548	12	1.9	
JH549	12	18	
INEEU	16	10	

IH548

JH550

### QUIETCLEANTM COMMERCIAL **UPRIGHT VACUUM**

· Designed for daytime cleaning with innovative sound dampening technology

- LEED Compliant and CRI Green Label certified
- 40 ft. Power cord
- · Amperage: 10
- · Air Flow: 135 CFM

#### JH553

- · Bagged cleaner combines a clean-air system with the ultimate in filtration, sealed HEPA
- · Allergen disposable dust bag

#### JH552

- Captures dust and allergens with its clean-air system and incredible filtration
- Sealed HEPA filter and an extra-large dust cup



### Sanitaire

☑ Electrolux

Model No.	Cleaning Path Width"	Capacity Qts.	Price /Each
JH553	13	4.5	
JH552	15	3.5	

# EON QUIETCLEAN™ COMMERCIAL **UPRIGHT VACUUM**

Sanitaire

☑ Electrolux

JH549

- · Engineered with professional-grade components to meet the demands of commercial cleaning
- No-tool assembly, no-tool brush roll change, quick-change cord and bag full indicator lights provide easy maintenance
- Provides 24/7 cleaning at 70 dBA or less which is equivalent to the noise level of a human conversation
- Ideal for bare floors to carpet with a four-setting height adjustment
- 40 ft. Power cord
- Cleaning Path Width: 12"
- Amperage: 10
- Air Flow: 105 CFM Capacity: 3 Quarts
- Model No. JH554

Price/Each \$



### COMMERCIAL UPRIGHT VACUUM

- · Standard filtration, shake out bag system
- Produces an effective wave action that vibrates deeply embedded dirt
- Replaceable Bristle Strips for continuous, deep cleaning every time
- 6 Position carpet height
- 50 ft. Power cord
- Cleaning Path Width: 12"
- Amperage: 7
  Air Flow: 145 CFM
- · Capacity: 18 Quarts

Model No. JH547 Price/Each \$





### GENESISTM COMMERCIAL **UPRIGHT VACUUM**

- · Designed for daytime cleaning with innovative sound dampening technology
- Captures dust and allergens with its clean-air system and incredible filtration
- LEED Compliant and CRI Green Label certified Sealed HEPA filter and an extra-large dust cup
- 40 ft Power cord
- Cleaning Path Width: 13"
- Amperage: 10

Price/Each \$

Air Flow: 135 CFM

Capacity: 3.5 Quarts Model No. IH551





