

# ThinkVision T23i-10 61ABMAR1US

**Product**

ThinkVision T23i-10

**Machine Type**

61AB

**Region**

NA

**Display Size**

23"

**View Area**

517.2x302.8 mm

**Panel**

In-Plane Switching

**Aspect Ratio**

16:9

**Resolution**

1920x1080

**Pixel Pitch**

0.2652x0.2652 mm

**Dot / Pixel Per Inch**

95.8 dpi

**View Angle (H / V)**

178 / 178

**Pixel Response Time**

6 ms

**Refresh Rate**

60 Hz

**Brightness**

250 nits

**Contrast Ratio**

1000:1

**Color Gamut**

72% NTSC

**Multiple Input**

HDMI, DP, VGA

**USB Port**

USB 3.0x5

**Camera**

None

**Speaker**

None

**Power Consumption (Typical / Maximum)**

16W / 45W

**Power Adapter**

Integrated

**Stand**

Tilt, Swivel, Pivot, Height Adjust Stand

**Color**

Black

**Side Bezel Width**

2 mm

**Dimensions with Stand (HxWxD)**

337.7x522.2x264.2 mm

**Weight (Including Stand)**

10.85lb / 4.92kg

**Monitor Cable**

DP, VGA

**ENERGY STAR**

Yes

**TCO**

TCO 7.0

**EPEAT**

Silver

**Low Blue Light / Eye Comfort / Eyesafe Display**

Eye Comfort

**Base Warranty**

3-year

**Operating System**

Support Windows 7, Windows 10

**Presets / User Settings**

HDMI:18 / DP:18

**On Screen Display**

OSD, 8 Languages

**Sync Technology**

None

**CPU / Platform**

None / None

**Display Ram / Storage / Card Slot**

None / None / None

**Wireless / Ethernet / Bluetooth**

None / None / None

**Touch Screen / Digitizer Pen / Battery**

None / None / None

**Announce Date**

2017-05-10

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

**L** [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



# ThinkVision T23i-10 MONITOR



Lenovo

## SPECIFICATIONS

DISPLAY		DIMENSIONS (W x D x H)	
Panel Size	23 Wide	Size Packed (mm)	590 x 187 x 422
Panel Type	IPS	Size Packed (inches)	23.23" x 7.36" x 16.61"
Backlight	WLED	Size Unpacked with Stand (mm)	522.2 x 264.2 x 337.7
Resolution (H x V)	1920 x 1080	Size Unpacked with Stand (inches)	20.56" x 10.4" x 13.3"
Aspect Ratio	16:9	Size Monitor Head Only (mm)	522.2 x 42.7 x 317.6
Anti-Glare	Yes	Size Monitor Head Only (inches)	20.56" x 1.68" x 12.5"
Borderless Screen	Yes	Stand Base Footprint Area (mm)	218.7 x 218.7
Screen Dimensions (W x H) (mm)	517.2 x 302.8	Stand Base Footprint Area (inches)	8.61" x 8.61"
Screen Dimensions (W x H) (inches)	20.36" x 11.92"	Weight Packed	Starting at 16.36 lbs (7.42 kg)
Maximum Brightness (Typical)	250 cd/m <sup>2</sup>	Weight Unpacked	Starting at 10.85 lbs (4.92 kg)
Viewing Angle (H/V at CR 10:1)	178°/178°	Weight Monitor Head Only	Starting at 6.94 lbs (3.15 kg)
Contrast Ratio (Typical)	1000:1		
Dynamic Contrast Ratio	3M:1		
Pixel Pitch (mm)	0.265 x 0.265		
Color Gamut NTSC (CIE 1931)	72%		
Color Support (Typical)	16.7 Million		
Response Time	4/6/14 ms		
CONNECTIVITY		POWER CONSUMPTION	
Video Input Signals	VGA + HDMI 1.4 + DisplayPort 1.2	Typical	16 W
Video Cables Supplied (Length)	1.8 m	Maximum	45 W
Audio	Audio-Out	Sleep-Mode	<0.5 W
OSD Languages	English, French, German, Spanish, Italian, Japanese, Simplified Chinese, Russian	Switch Off-Mode	<0.5 W
		Power Supply	Internal
		Power Voltage	100 VAC - 240 VAC
MECHANICAL		COMPLIANCE	
Tilt Angle (Front / Back)	-5° / 30°	Arsenic-Free Glass	Yes
Swivel Angle (Left / Right)	+/-45°	PVC-Free	Yes; Without Cable
Lift (mm / inches)	110 / 4.33"	Mercury-Free	Yes
Pivot	-90° / 90°	EPEAT	Silver
Cable Management	Yes	ENERGY STAR Rating	8.0
Kensington Lock	Yes	TCO	7.0
VESA Mounting	Yes (100 mm)	TCO Edge	2.0
Bezel Color	Raven Black	RoHS (EU 2002/95/EC)	Yes
Bezel Width		China Energy Efficiency Standard	Tier 2
Top (mm / inches)	2 / 0.08"	Windows Certification	Windows 7 / Windows 10
Bottom (mm / inches)	23.7 / 0.93"		
Sides (mm / inches)	2 / 0.08"		



WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit [www.lenovo.com](http://www.lenovo.com). Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage and ThinkVision. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit [www.lenovo.com/lenovo/us/en/safecomp/](http://www.lenovo.com/lenovo/us/en/safecomp/) periodically for the latest information on safe and effective computing. ©2020 Lenovo. All rights reserved.

# ThinkVision T23i-10

