

CTL® Chromebook NL81 Series

Ideal for Educators, Enterprise, and High-Performance Users

ctl.re/ctl-nl81series



Touch and Non-Touch Versions of Our Biggest Panel Yet

- 14" FHD 1080p anti-glare panel on the NL81 and 14" FHD 1080p 10-point multi-touch panel on NL81T model (touchscreen model is not anti-glare).
- NL81 has a powerful Intel® Gemini Lake R N4020 Processor for higher processing speeds and file storage. The NL81T packs a Intel® Pentium N5030 Processor for a step up in performance.
- IP rated drop resistant design with non-slip texture, reinforced ports, hinges and power plug. Water resistant keyboard and anti-peel keys provide added durability.
- HD camera, USB-C quick charge and HDMI port for additional connectivity.
- MU-MIMO supports a constant signal and uninterrupted streaming.
- AUE extends until June 2026.



FEATURES & BENEFITS

Our NL81 model is powered by an Intel® Gemini Lake R N4020 Processor, while the NL81T includes an Intel® Pentium N5030 Processor for higher functionality. Both allow you to quickly toggle from multiple browsers and applications with efficiency for optimal productivity.

Intel® Wireless-AC 9560 is the first wireless solution that provides Gigabit WiFi speeds. When using 160MHz channels, it can deliver up to 1.73Gbps maximum theoretical throughput, nearly 12x faster than baseline 1x1 BGN (150Mbps) WiFi used in today's PCs.

Our largest Chromebook panel measures in at 14" for greater functionality while still remaining portable for remote work. The NL81 model has an anti-glare screen and the NL81T touch model has a 10-point capacitive touch screen for more versatile and intuitive functionality. Both models have FHD for crisper graphics at 1080p.

Equipped with an HD camera, USB and HDMI ports, users are able to connect to external displays, drives and adapters or pair audio devices wirelessly via Bluetooth 5.0.






CTL® Chromebook NL81 Series

Ideal for Educators, Enterprise, and High-Performance Users

ctl.re/ctl-nl81series



	CTL Chromebook NL81 SKU CBUS1400001	CTL Chromebook NL81T SKU CBUS1400002
PERFORMANCE	<p>PROCESSOR Intel® Gemini Lake R N4020 Processor (4M Cache, up to 2.80 GHz)</p> <p>OPERATING SYSTEM Chrome OS</p> <p>MEMORY 4GB LPDDR4</p> <p>GRAPHICS Intel® UMA GLK-R Integrated Graphics</p> <p>CAMERA HD 720P camera with LED indicator</p> <p>STORAGE 32GB eMMC, Optional Google Drive storage</p> <p>AUDIO Single digital microphone, and audio combo jack</p> <p>BATTERY Up to 12 hours of battery life, serviceable battery - can be replaced by school IT</p>	<p>PROCESSOR Intel® Pentium N5030 Processor (4M Cache, up to 2.80 GHz)</p> <p>OPERATING SYSTEM Chrome OS</p> <p>MEMORY 8GB LPDDR4</p> <p>GRAPHICS Intel® UMA GLK-R Integrated Graphics</p> <p>CAMERA HD 720P camera with LED indicator</p> <p>STORAGE 64GB eMMC, Optional Google Drive storage</p> <p>AUDIO Dual microphone and audio combo jack</p> <p>BATTERY Up to 12 hours of battery life, serviceable battery - can be replaced by school IT</p>
DESIGN	<p>DISPLAY Anti-glare 16:9 14" 1920 X 1080p FHD LED</p> <p>DIMENSION 12.82" x 8.6" x 0.7"</p> <p>WEIGHT 2.8 lbs.</p>	<p>DISPLAY 16:9 14" 1920 X 1080p FHD LED 10-point capacitive touch</p> <p>DIMENSION 12.82" x 8.6" x 0.7"</p> <p>WEIGHT 2.8 lbs.</p>
CONNECTIVITY	<p>INTERNET CONNECTION</p> <ul style="list-style-type: none"> • WL/BT 802.11ABGN/AC 9560.NG.WG.NV • Intel® 9560 Wireless • MU-MIMO support <p>PORTS</p> <ul style="list-style-type: none"> • 2x USB 3.0 • 1x USB-C with PD function • 1x Audio Combo Jack 	<p>INTERNET CONNECTION</p> <ul style="list-style-type: none"> • WL/BT 802.11ABGN/AC 9560.NG.WG.NV • Intel® 9560 Wireless • MU-MIMO support <p>PORTS</p> <ul style="list-style-type: none"> • 1x HDMI • 1x USB 3.0 • 1x USB-C with PD function • 1x Audio Combo Jack



UPGRADES

- Full Color Logo Painting
- Chrome Management Licenses
- White Glove Service
- Bulk Pack Shipping
- "Buy and Try" discounted prices
- Store and Charge Carts
- Educational apps

WARRANTIES

- CTL 1 Year Parts/Labor Warranty (included with NL81 NL81T)
- CTL 1 Year AD Depot
- Available warranty upgrades include:
 - 1, 2, 3 and 4-year warranty
 - 1, 2, 3 and 4-year 2-way shipping
 - 1, 2, 3 and 4-year accidental damage
 - 3-year premium battery support
 - 3 and 4-year Complete Suite