

MLEBDD162

Ionic | Electric HAT - 2 Leg Base Only



- 2 leg table base for use with MLxxxxHAT tops
- Controller with digital read-out and three memory programmable positions
- Quiet hex rod driven single motor.
- Cannot be converted to a 3 legged table base
- Silver finish only
- Range of adjustability without top 26.8" to 44.5"H
- Shipped easy to assemble in 1 carton

Link:

Video | [How to Assemble Your Ionic Height Adjustable Table](#) (3:42)

Specifications

Dimensions: 48"W x 21.5"D x 26.8"-44.5"H


Weight: 75 lbs / 34.02 kg

Volume: 2.4 ft³ / 0.06 m³

Environmental Certificates



[Ionic](#)



Instructional 3:42

How to Assemble Your Ionic Height Adjustable Table