

# Pro EX9240 3LCD Full HD 1080p Wireless Projector with Miracast<sup>®</sup>



## Own the Room.

**Amazing brightness** — 4,000 lumens of color and white brightness<sup>1</sup> ideal for displaying large-group presentations, spreadsheets and videos, even in well-lit rooms

**Stunning image quality** — amazing Full HD 1080p resolution delivers crisp text and images; perfect for displaying professional-quality presentations, video and more

**True 3-Chip 3LCD technology** — displays 100% of the RGB color signal for every frame, providing outstanding color accuracy while maintaining excellent color brightness, without any distracting “rainbowing” or “color brightness” issues seen with other projection technologies

**Wireless connectivity** — including screen mirroring with Miracast, plus two HDMI<sup>®</sup> ports, so you can easily video conference and connect streaming devices, including Fire TV, Apple TV<sup>®</sup>, Roku and Chromecast<sup>™2</sup>

**Get up and running in no time** — with easy image adjustments and convenient control like 1-1.6x optical zoom, horizontal slider and auto vertical correction

**Incredible sound** — built-in 16 W speaker for astounding audiovisual experience and incredible sound quality right out of the box

**Built-in picture skew sensor** — automatically analyzes the picture and instantly corrects the vertical keystone to help square the image

**Amazing dynamic contrast ratio up to 16,000:1** — provides crisp, rich detail for graphs, images and videos

**Award-winning service and support** — standard 1-year limited warranty, full-unit replacement, along with free technical phone support for the life of the product



**Specifications**

**Projection System** Epson® 3LCD, 3-chip technology  
**Projection Method** Front/rear/ceiling mount  
**Driving Method** Epson Poly-silicon TFT Active Matrix  
**Color Brightness<sup>1</sup>** Color Light Output: 4,000 lumens  
**White Brightness<sup>1</sup>** White Light Output: 4,000 lumens  
**Aspect Ratio** 16:9  
**Output Resolution** 1080p (1920 x 1080)  
**Supports** 16:10, 4:3  
**Lamp Type** 230 W UHE  
**Lamp Life** Normal Mode: Up to 5,500  
 ECO Mode: Up to 12,000 hours  
**Size (Projected)** 30" – 300"  
**Keystone Correction Auto** Vertical: ± 30 degrees  
**Keystone Correction Manual** Horizontal: ± 30 degrees  
**USB Plug 'n Play** Projects audio and video, PC and Mac® compatible  
**Contrast Ratio** Up to 16,000:1  
**Color Reproduction** Up to 1.07 billion colors

**Projection Lens**

**Type** Optical zoom/Manual focus  
**F-Number** 1.51 – 1.99  
**Focal Length** 18.2 mm – 29.2 mm  
**Zoom Ratio** Manual zoom 1.0 – 1.6  
**Throw Ratio Range** 1.32 – 2.14

**Other**

**Display Performance** NTSC: 1080p, HC, 2D, 3D  
**Input Signal**  
 HDMI: TMDS  
 Video Compatibility: 2D: WXGA60 Hz, WXGA, SXGA, XGA, SVGA, VGA 3D: 720p 50/60 Hz, 1080i 50/60 Hz, 1080p 50/60/24 Hz  
**Computer Compatibility** PC, Mac  
**Speaker** 16 w mono  
**Media Format** 16:9  
**Operating Temperature** 41 ° to 104 °F (5 ° to 40 °C)  
**Power Supply Voltage** 100 - 240 V AC +/- 10%, 50/60 Hz  
**Power Consumption**  
 Normal Mode: 345 W  
 ECO Mode: 235 W (lamp on)  
 Energy Saving 0.3 W  
**Fan Noise**  
 Normal Mode: 37 dB  
 Quiet Mode: 28 dB

**Interfaces**

2x HDMI  
 Computer/component video: 1x D-dub 15-pin  
 Composit video: 1x RCA (Yellow)  
 Audio In: 1x RCA (White/Red)  
 1x USB connector Type A: PC-free USB and other  
 1x USB connector Type B: USB Plug 'n Play



**Dimensions (W x D x H)**

**Including Feet** 12.2" x 11.2" x 4.1"  
**Excluding Feet** 12.2" x 11.2" x 3.5"  
**Weight** 6.8 lb

**Remote Control**

**Features** Front and rear directional  
**Operating Angle**  
 Right/left: ± 30 degrees  
 Upper/lower: ± 15 degrees  
**Operating Distance** 19.7 ft (6 m)

**Eco Features**

RoHS compliant  
 Recyclable product<sup>4</sup>  
 Epson America, Inc. is a SmartWay® Transport Partner<sup>5</sup>

**Support**

**Epson Connection<sup>SM</sup>** Pre-sales support: U.S. and Canada 800-463-7766  
 Internet website: www.epson.com  
**Service Programs** 1-year projector limited warranty, Epson Extra Care<sup>SM</sup> Road Service program, PrivateLine<sup>®</sup> dedicated toll-free support and 90-day limited lamp warranty

**What's in the Box**

Pro EX9240 projector, power cable, projector remote control, batteries, Quick Start Guide

**Ordering Information**

Pro EX9240 Projector	V11H978020
Genuine Epson Lamp (ELPLP97)	V13H010L97
Replacement Air Filter (ELPAF54)	V13H134A54
Projector Ceiling Mount (ELPMBPJG)	V12H808001
Soft Carrying Case (ELPKS70)	V12H001K70
Duet™ Screen	ELPSC80
ES1000 Screen	V12H002S4Y
ES3000 Screen	V12H002S3Y

<sup>1</sup> Color brightness (color light output) and white brightness (white light output) will vary depending on usage conditions. Color light output measured in accordance with IDMS 15.4; white light output measured in accordance with ISO 21118. | <sup>2</sup> Requires wireless network connection of 5 Mbps or faster. Some apps require paid subscriptions. | <sup>3</sup> Based on TFCinfo: U.S. Projector Brand Customer Perception and Preference Study, Multimedia Projectors 2019. | <sup>4</sup> For convenient and reasonable recycling options, visit www.epson.com/recycle | <sup>5</sup> SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

Better Products for a Better Future™  
eco.epson.com



Epson America, Inc.  
3131 Katella Ave., Los Alamitos, CA 90720

Epson Canada Limited  
185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com  
www.epson.ca

EPSON is a registered trademark, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future is a trademark of Seiko Epson Corporation. PrivateLine is a registered trademark, Duet is a trademark and Epson Connection and Extra Care are service marks of Epson America, Inc. Apple TV and Mac are trademarks of Apple Inc., registered in the U.S. and other countries. Chromecast is a trademark of Google LLC. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2021 Epson America, Inc. CPD-60122R4 3/21

**Contact:**