

VESA Mounting Plate for Tripp Lite U442-DOCK20-B Docking Station

MODEL NUMBER: U442-DOCK20-VMB



Rugged metal plate securely mounts your U442-DOCK20-B dock to the rear of your monitor to clear desk space.

Features

Mounts Your Tripp Lite Docking Station Behind Your Monitor to Prevent Desktop Clutter

This sturdy mounting plate attaches the Tripp Lite U442-DOCK20-B docking station to the rear of your monitor using the included hardware. Made from durable SECC metal engineered to stand up to everyday commercial application use, the U442-DOCK20-VMB supports 75 x 75 mm and 100 x 100 mm VESA mounting patterns to provide you with a clutter-free workstation. By mounting your USB-C docking station behind your monitor, you can clear up valuable desk space, cut down on disorganized cable clutter and help prevent cables from becoming accidentally disconnected. **Note:** *this VESA mounting plate is designed only for the Tripp Lite U442-DOCK20-B USB-C docking station.*

Highlights

- Attaches behind your monitor to provide a clutter-free workstation
- Supports 75 x 75 mm and 100 x 100 mm VESA mounting patterns for quick installation
- Made from durable SECC metal to withstand the rigors of everyday use
- Provides behind-monitor cable management to avoid annoying cord clutter
- Designed specifically for Tripp Lite U442-DOCK20-B docking station only

Applications

Mount your U442-DOCK20-B USB-C docking station to the back of your monitor to give yourself extra workspace and prevent accidental disconnections

System Requirements

Tripp Lite U442-DOCK20-B USB-C docking station

Package Includes

- U442-DOCK20-VMB mounting plate
- (2) M3 screws
- (2) M4 screws
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332256515
Product Type	VESA Adapter
Accessories Type	VESA Adapter
PHYSICAL	
Color	Black
VESA Pattern (mm)	75x75; 100x100
Material of Construction	SECC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	6.06 x 4.65 x 0.41
Unit Packaging Type	Box
Unit Weight (kg)	0.15
Unit Weight (lbs.)	0.34
ENVIRONMENTAL	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Relative Humidity	20% to 80% RH, Non-Condensing
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>