


1.44kW 120V Single-Phase Basic PDU - 16 NEMA 5-15R Outlets, 5-15P Input, 15 ft. Cord, 48 in. 0U Rack

MODEL NUMBER: PDUV15-48



Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a data center or network closet.

Features

Single-Phase 120V PDU Distributes Network-Grade Power to Multiple Loads

This basic PDU is an ideal no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Recommended for small to mid-sized data centers, computer rooms and network closets, the PDUV15-48 features 16 NEMA 5-15R outlets for connecting equipment. A 15-foot cord with 5-15P input plug connects to your facility's AC power source, generator or protected UPS system to distribute power to connected loads.

Up-to-Date Safety Features Protect Your Vital Equipment

A lighted on/off switch is protected by a transparent plastic cover to help prevent an accidental shutdown that could lead to costly downtime. A 15A circuit breaker protects connected components from dangerous overloads.

Versatile Installation Options Give You Plenty of Choices

The 48-inch 0U PDU mounts vertically in an EIA-standard 19-inch rack using the included toolless mounting buttons or the included mounting clips and hardware. You may also use the clips to secure the PDU to a wall, counter or other flat, secure surface.

Highlights

- Ideal no-frills PDU for telecom, security, audio/video and other network applications
- 16 NEMA 5-15R outlets distribute AC power to connected equipment
- Lighted power switch with protective cover helps prevent accidental shutdowns
- 15 ft. power cord with NEMA 5-15P input connects to compatible AC source
- 48 in. 0U PDU with included mounting hardware installs in rack or under counter

Applications

Deliver network-grade power to high-density equipment in networking, telecom, security, audio/video and sound reinforcement applications

Package Includes

- PDUV15-48 1.44kW 120V Single-Phase Basic PDU
- Rack-mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332255815
PDU Type	Basic
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V



Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A circuit breaker
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted on/off switch with transparent switch cover
PHYSICAL	
Form Factors Supported	Vertical (0U) mounting in rack enclosures
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	51.77 x 3.43 x 2.40
Shipping Weight (kg)	2.01
Unit Dimensions (hwd / cm)	123.1 x 3.81 x 4.2
Unit Dimensions (hwd / in.)	48.47 x 1.5 x 1.64
Unit Weight (kg)	1.70
Unit Weight (lbs.)	3.74
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% Non-condensing
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1: 2007 R10.14 (USA), CAN/CSA-C22.2 No. 60950-1-07+A1:2011+A2:2014 (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>