

PERFORMANCE

Processor

MediaTek Helio A22 (4C, 4x A53 @2.0GHz)

Graphics

Integrated IMG PowerVR GE-class GPU

Chipset

MediaTek SoC Platform

Memory

2GB Soldered LPDDR4x

Storage

32GB eMMC

Expandable Memory

MicroSD card (Up to 128GB)

Card Reader

Single Nano-SIM & MicroSD Card Slot

Storage Support

- 32GB eMMC on systemboard
- MicroSD card, supports FAT32 up to 128GB

Camera

Front 2.0MP / Rear 8.0MP

Microphone

2x, Array

Speakers

Dual side speaker, tuned with Dolby® Atmos®

Sensors

- Ambient light sensor (ALS)
- Accelerometer (G) sensor
- Proximity sensor

Vibrator

Vibrator

Battery

Integrated 5000mAh

Max Battery Life

Standby Time: Over 2 weeks

Online Video Playback Time: 12 hr

Browsing Time: 12 hr

Charging Time

Over 3.5 hours

Power Adapter

5V / 2.0A

DESIGN

Display

8" HD (1280x800) IPS 350nits

Touchscreen

10-point Multi-touch

Case Material

Metal

Water Proofing

IP5X

Dimensions (WxDxH)

121.8 x 8.15 x 199.1 mm (4.79 x 0.32 x 7.84 inches)

Weight

310 g (0.68 lbs)

Case Color

Iron Grey

SOFTWARE

Operating System

Android Pie

Preinstalled Software

- YouTube Music
- Google Play
- Google Play Movies & TV
- Gmail
- Google Assistant
- Google Calendar
- Google Chrome
- Contacts
- Dolby Atmos
- Maps

CONNECTIVITY

WLAN + Bluetooth™

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

4G LTE

Location

GPS + GLONASS + A-GPS

SIM Card

Not configured

VoiceCall

VoiceCall

Standard Ports

- 1x USB-C 2.0
- 1x Nano-SIM + microSD card slot
- 1x headphone / microphone combo jack (3.5mm)
- 1x Pogo pin connector (2-point)

SERVICE

Base Warranty

1-year, Mail-in

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- RoHS

MODEL

TopSeller : No

Announce Date : 2020-08-04

EAN / UPC / JAN : 195235898307



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.


Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference