

Features

- 44X Optical Zoom
- Starlight illumination
- Accurate and fast focusing
- Optical Defog Supported
- Up to 120 dB Optical WDR(Wide Dynamic Range)
- The Fifth-generation infrared technology, more than 250m (820ft) IR distance
- Optical glass window with higher light transmittance
- IR anti-reflection window to increase the infrared transmittance
- Smart IR
- EIS (Electronic Image Stabilization)
- H.265, H.264, MJPEG
- Embedded smart algorithm
- Triple streams
- 1080P@60fps supported
- ONVIF Conformance
- Innovative snow-removing functionality
- More effective heat dissipation system
- Intelligent temperature control technology
- 6 KV surge protection designed for network interface
- Fast Installing structure designed



Specification

Camera	
Sensor	1/2.8", 2megapixel, progressive scan, CMOS
Lens	5 ~ 220 mm (44x optical zoom)
Angle of View (H)	56.7deg. (wide) ~ 3.07deg. (tele)
Shutter	Auto/Manual; shutter time: 1/6 s ~ 1/8000 s
Minimum Illumination	Colour: 0.002 lux (F1.2, 50IRE) 0 lux with IR
Iris	Auto/Manual; F1.2 ~ F3.5

Day/Night	IR-cut filter with auto switch (ICR)
S/N	>52dB
WDR	120dB
Video	
Max. Resolution	1920 x 1080
Video Compression	H.265, H.264,MJPEG
Frame Rate	1080P (1920x1080):Max.60 fps;
Video Streaming	Triple
Defog	Optical Defog & Digital Defog
HLC	Supported
OSD	Up to 8 OSDs
Privacy Mask	Up to 8 areas
Digital Zoom	Supported
Smart	
Behavior Detection	Intrusion, crossing line, motion detection
Exception Detection	Audio detection
Intelligent Identification	Face detection
Statistical Analysis	People counting
Audio	
Audio Compression	G.711
Two-way audio	Supported
Storage	
Edge Storage	Micro SD, up to 128GB
Network	
Protocols	L2TP, IPv4, IGMP, ICMP, ARP, TCP, UDP, DHCP, PPPoE, RTP, RTSP, RTCP, DNS, DDNS, NTP, FTP, UPnP, HTTP, HTTPS, SMTP, SIP, 802.1x
Compatible Integration	ONVIF, API
Pan & Tilt	
Pan Range	360deg. (endless)
Pan Speed	0.1deg./s ~ 240deg./s
	Preset speed: 300deg./s
Tilt Range	15deg. ~ +90deg. (auto reverse)
Tilt Speed	0.1deg. ~ 160deg./s
	Preset speed: 240deg./s
Number of Presets	256
Patrol	Preset patrol, route patrol, recorded patrol

Home Position	Supported
Interface	
Audio I/O	Audio cable
	1 Input: impedance 35 kohm; amplitude 2 V [p-p]
	1 Output: impedance 600 ohm; amplitude 2 V [p-p]
Alarm I/O	2 / 1
Serial Port	1 RS485
Network	1 RJ45 10M/100M Base-TX Ethernet
Video Output	1 BNC, impedance 75 ohm; amplitude 1 V [p-p]
General	
Power	24 V+/-25% AC (Default), 24 V+/-25% DC
	Power consumption:16 ~56W
Dimensions(Dia.xH)	Dia.270mmx496.7mm(Dia.10.6" x 19.6")
Weight	9.69kg(21.4lb)
Working Environment	-45°C~70°C(-49°F ~ 158°F), Humidity
Ingress Protection	IP66
Heat	Built-in Heater and Temperature control system

Dimension

