


Features

- Smart H.265+/H.265/Smart H.264+/H.264
- Max 200Mbps Incoming Bandwidth
- Up to 8MP Resolution for Preview and Playback
- Up to 2ch@4K/8ch@1080P decoding
- HDMI/VGA simultaneous video output
- Support IPC UPnP, 16PoE ports



Specification

System	
Main Processor	Quad-core embedded processor
Operating System	Embedded LINUX
Audio and Video	
IP Camera Input	16 Channel
Two-way Talk	1 Channel Input, 1 Channel Output, RCA
Display	
Interface	1 HDMI, 1 VGA
Resolution	HDMI: 3840×2160, 1920×1080, 1280×1024, 1280×720
	VGA: 1920×1080, 1280×1024, 1280×720
Decoding Capacity	2ch@4K 30fps, 8ch@1080P 30fps
Multi-screen Display	1/4/8/9/16
OSD	Camera title, Time, Camera lock, Motion detection, Recording
Recording	
Compression	Smart H.265+/H.265/Smart H.264+/H.264
Resolution	8Mp/ 6Mp/ 5MP/ 4MP/ 3MP/ 1080P/ 1.3MP/ 720P etc.
Record Rate	200Mbps
Bit Rate	16Kbps ~ 20Mbps Per Channel

Record Mode	Manual, Schedule (Regular, Continuous), MD (Video detection: Motion Detection, Tampering, Video Loss), Stop
Record Interval	1 ~ 120 min (default: 60 min), Pre-record: 1 ~ 30 sec, Post-record: 10 ~ 300 sec
Video Detection and Alarm	
Trigger Events	Recording, PTZ, Tour, Video Push, Email, Snapshot, Buzzer and Screen Tips
Video Detection	Motion Detection, MD Zones: 396 (22 × 18), Video Loss and Tampering
Alarm input	4 Channel
Alarm output	2 Channel
Playback and Backup	
Playback	1/4/9/16
Search Mode	Time /Date, MD and Exact Search (accurate to second), Smart search
Playback Function	Play, Pause, Stop, Rewind, Fast play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Full Screen, Backup Selection, Digital Zoom
Backup Mode	USB Device/Network
Third-party Support	
Third-party Support	Arecont Vision, Airlive, AXIS, Canon, Dynacolor, JVC, LG, Panasonic, Pelco, PSIA, Samsung, Sanyo, Sony, Watchnet and more
Network	
Interface	1 RJ-45 Port (10/100/1000Mbps)
Ethernet Port	1 Independent 1000Mbps Ethernet Port
PoE	16 ports (IEEE802.3at/af)
Network Function	HTTP, HTTPS, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPoE, DDNS, FTP, SNMP, IP Search (Support IP camera, DVR, NVS, etc.), Easy4ip
Max. User Access	128 users
Smart Phone	iPhone, iPad, Android
Interoperability	ONVIF 2.4, SDK, CGI
Storage	
Internal HDD	2 SATA III Ports, Up to 6 TB capacity for each HDD
HDD Mode	Single
Auxiliary Interface	
USB	2 ports(1 USB2.0, 1 USB3.0)
RS232	1 Channel
RS485	N/A
Electrical	
Power Supply	AC100V ~ 240V, 50 ~ 60 Hz
Power Consumption	NVR: < 13.2W(without HDD)
	PoE: Max 25.5w for single port, 130w in total

Environmental

Operating Conditions	-10°C ~ +55°C (+14°F ~ +131°F), 86 ~ 106kpa
----------------------	---

Storage Conditions	-20°C ~ +70°C (-4°F ~ +158°F), 0 ~ 90% RH
--------------------	---

Construction

Dimensions	1U, 375mm×327.5mm×53mm (14.8" x 12.9" x2.1")
------------	--

Net Weight	2.6kg (5.7 lb) (without HDD)
------------	------------------------------

Gross Weight	4kg(8.8 lb)(without HDD)
--------------	--------------------------