

## PERFORMANCE

### Processor

Intel® Core™ i7-1185G7 (4C / 8T, 3.0 / 4.8GHz, 12MB)

### Graphics

NVIDIA® Quadro® T500 4GB GDDR6

### Chipset

Intel SoC Platform

### Memory

16GB Soldered DDR4-3200 non-ECC

### Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

### Max Memory

Up to 48GB (16GB soldered + 32GB SO-DIMM)

### Storage

512GB SSD M.2 2280 PCIe 3.0 NVMe Opal2

### Storage Support

One drive, up to 2TB M.2 2280 SSD

### Card Reader

MicroSD Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

### Camera

720p + IR with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 50Wh

### Max Battery Life

Battery life data is still under tuning and pending availability

### Power Adapter

65W USB-C Slim 2-pin

## DESIGN

### Display

14" FHD (1920x1080) IPS 300nits Anti-glare

### Touchscreen

None

### Color Calibrator

None

### Keyboard

Backlit, English

### Case Color

Black

### Case Material

PC + ABS (Top), PC + ABS / Talc15 + Magnesium Alloy (Keyboard Cover), PA / 50% GF (Bottom)

### Dimensions (WxDxH)

329 x 227 x 17.9 mm (12.95 x 8.94 x 0.70 inches)

### Weight

1.469 kg (3.24 lbs)

## SOFTWARE

### Operating System

Windows® 10 Pro 64, English

### Bundled Software

None

## CONNECTIVITY

### Ethernet

100/1000M

### WLAN + Bluetooth™

Intel AX210 11ax, 2x2 + BT5.2

### WWAN

WWAN Upgradable

### SIM Card

None

### NFC

None

### Standard Ports

- 1x side docking connector
- 1x Ethernet (RJ-45)
- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microSD card reader
- 1x HDMI® 2.0
- 2x Thunderbolt™ 4 / USB4™ 40Gbps / USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)

### Optional Ports (configured)

1x Smart card reader

### Monitor Cable

None

## SECURITY & PRIVACY

### Smart Card Reader

None

### Security Chip

Discrete TPM 2.0

### Fingerprint Reader

Touch Style, Match-on-Chip

### Physical Locks

Kensington® Security Slot

## MANAGEABILITY

### System Management

Intel® vPro, DASH

## SERVICE

### Base Warranty

3-year, Depot

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold
- TCO Certified Notebooks 8
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed


### ISV Certifications

Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)

## MODEL

**TopSeller** : Yes **Announce Date** : 2021-02-23

**EAN / UPC / JAN** : 195713090803 **End of Support** : 2027-09-23



· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad USB-C Dock Gen 2

40AJ0135US

- Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C dock is compatible with Lenovo notebooks as well as note...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Accidental Damage Protection + Keep Your Drive + 3Y Sealed Battery) (5PS0N73238)
BETTER	3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)
GOOD	3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07092)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference