


Features

- H.265+/H.265 dual-stream video compression
- Supports HDCVI/AHD/TVI/CVBS/IP video inputs
- Supports 8 channels of IPC access, each channel up to 8MP input; Max 32Mbps Incoming Bandwidth
- IoT & POS functionalities
- Perimeter Protection and SMD Plus
- Up to 2 channels video stream(analog channel)human face recognition



Specification

System	
Main Processor	Embedded Processor
Operating System	Embedded LINUX
Perimeter Protection	
Perimeter protection	<ol style="list-style-type: none"> 1.AI by DVR: Detection alarm for human and vehicle. Filter misinformation such as leaves and light. 2.Function configuration: Set at most 10 rules such as area intrusion and tripwire intrusion. 3.Performance: 2 channels
Live View	<ol style="list-style-type: none"> 1. Rule box inspection: Configure the rule box and object inspection box. 2.Smart panel: Display object classification (human, vehicle), event types, triggering time, image matting and object types. Attribute is not supported. 3. Counting: Count people in Peopletotal. Count motor vehicles in Vehicle. Support exporting of associated event playback before and after 10 seconds.
Playback	<ol style="list-style-type: none"> 1. Search conditions: According to channels, time, event types and target types. 2.Functions: Support search of associated event playback or snapshot before and after 10 seconds. 3. Snapshot capacity: 500,000
Face Recognition	

Performance	1. UP to 12 face pictures/sec processing (modeling and comparing). 2. Up to 2 channels video stream (analog channel) human face recognition. 3. Up to 10 face databases with 10,000 face images in total. 4. Up to 300,000 face detection events in total. 5. Up to 300,000 face Recognition events in total.
Stranger Mode	Detect strangers' faces (not in device's face database).Similarity threshold can be set manually.
AI Search	Up to 8 target face images search at same time, similarity threshold can be set for each target face image.
Database Management	Up to 10 face databases with 10,000 face images in total. Name, gender, birthday, nationality, address, ID information can be added to each face picture.
Database Application	Each database can be applied to video channels independently.
Trigger Events	Buzzer, Voice Prompts, Email, Snapshot, Recording, Alarm Out, PTZ Activation, etc.
SMD Plus	
SMD Plus	1. AI by DVR: Motion detection alarm for human and vehicle. Filter misinformation such as leaves and light. 2. Performance: 4 channels , AI by DVR
Preview	Preview: Configure and inspect detection box
Playback	1.Playback: Search videos through channels, time and target types. 2.Functions: Support search of associated event playback before and after 10 seconds.
Video and Audio	
Analog Camera Input	4 Channel, BNC
HDCVI Camera	4K, 6MP, 4MP, 1080P@25/30fps, 720P@50/60fps, 720P@25/30fps
AHD Camera	5MP, 4MP, 3MP, 1080P@25/30, 720P@25/30fps
TVI Camera	5MP, 4MP, 3MP, 1080P@25/30, 720P@25/30fps
CVBS Camera	PAL/NTSC
IP Camera Input	4+4 Channel, each channel up to 8MP
Audio In/Out	4 Channel Input, 1 Channel Output, RCA
Two-way Talk	Reuse audio in/out, RCA
Recording	
Compression	H.265+/H.265/H.264+/H.264
Resolution	4K, 6MP, 5MP, 4K-N, 4MP, 3MP, 4M-N, 1080P, 720P, 960H, D1, CIF, QCIF
Record Rate	Main stream: All channel: 4K(1fps-7fps); 6MP(1fps-10fps); 5MP(1fps-12fps); 4K-N/4MP/3MP(1fps-15fps); 4M-N/1080P/720P/960H/D1/CIF/QCIF (1fps-25/30fps); Sub stream:960H(1fps-15fps); D1/CIF/QCIF(1fps-25/30fps)
Bit Rate	32Kbps-6144Kbps Per Channel
Record Mode	Manual, Schedule (General, Continuous), MD (Video detection: Motion Detection, Video Loss, Tampering), Alarm, Stop
Record Interval	1-60 min (default: 60 min), Pre-record: 1 sec-30 sec, Post-record: 10 sec-300 sec
Audio Compression	AAC(only for the 1st channel), G.711A, G.711U, PCM

Audio Sample Rate	8KHz, 16 bit Per Channel
Audio Bit Rate	64Kbps Per Channel
Display	
Interface	1 HDMI, 1 VGA
Resolution	HDMI:2560×1440, 1920×1080, 1280×1024, 1280×720 VGA: 1920×1080, 1280×1024, 1280×720
Multi-screen Display	When IP extension mode not enabled: 1/4 When IP extension mode enabled: 1/4/8
OSD	Camera title, Time, Video loss, Camera lock, Motion detection, Recording
Network	
Interface	1 RJ-45 Port (100M)
Network Function	HTTP, HTTPS, TCP/IP, IPv4/IPv6, UPnP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPoE, DDNS, FTP, Alarm Server, P2P, IP Search (Support IP camera, DVR, NVS, etc.)
Max. User Access	128 users
Smart Phone	iPhone, iPad, Android
Interoperability	ONVIF 16.12, CGI Conformant
Video Detection and Alarm	
Trigger Events	Recording, PTZ, Tour, Video Push, Email, FTP, Snapshot, Buzzer and Screen Tips
Video Detection	Motion Detection, MD Zones: 396 (22 × 18), Video Loss, Tampering and Diagnosis
Alarm input	8
Relay Output	3
Playback and Backup	
Playback	1/4
Search Mode	Time /Date, Alarm, MD and Exact Search (accurate to second)
Playback Function	Play, Pause, Stop, Rewind, Fast play, Slow Play, Next File, Previous File, Next Camera, Previous Camera, Full Screen, Repeat, Shuffle, Backup Selection, Digital Zoom
Backup Mode	USB Device/Network
Storage	
Internal HDD	1 SATA Port, up to 10TB capacity for each disk
eSATA	N/A
Auxiliary Interface	
USB	2 USB Ports (2 USB 2.0)
RS232	N/A
RS485	1 Port, for PTZ Control
Electrical	

Power Supply	DC 12V/2A
Power Consumption	<10W (Without HDD)
Construction	
Dimensions	Mini 1U, 325mm×255mm×55mm (12.8" x 10" x 2.2")
Net Weight	1.45kg (3.2lb) (without HDD)
Gross Weight	2kg (4.4lb)
Installation	Desktop installation
Environmental	
Operating Conditions	-10°C to +55°C (+14°F to +131°F), 0-90% RH
Storage Conditions	-20°C to +70°C (-4°F to +158°F) , 0-90% RH
Third-party Support	
Third-party Support	Arecont Vision, AXIS, Bosch, Brickcom, Canon, CP Plus, Dynacolor, Honeywell, Panasonic, Pelco, Samsung, Sanyo, Sony, Videotec, Vivotek, and more