

## 1500VA 900W 230V SmartPro Line-Interactive UPS - 8 C13 Outlets, 2 Australian Outlet Adapters, LCD, USB, Tower

MODEL NUMBER: **SMX1500LCDTA**



Desktop UPS offers complete power protection for small network applications, including home offices, security systems and digital signage.

### Features

#### 1.5kVA/900W/230V Battery Backup for PCs, Home Theaters or Digital Signage

This SmartPro® line-interactive UPS system with AVR protection provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The 230V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, HDTVs, Blu-ray players, game consoles, ATMs, kiosks, security systems and digital signage equipment.

#### Allows Time to Back Up Critical Files During a Blackout

Backup support allows you to work through short power failures and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the line-interactive UPS system should keep an energy-efficient desktop computer with small LCD monitor powered as long as 90 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

#### 8 IEC 320 C13 Outlets Protect Your Connected Components

Six C13 outlets provide battery backup, surge protection and voltage regulation for your computer, monitor and other crucial components. The other two C13 outlets provide surge suppression only for printers, speakers and other desktop equipment regarded as non-essential during a blackout. Included outlet adapters convert two C13 outlets to 10A Australia/New Zealand-compatible outlets. A high >95% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

#### Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts and overvoltages. The SMX1500LCDTA can correct brownouts as low as 170V and overvoltages as high as 280V back to nominal 230V power continuously, all while keeping the battery fully charged and ready to take over in case of power failure.

#### 455 Joules Fight Back Against Unexpected Power Surges

A 455-joule surge suppression rating protects connected components from the harmful effects of power surges. In addition to the C13 outlets, the RJ45 jacks for phone, DSL, fax, modem and Ethernet connections (not compatible with PoE applications) also are protected against surges.

### Highlights

Protects equipment against blackouts, brownouts, transient surges and line noise  
Keeps AC power running during outages to allow time for file saves and safe shutdown  
Maintains line power operation with input voltage as low as 170V and as high as 280V  
8 C13 outlets with 2 AUS/NZ adapters power and protect PCs and other equipment  
Multifunction LCD screen provides valuable voltage, load, battery and fault statuses

### Applications

- Protect your PC and other sensitive electronics against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Support small business phone systems, point-of-sale (POS) systems, kiosks and ATMs

### Package Includes

- SMX1500LCDTA 1.5kVA 900W 230V Line-Interactive UPS with 8 Outlets
- (2) C13 to AUS/NZ outlet adapters
- USB cable
- Power cord with 10A AUS/NZ plug, 1.5 m
- Owner's manual



#### Combats Electromagnetic Interference That Can Harm Equipment

EMI (electromagnetic interference) and RFI (radio frequency interference) line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The SMX1500LCDTA incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

#### Interactive LCD Reports Real-Time UPS and Power Status

The multifunction LCD screen displays vital voltage, load and battery data, as well as critical fault status. An audible alarm will sound in case of low battery, overload, fault and power failure.

#### HID-Compliant USB Port Allows for Automatic Saves and Shutdowns

This port connects the SMX1500LCDTA to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended system shutdown in case of a prolonged power failure. USB cable is included. The UPS works with Windows, Mac and Linux operating systems.

#### Tower Form Factor for Easy Placement in Your Workspace or Media Center

The compact ABS housing fits easily on a desktop, shelf or anywhere else convenient to your workstation or home theater. Connect the C14 power inlet to a properly grounded AC wall outlet with a user-supplied power cord with country-specific plug. A detachable 1.5-meter power cord with 10A Australia/New Zealand input plug is included. A variable-speed cooling fan regulates the UPS system's internal temperature to prevent the unit from overheating.

## Specifications

OVERVIEW	
UPC Code	037332255181
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	9A
Nominal Input Voltage(s) Supported	230V AC
UPS Input Connection Type	C14 inlet
UPS Input Connection Description	1.5m power cord with 10A Australia / New Zealand input plug
Input Circuit Breakers	10A fuse
UPS Input Cord Length (ft.)	5
UPS Input Cord Length (m)	1.5
Input Phase	Single-Phase
OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output Capacity (kVA)	1.5
Output Watt Capacity (Watts)	900
Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz



Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 2 surge-only outlets
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Output Receptacles	(8) C13
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Half Load Runtime (min.)	10 minutes (450 watts)
Expandable Runtime	No
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 8 hours from 10% to 90%
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS~RBC51">RBC51</a>&nbsp; (requires 2)
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with a correction range from 170V to 280V
Overvoltage Correction	Input voltages between 247 and 280 are reduced by 15%
Undervoltage Correction	Input voltages between 170 and 207 are boosted by 18%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	LCD screen with scroll buttons indicates Input voltage, Output voltage, Frequency (Hz), AVR boost / cut status, Output load in watts, Output load percentage, Output load in watts, Battery voltage and Estimated runtime in minutes
Switches	Power switch offers whole UPS power control; Scroll/mute button enables LCD selection options and silences audible alarm; Test button initiates self test
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	455
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes



<b>PHYSICAL</b>	
Primary Form Factor	Tower
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	Tower
Primary UPS Depth (mm)	394
Primary UPS Height (mm)	203
Primary UPS Width (mm)	146
Shipping Dimensions (hwd / in.)	12.10 x 9.10 x 19.20
Shipping Weight (kg)	12.25
UPS Power Module Dimensions (hwd, in.)	8 x 5.75 x 15.5
UPS Power Module Weight (kg)	11.20
UPS Power Module Weight (lbs.)	24.7
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	79
Battery Mode BTU / Hr. (Full Load)	918
AC Mode Efficiency Rating (100% Load)	95%
<b>COMMUNICATIONS</b>	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	6 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	170V (factory setting), 175V (medium setting), 180V (narrow setting)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

High Voltage Transfer to Battery Power (Setpoint)	280V (factory setting), 275V (medium setting), 270V (narrow setting)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	GOST (Russia); EN 62040-1; EN 62040-2
Product Compliance	RoHS; SASO (Saudi Arabia); CE (Europe)
<b>WARRANTY</b>	
Product Warranty Period (International)	2-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>