



Manage this device with Digi Remote Manager

# DIGI IX20

## Cloud managed networking for critical applications

Digi IX20 is a full-featured cellular router that scales from general connectivity applications to industrial routing and security. Its flexible power and connectivity options make it a versatile choice for use in industrial infrastructure, digital signage, retail kiosks, service terminals and other critical assets with a need for secure transactions.

The high-performance architecture of the Digi IX20 router provides automatic and software-selectable primary and backup WWAN connectivity over multi-carrier cellular LTE. Digi IX20 supports advanced security (stateful firewall, MAC filtering and VPN), cellular redundancy (Digi SureLink®) and management (SNMP, event logging, analyzer trace and QoS), facilitating use in PCI or NERC-CIP compliant applications.

Gain critical insights into your deployed devices and manage your network with Digi Remote Manager® (Digi RM) — the command center for your deployment. Digi RM is a cloud-based solution that facilitates easy setup, mass configuration, maintenance and support, even for thousands of devices. In the event of an interruption to your primary network connection, Digi RM also provides secure, out-of-band management access to Digi IX20 through a serial port and command-line interface.

The Digi IX20 family of routers has a single part number, which simplifies inventory control for global distribution and deployment. In addition, Digi IX20 is designed for Digi CORE® plug-in LTE modems that can be changed out or upgraded without replacing the entire router.


### FEATURES AND BENEFITS

- Compact and economical cellular routing platform with industrial feature set
- Redundant connectivity with dual SIMs and Digi SureLink®
- Global bands and single part number to simplify global distribution, deployment and management
- Built-in Digi TrustFence® for device security, secure encrypted connections, ongoing monitoring and support
- Digi Remote Manager® platform for easy setup, mass configuration and out-of-band management
- Dual Ethernet ports and single serial (RS-232) port

### RELATED PRODUCTS



### APPLICATION EXAMPLE



## SPECIFICATIONS

## DIGI® IX20

## CELLULAR\*

## CERTIFICATIONS

Visit [www.digi.com/resources/certifications](http://www.digi.com/resources/certifications) for latest certifications

LTE (G4) WITH DIGI CORE® PLUG-IN  
LTE MODEM 1002-CMG4

LTE Cat 4: B1, B2, B3, B4, B5, B7, B8, B12, B13, B18, B19, B20, B25, B26, B28, B38, B39, B40, B41  
3G: B1, B2, B4, B5, B6, B8, B19  
2G: 850 / 900 / 1800 / 1900 MHz

LTE (N4) WITH DIGI CORE PLUG-IN  
LTE MODEM 1002-CMF4

LTE Cat 4: B2, B4, B5, B12, B13, B14, B66, B71  
3G: B2, B4, B5  
2G: No support

LTE (M1) WITH DIGI CORE PLUG-IN  
LTE MODEM 1002-CMM1\*\*

LTE Cat M1/NB1: B1, B2, B3, B4, B5, B8, B12, B13, B18, B19, B20, B26, B28;  
2G: 850 / 900 / 1800 / 1900 MHz;

## CONNECTORS

(2) 50 Ω SMA (center pin: female)

## SIM SLOTS

(2) Mini-SIM (2FF)

## SIM SECURITY

Secured in cellular module

## WI-FI

## MODULE

1 x 1 SISO dual-band 802.11a/b/g/n/ac (2.4 GHz / 5 GHz)

## AUTHENTICATION

TACACS+, Enterprise RADIUS

## MODES

Client mode and access point mode simultaneously

## CLIENTS

Maximum 10 clients (access point mode: regardless of combination of clients and access points)

## ACCESS POINTS

Maximum 2 access points (access point mode: regardless of combination of clients and access points)

## SECURITY

WPA/WPA-2 personal, WPA/WPA-2 enterprise

## CONNECTORS

(1) 50 Ω SMA (center pin: male)

## SOFTWARE AND MANAGEMENT

## REMOTE MANAGEMENT

Digi Remote Manager®; SNMP v2/v3 (user installed/managed)

## LOCAL MANAGEMENT

WebUI (HTTP/HTTPS); CLI (Telnet, SSH)

MANAGEMENT/  
TROUBLESHOOTING TOOLS

FTP client, SCP; protocol analyzer with PCAP for Wireshark; event logging with syslog and SMTP client; NTP/SNTP; Nagios, Intelliflow, iPerf, Dynamic DNS, ping, traceroute

## MEMORY

256 MB RAM, 256 MB flash

## ETHERNET

## PORTS

(2) RJ-45; 10/100 Mbps (auto-sensing)

## SERIAL

## PORTS

(1) DB9M; RS-232 DTE; signal support TXD, RXD, CTS, DTR, DCD, flow control software (XON/OFF), hardware supported (CTS/RTS)

## PHYSICAL

## DIMENSIONS (L x W x H)

107 mm x 162 mm x 35 mm (4.21 in x 6.38 in x 1.38 in)

## WEIGHT

0.65 kg (1.4 lb)

## STATUS LEDs

Power, Internet, Wi-Fi, SIM 1, SIM 2, signal strength (5), LTE

## ENCLOSURE

Glass-filled polyphenylene sulphide (PPS) / IP30

## POWER REQUIREMENTS

## POWER INPUT

9 - 30 VDC, 1.0 A maximum; Connector: 2-position rewirable plug with securing screws included

## POWER CONSUMPTION

2.5 W typical (idle); 6 W typical (peak Tx/Rx)

## ENVIRONMENTAL

## OPERATING TEMPERATURE

Models with Wi-Fi: -20° C to 70° C (-4° F to 158° F); device performance may be impacted above 50° C (122° F)

Models without Wi-Fi: -40° C to 70° C (-40° F to 158° F); device performance may be impacted above 50° C (122° F)

## STORAGE TEMPERATURE

-40° C to 85° C (-40° F to 185° F)

## RELATIVE HUMIDITY

5% to 95% (non-condensing)

\*Transfer rates are network operator dependent.

\*\*Digi CORE 1002-CMM1 requires only one cellular antenna.

## SPECIFICATIONS

## DIGI® IX20

### APPROVALS

#### CELLULAR

Visit [www.digi.com/resources/certifications](http://www.digi.com/resources/certifications) for latest cellular certifications

#### SAFETY

IEC62368-1, CB, EN62311

#### ENVIRONMENTAL

ROHS3

#### EMISSIONS / IMMUNITY

CE; RED; FCC Part 15, Subpart B; ICES-003; AU/NZS CISPR32

### WARRANTY

#### PRODUCT WARRANTY

3-year\*

\*Standard 3-year warranty upgradeable to 5 years with purchase of a Digi Remote Manager Premier 5-year subscription applicable to the product purchased only at the time of product purchase and with product registration at that time in Digi Remote Manager.

## ENTERPRISE SOFTWARE

## DESCRIPTION

### CELLULAR CONNECTIVITY

#### PROTOCOL SUPPORT

HTTPS, FTP client, SSL, TLS v1.2, SCP (client and server), SFTP, SMTP client for use by scripts and the command line, SNMP (v2/v3), SSH; remote management via Digi Remote Manager®; Protocol analyzer, ability to capture PCAP for use with Wireshark; DynDNS; Dynamic DNS client compatible with BIND9/No-IP/DynDNS; Captive portal, Intelliflow; Nagios, DNS server, NTP server, Multicast, mDNS, IPerf

#### SECURITY

IP filtering, stateful firewall, custom firewall rules (iptables), address and port translation; TLS 1.2 and above, FIPS 197, open VPN client and server; VPN tunnels; Authentication: RADIUS, TACACS+; certificates; MAC address filtering; VLAN support

#### VPN

IPSec with IKEv1, IKEv2, NAT Traversal; OpenVPN client and server; GRE VPN tunnels; Cryptology: SHA-1/256/384/512, MD5, RSA; Encryption: 3DES and AES up to 256-bit (CBC mode for IPsec); Diffie Hellman: DH groups 1-32 (CURVE448)

#### ROUTING / FAILOVER

IP pass-through; NAT, NAPT with IP port forwarding; Ethernet bridging; GRE; Multicast routing; Routing protocols: RIP (v1, v2) OSPF, BGP; IP failover: VRRP; automatic failover, Digi SureLink®

#### OTHER PROTOCOLS

DHCP; dynamic DNS client compatible with No-IP/DynDNS

## PRODUCT IMAGES

### FRONT



### WITH ANTENNAS



### BACK



# DIGI REMOTE MANAGER®



Digi Remote Manager is the technology platform that brings networks to the next level, allowing networks — and the people who manage them — to work smarter. With Digi Remote Manager you can transform a multitude of dispersed IoT devices into a dynamic, intelligent network. Now you can easily deploy, monitor and diagnose thousands of mission-critical devices from a single point of command — on your desktop, tablet or phone. All the while, its software-defined security diligently safeguards your entire Digi ecosystem.

Learn more at [www.digi.com/digi-remote-manager](http://www.digi.com/digi-remote-manager)

## CAPABILITIES

- Activate, monitor and diagnose your mission-critical devices from a single point of command and control — on your desktop or mobile app
- Schedule key operations — including firmware updates and file management — on a single device or on a group of devices, keeping your network functionality up-to-date and maintaining compliance standards
- Manage edge devices out-of-band via console terminal access
- Keep tabs on device health and connectivity across device deployments of any size
- Create detailed reports and enable real-time alerts for specified conditions
- Integrate device data through open APIs to gain deeper insights and control with third-party applications
- Report and alert on performance statistics, including connection history, signal quality, latency, data usage and packet loss

## INFRASTRUCTURE

- Hosted in a commercial-grade cloud server environment that meets SOC 1®, SOC 2® and SOC 3® standards
- Superior availability, operating to 99.9% or greater
- Open APIs available to support application development

## SECURITY

- More than 175 security controls in place to protect your data
- Member of the Center for Internet Security® (CIS®)
- Enables compliance with security frameworks like ISO27002, HIPAA, NIST and more
- Earned Skyhigh's CloudTrust™ Program highest rating of Enterprise-Ready

PART NUMBERS	DIGI® IX20
IX20-WAG4	Digi IX20 - LTE Cat 4 Global, Wi-Fi, (2) Ethernet, DB-9 RS-232; includes DIN rail clip, power supply, (2) cellular antenna, Wi-Fi antenna and Ethernet cable
IX20-0AG4	Digi IX20 - LTE Cat 4 Global, (2) Ethernet, DB-9 RS-232, includes DIN rail clip, power supply, (2) cellular antenna and Ethernet cable
IX20-W0G4	Digi IX20 - LTE Cat 4 Global, Wi-Fi, (2) Ethernet, DB-9 RS-232
IX20-00G4	Digi IX20 - LTE Cat 4 Global, (2) Ethernet, DB-9 RS-232
IX20-WAN4	Digi IX20 - LTE Cat 4 North America, Wi-Fi, (2) Ethernet, DB-9 RS-232; includes DIN rail clip, power supply, (2) cellular antenna, Wi-Fi antenna and Ethernet cable
IX20-0AN4	Digi IX20 - LTE Cat 4 North America, (2) Ethernet, DB-9 RS-232, includes DIN rail clip, power supply, (2) cellular antenna and Ethernet cable
IX20-W0N4	Digi IX20 - LTE Cat 4 North America, Wi-Fi, (2) Ethernet, DB-9 RS-232
IX20-00N4	Digi IX20 - LTE Cat 4 North America, (2) Ethernet, DB-9 RS-232
IX20-WAM1	Digi IX20 - LTE Cat M1 Global, Wi-Fi, (2) Ethernet, DB-9 RS-232; includes DIN rail clip, power supply, (1) cellular antenna, Wi-Fi antenna and Ethernet cable
IX20-0AM1	Digi IX20 - LTE Cat M1 Global, (2) Ethernet, DB-9 RS-232, includes DIN rail clip, power supply, (1) cellular antenna and Ethernet cable
IX20-W0M1	Digi IX20 - LTE Cat M1 Global, Wi-Fi, (2) Ethernet, DB-9 RS-232
IX20-00M1	Digi IX20 - LTE Cat M1 Global, (2) Ethernet, DB-9 RS-232

PART NUMBERS	ACCESSORIES
76002104	Power supply with plug tips for US, UK, EU, AU
76002105	Wi-Fi antenna
76002106	Ethernet cable - 2 m (6 ft)
76000926	Cellular antenna
76002093	DIN rail mounting bracket kit
76002095	DIN rail clip kit

PART NUMBERS	DIGI REMOTE MANAGER®
DIGI-RM-STD-1YR	Digi Remote Manager Standard - 1-year subscription
DIGI-RM-PRM-1YR	Digi Remote Manager Premier - 1-year subscription
DIGI-RM-PRM-3YR	Digi Remote Manager Premier - 3-year subscription
DIGI-RM-PRM-5YR	Digi Remote Manager Premier - 5-year subscription

FOR MORE INFORMATION  
PLEASE VISIT [DIGI.COM](http://DIGI.COM)

**DIGI SERVICE AND SUPPORT** / You can purchase with confidence knowing that Digi is always available to serve you with expert technical support and our industry leading warranty. For detailed information visit [www.digi.com/support](http://www.digi.com/support).

© 1996-2020 Digi International Inc. All rights reserved.  
All trademarks are the property of their respective owners.

91004421  
C6/121

**DIGI INTERNATIONAL WORLDWIDE HQ**  
877-912-3444 / 952-912-3444 / [www.digi.com](http://www.digi.com)

**DIGI INTERNATIONAL JAPAN**  
+81-3-5428-0261 / [www.digi-intl.co.jp](http://www.digi-intl.co.jp)

**DIGI INTERNATIONAL GERMANY**  
+49-89-540-428-0

**DIGI INTERNATIONAL SINGAPORE**  
+65-6213-5380

**DIGI INTERNATIONAL CHINA**  
+86-21-50492199 / [www.digi.com.cn](http://www.digi.com.cn)

