

PERFORMANCE

Processor

Qualcomm® Snapdragon™ 730G (8C, 8x Kryo 470 @2.2GHz)

Graphics

Integrated Qualcomm Adreno 618 GPU

Chipset

Qualcomm SoC Platform

Memory

4GB LPDDR4x (uMCP, DRAM)

Storage

128GB (uMCP, UFS 2.1)

Expandable Memory

MicroSD card (Up to 1TB, exFAT)

Card Reader

MicroSD Card Slot

Storage Support

- 128GB uMCP (UFS-Based MCP, UFS 2.1) on systemboard
- MicroSD card, supports FAT32 up to 256GB, exFAT up to 1TB

Camera

Front 8.0MP (RGB) + 8.0MP (IR) / Rear 13.0MP (wide) + 5.0MP (ultrawide)

Microphone

2x, Array

Speakers

4 side stereo speakers, 1.5W x4, JBL authorized, Dolby® Atmos®

Sensors

- Accelerometer (G) sensor
- eCompass
- Hall sensor
- Gyroscope sensor
- Ambient light sensor (ALS)
- ToF sensor
- Proximity sensor

Vibrator

Vibrator

Battery

Integrated 8400mAh / 8600mAh

Max Battery Life

Standby Time: up to 4.4 wks
 Video Playback Time: up to 15 hr
 Browsing Time: up to 8 hr, up to 15 hr (Dark Mode)
 Normal comprehensive usage time: up to 15 hr
 Tablet comprehensive usage time: up to 10.4 hr

Charging Time

Over 3.1 hr

Power Adapter

10V / 2.0A

DESIGN

Display

11.5" WQXGA (2560x1600) OLED 350nits Glossy, 100% sRGB, HDR10, Dolby Vision™

Touchscreen

10-point Multi-touch

Case Material

Pure metal (Uni-Body)

Pen

None

Dimensions (WxDxH)

264.28 x 5.8 x 171.4 mm (10.40 x 0.22 x 6.74 inches)

Weight

Around 485 g (1.06 lbs)

Case Color

Slate Grey

SOFTWARE

Operating System

Android 10

Preinstalled Software

- Google Play
- Google Photos
- Dolby Atmos
- Office
- Dolby Vision
- Google Chrome
- Google
- Netflix
- Gmail
- Kids Space
- Bamboo Paper
- OneNote
- Squid

CONNECTIVITY

WLAN + Bluetooth™

11a/b/g/n/ac, 2x2 + BT5.0

WWAN

None

SIM Card

No SIM card

VoiceCall

No

Standard Ports

- 1x Pogo pin connector (4-point)
- 1x USB-C 3.1 Gen 1 (support OTG, data transfer, Power Delivery, extend screen, T-Hub and USB-C audio devices)

Optional Ports (configured)

1x microSD card slot (WLAN model)

Docking

No docking

SECURITY & PRIVACY

Fingerprint Reader

Touch style fingerprint reader on power button

SERVICE

Base Warranty

1-year, Mail-in

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- RoHS compliant

Other Certifications

TÜV Rheinland (Full Care Display Certification)

MODEL

TopSeller : No

Announce Date : 2020-09-15

EAN / UPC / JAN : 195235752869

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference