

**PERFORMANCE****Processor**

Intel® Xeon® W-2225 (4C / 8T, 4.1 / 4.6GHz, 8.25MB)

**Processor Sockets**

1x FCLGA2066

**Chipset**

Intel C422

**Memory**

1x 16GB RDIMM DDR4-2933 ECC

**Memory Slots**

4 DIMM sockets with 4 channels

**Max Memory**

- Up to 128GB (with 4 x 32GB DDR4-2666 RDIMMs) on models with Intel Xeon W-2100 Series processor
- Up to 256GB (with 4 x 64GB DDR4-2933 RDIMMs) on models with Intel Xeon W-2200 Series processor

**M.2 SSD RAID Controller**

RAID 0/1

**M.2 SSD Drive**

1x 512GB SSD M.2 PCIe NVMe Opal

**HDD Controller**

Onboard Intel RSTe SATA

**Storage Support**

Up to 4x 3.5" SATA HDD / 2.5" SATA HDD / 2.5" SATA SSD + 5x M.2 PCIe SSD

- 3.5" HDD up to 6TB each
- 2.5" SATA HDD up to 500GB each
- 2.5" SATA SSD up to 2TB each
- M.2 SSD up to 2TB each

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC662 codec

**Power Supply**

625W

**DESIGN****Keyboard**

USB Traditional Keyboard, Black, English

**Mouse**

USB Calliope Mouse

**Expansion Slots**

- Two PCIe 3.0 x16
- One PCIe 3.0 x4
- One PCIe 3.0 x8

**M.2 Slots**

Up to 5x M.2 SSD:

- 2 via onboard slots
- 3 via Single M.2 to PCIe adapter

**Bays**

2x 3.5" disk bay

**Flex Bays**

2x flex bays. Supports the following:

- 2x half-height optical drives
- 2x 5.25" 9.0mm optical drives
- 1x 5.25" 9.0mm optical drive + 2x 3.5"/2.5" SATA SSD/HDD
- 1x 3.5"/2.5" SATA SSD/HDD with Front Access Storage Enclosure

• 1x flex module for the following options:

Tray 1: 9.0mm optical

Tray 2: 15-in-1 USB 3.1 Gen 1 reader, 2x Thunderbolt™, or 4-digit diagnostic display

Port 1 and 2: Front USB 3.1 Gen 1 Type-C or eSATA

- 2x M.2 SSD with 2x Front Removable Drive Enclosures

**Dimensions (WxDxH)**

175 x 426 x 376 mm (6.89 x 16.77 x 14.8 inches, with feet)

**Weight**

14.5 kg (31.96 lbs, maximum configuration)

**CONNECTIVITY****Onboard Ethernet**

1x GbE RJ-45

**Card Reader**

SD Reader

**Front Ports**

- 2x USB 3.1 Gen 1
- 1x microphone (3.5mm)
- 1x headphone (3.5mm)

**Rear Ports**

- 4x USB 3.1 Gen 1
- 1x line-in (3.5mm)
- 2x PS/2 ports (keyboard/mouse)
- 1x Ethernet (RJ-45)
- 2x USB 2.0
- 1x microphone (3.5mm)
- 1x line-out (3.5mm)

**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0, TCG certified

**Physical Locks**

Kensington® Security Slot

**MANAGEABILITY****System Management**

Intel® vPro with AMT 11, DASH

**SERVICE****Base Warranty**

3-year, Onsite

**Included Upgrade**

3Y Premier Support Upgrade from 3Y Onsite (5WSOU26649)

**CERTIFICATIONS****Green Certifications**

- GREENGUARD®
- EPEAT™ Silver
- RoHS compliant
- ENERGY STAR® 8.0 (On model 30BX0095US)

**ISV Certifications**Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)**SOFTWARE****Operating System**

Windows® 10 Pro 64 for Workstations, English

**MODEL**

<b>TopSeller</b>	:	Yes	<b>Announce Date</b>	:	2021-01-19
<b>EAN / UPC / JAN</b>	:	195713399807	<b>End of Support</b>	:	2025-12-21



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 32GB DDR4 2666MHz ECC RDIMM Memory

4X60N86662

Need Increased performance from your system? Add more memory. The Lenovo 32GB DDR4 2666MHz ECC RDIMM memory will upgrade your system's performance and enhance its ability to run more programs simultaneously. Test prov...

## Recommended Services

BEST	5Y Premier Support upgrade from 3Y Premier Support (5WSOW86668)
BETTER	4Y Premier Support upgrade from 3Y Premier Support (5WSOW86673)
GOOD	-

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference