


5.7kW 3-Phase Basic PDU - 42 NEMA 5-15/20R 120V Outlets, 208V L21-20P Input, 6 ft. Cord, 70 in. 0U Rack, TAA

MODEL NUMBER: PDU3V6L2120LV



Delivers 120V AC power to multiple loads from a utility outlet, generator or UPS system in a data center or network closet.

Features

3-Phase 120V PDU Distributes Network-Grade Power to Multiple Loads

This basic PDU is an ideal no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Recommended for small to mid-sized data centers, computer rooms and network closets, the PDU3V6L2120LV features 42 NEMA 5-15/20R outlets in three single-phase output load banks for connecting equipment. A six-foot (1.8-meter) cord with NEMA L21-20P 3-phase input plug connects to your facility's AC power source, generator or protected UPS system to distribute power to connected loads.

Easy to Install Vertically in an EIA-Standard 19 in. Rack

The 70-inch 0U PDU's all-metal housing mounts vertically using the pre-installed toolless mounting buttons or the included brackets. Spare buttons are also included. Use the included PDUMVROTATEBRKT kit to install the PDU with outlets facing the rear for better airflow or equipment access. Cable retention brackets keep power cords organized and your rack free of clutter. The PDU's switchless design helps prevent an accidental shutdown, which could lead to costly downtime.

TAA-Compliant for GSA Schedule Purchases

The PDU3V6L2120LV is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Ideal no-frills PDU for telecom, security, audio/video and other network applications
- 42 NEMA 5-15/20R 120V outlets distribute AC power to connected equipment
- Switchless design helps prevent accidental shutdowns that can lead to costly downtime
- 6 ft. power cord with NEMA L21-20P 3-phase input connects to AC source
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

Deliver network-grade power to high-density equipment in networking, telecom, security, audio/video and sound reinforcement applications

Package Includes

- PDU3V6L2120LV 5.7kW 208V 3-Phase Basic PDU with 120V Output
- Cable retention brackets with installation hardware
- Rack-mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332255709
PDU Type	Basic
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PDU Input Voltage	208
Recommended Electrical Service	20A 208V with NEMA L21-20R outlet
Maximum Input Amps	16
PDU Plug Type	NEMA L21-20P
Input Phase	3-Phase
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
OUTPUT	
Output Capacity Details	5.7kW (120V) total capacity / 16A max per output phase (L1, L2, L3); 16A max per 5-15/20R outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(42) 5-15/20R
Output Nominal Voltage	120
Overload Protection	n/a
PHYSICAL	
Form Factors Supported	Vertical rackmount installation supported with included mounting brackets; supports toolless mounting in button-mount compatible racks
Material of Construction	Metal
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	5.40 x 6.80 x 76.00
Shipping Weight (kg)	6.62
Unit Dimensions (hwd / cm)	177.8 x 5.6 x 4.34
Unit Dimensions (hwd / in.)	70 x 2.2 x 1.71
Unit Weight (kg)	5.76
Unit Weight (lbs.)	12.7
ENVIRONMENTAL	
Operating Temperature Range	0-50C (32-122F)
Storage Temperature Range	-30°C to +60°C (-22°F to +140°F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA), CAN/CSA (Canada), NOM (Mexico), Class A (Emissions), ROHS, TAA Compliant;
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	2-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>