

## HDMI over Cat6 Receiver with Repeater, 4K 60Hz, HDR, 4:4:4, IR Transceiver, PoC, HDCP 2.2, 230 ft., TAA

MODEL NUMBER: **B127A-110-BH**



Works with Tripp Lite's HDMI extender kit to extend 4K video an extra 230 ft. between source and display via Cat6 cable.

### Features

#### HDMI Extender Transceiver Unit Ideal for Digital Signage in Schools and Restaurants

This 4K IR transceiver is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow.

#### Combines with Tripp Lite HDMI Extender Kit to Add More Distance

The B127A-110-BH works with Tripp Lite's B127A-111-BHTH extender kit (sold separately) to further extend a 4K audio/video signal up to 230 feet. It connects between the transmitter and transceiver from the extender kit with user-supplied Cat6 cabling. IR remote control lets you operate the source from the display end of the installation.

#### Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127A-110-BH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified by HDMI 2.0, with full, rich uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This transceiver also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Built-in equalization allows you to fine-tune the image quality at the remote display.

#### Create a Daisy Chain to Achieve More Distance

This transceiver combines with the Tripp Lite B127A-111-BHTH extender kit (sold separately) and additional B127A-110-BH transceivers to form daisy-chain installations up to 920 feet from the transmitter. Up to four total transceivers can be chained together, each capable of extending a 4K/60 Hz signal up to 230 feet per unit. In addition to the extender kit, this transceiver is also compatible with Tripp Lite's B127A-1A1-BCBH, B127A-1A1-BDBH and B127A-1A1-BHBH and can be used to replace any receivers in the installation as well.

#### Add a Tripp Lite Signal Booster to Achieve, Yes, Even More Distance

The transceiver is also compatible with Tripp Lite's B127A-010-H signal booster (sold separately), which allows the signal to be boosted up to 400 feet total between the transmitter and transceiver. When used in a daisy-chain installation, this brings the total extension distance up to 1,090 ft. **Note: B127A-010-H will only work when used in the first link of the daisy-chain installation.**

#### Built-In PoC Technology Lets You Avoid Bulky External Power Bricks

Power over Cable (PoC) technology powers the receiver at the end of the chain over Cat6 cable. LEDs on both the transmitter and transceiver will light up to indicate the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to

### Highlights

- Combines with Tripp Lite's B127A-111-BHTH to extend 4K signals up to 230 ft.
- Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Power over Cable (PoC) technology provides power to the receiver via Cat6 cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Extend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codes
- Gain flexibility in where the transceiver is placed, with the freedom to move and relocate it away from an AC outlet
- Improve the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location

### System Requirements

- Source device with HDMI output (Blu-ray player, cable box, laptop)
- Display device with HDMI input (HDTV, projector, monitor)
- Tripp Lite B127A-111-BHTH



place the transceiver where needed without worrying about finding a nearby AC outlet. Power is also equally distributed to any additional transceivers within a daisy-chain installation.

**Plug-and-Play Operation for Quick Setup and Immediate Use**

The transceiver works right out of the box with no software required. Mounting hardware is included for installing it on a wall, pole or 19-inch rack. Connect the transceiver to a transmitter and any additional transceiver with user-supplied Cat6 patch cable (such as Tripp Lite's N202-Series). Connect to a 4K display with a user-supplied HDMI cable (such as Tripp Lite's P568- or P569-Series).

**TAA-Compliant for GSA Schedule Purchases**

The B127A-110-BH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

HDMI over Cat6 Extender Kit

**Package Includes**

- B127A-110-BH HDMI over Cat6 IR Transceiver
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332258601
Product Type	Cat5/Cat6 Transceiver
Technology	HDMI; HDR; Cat5/5e; Cat6; POC; IR
Form Factor and Mounting Options	Box; Wall-mount
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max. Distance (Between any 2 Units)	230 ft.
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1



Signal Range (ft.)	230
Signal Range (m)	70
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Max Supported Color Depth	36-bit True Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
<b>AUDIO</b>	
Audio Input	HDMI
Audio Output	Toslink; HDMI
Audio Specification	Pass-through audio (LPCM 2.0/5.1/7.1)
<b>POWER</b>	
Power Source	Unit (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.6A
External Power Supply Output Specs (V / A)	24V/1A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply Certifications	CE; FCC; CCC; GS; TUV; UL; cUL
Power Over Cable (PoC) Support	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Green (Power); RJ45 ports: Green (Connection), Orange (Activity)
<b>PHYSICAL</b>	
Included Mounting Accessories	Wallmount
Material of Construction	Metal
Number of Displays	1
Unit Dimensions (hwd / cm)	2.7 x 11.5 x 6.24
Unit Dimensions (hwd / mm)	27 x 115 x 62.4
<b>ENVIRONMENTAL</b>	



Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	230
Signal Range (m)	70
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	Zero-Latency
USB Extension Support	No
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (FEMALE)
Side A - Connector 2	3.5MM (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
Side B - Connector 4	TOSLINK (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
Recommended Category Cable	Cat6
Transmission Distance	230 ft., 400 ft. with B127A-010-H signal booster
Built-In Equalizer	No
<b>SPECIAL FEATURES</b>	
DIN Mountable	No
Integrated/Removable Cable	No
MST Support	No
Included Mounting Accessory	No
Multi-Resolution Support	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, REACH, RoHS
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	1-year limited warranty
--	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>