



PDU33103 | MONITORED PDU SERIES



Deliver and manage reliable power to electronic equipment, servers, and network/telecom devices

Stay informed about your power with the CyberPower PDU33103 monitored 3-Phase PDU. Ideal for data centers and network closets, this unit provides power monitoring in real time over the network by using the CyberPower management console and the RJ45 Ethernet port for network connection or locally by using the LCD.

The PDU33103 supports a 208V 20A input and includes 44 outlets. Other features include an interactive digital display with selectable background color, high operating temperature range, built-in web interface, and power event notifications. The CyberPower PDU33103 is protected by a three-year limited warranty.

Typical Applications

- Corporate Servers
- Network Closets
- Data Centers

Features

- Phase: 3-Phase
- Notifications: Email, SMS Text, and SNMP Trap
- Amps: 20A (Derated to 16A)
- Volts: 208V
- Frequency: 50/60Hz
- Input plug type: NEMA L21-20P
- Outlets: (2) NEMA 5-20R + (36) IEC-320 C13 + (6) IEC-320 C19
- Size: 0U Rackmount
- Cord Length (ft): 10
- Dimensions (in): 2.2W x 70.5H x 2.2D
- Warranty: 3 year

SPECIFICATIONS

GENERAL

Type Monitored

INPUT

Nominal Input Voltage 208 VAC

Input Frequency Range 50 Hz - 60 Hz

Input Plug Type NEMA L21-20P

Cord Length 10 ft (3m)

Maximum Input Current 20A

Derated Input Current 16 A

Phase 3-Phase

OUTPUT

Nominal Output Voltage 208 VAC, 120 VAC

Outlet Types 2 - NEMA 5-20R + 36 - IEC-320 C19 + 6 - IEC-320 C19

Outlets - # of Banks 3

Outlets - Total 44

PHYSICAL

Rack Height 0U

Physical Dimensions - (WxHxD) (cm) 5.59 x 179.07 x 5.59 (cm)

Physical Dimensions - (WxHxD) (in) 2.2 x 70.5 x 2.2 (in)

Physical Dimensions - (WxHxD) (mm) 56 x 1791 x 56 (mm)

Material of Construction Metal

Cord Retention Tray/Cord Organizers Yes

Adjustable Mounting Brackets 1 set

Color Black

PDU33103 | MONITORED PDU SERIES



SPECIFICATIONS CONT.

MANAGEMENT & COMMUNICATION

Monitoring Level	Input, Per Circuit
Software (Free Download)	PowerPanel® Business
Modular Expandability (Cascading)	Yes, via RJ45
Protocols	IPv4, TCP/IP, UDP, SNMPv1, HTTP, NTP, DNS, Telnet, DHCP, SMTP, FTP, IPv6, SNMPv3, HTTPs, SSH, SSL, TLS, LDAP(S), RADIUS, Syslog, CLI, Windows AD
Environmental Sensor	Optional, via RJ45
LED Indicators	Tx/Rx, LINK, Normal/Warning/Critical Status
Upgradeable firmware	Yes
LCD	Multifunction LCD

ENVIRONMENTAL

Operating Temperature	23 - 140 °F (-5 - 60 °C)
Operating Elevation	0 - 11480 ft (0 - 3499 m)
Operating Relative Humidity	0 - 95 % (non-condensing)

CERTIFICATIONS

Environmental	RoHS Compliant
Safety	UL60950-1 UL62368-1 FCC Class A

WARRANTY

Product Warranty	3 Year Limited Warranty
------------------	-------------------------