



PDU33110 | MONITORED PDU SERIES



Deliver and manage reliable power to electronic equipment, servers, and network/telecom devices

Stay informed about your power with the CyberPower PDU33110 monitored 3-Phase PDU. Ideal for data centers and network closets, this unit provides power monitoring in real time over the network by using the CyberPower management console and the RJ45 Ethernet port for network connection or locally by using the LCD.

The PDU33110 supports inputs between 200-240V and includes 18 IEC-320 outlets. Other features include an interactive digital display with selectable background color, built-in web interface, and power event notifications. The CyberPower PDU33110 is protected by a three-year limited warranty.

Typical Applications

- Corporate Servers
- Network Closets
- Data Centers

Features

- Phase: 3-Phase
- Notifications: Email, SMS Text, and SNMP Trap
- Amps: 60A (Derated to 48A)
- Volts: 200V-240V
- Frequency: 50/60Hz
- Input plug type: Hubbell CS8365C
- Outlets: (6) IEC-320 C13 + (12) IEC-320 C19
- Size: 0U Rackmount
- Cord Length (ft): 10
- Dimensions (in): 2.2W x 70.5H x 2.2D
- Warranty: 3 year

SPECIFICATIONS

GENERAL	
Type	Monitored
INPUT	
Nominal Input Voltage	200 - 240 VAC
Input Frequency Range	50 Hz - 60 Hz
Input Plug Type	IEC-309 60A Blue (3P+E)
Cord Length	10 ft (3m)
Maximum Input Current	60A
Derated Input Current	48 A
Phase	3 Phase
OUTPUT	
Overload Protection	20A X 6
Nominal Output Voltage	200 - 240 VAC
Outlet Types	6 - IEC-320 C13 + 12 - IEC-320 C19
Outlets - # of Banks	6
Outlets - Total	18

PHYSICAL	
Rack Height	0U
Physical Dimensions - (WxHxD) (cm)	5.59 x 179.07 x 5.59 (cm)
Physical Dimensions - (WxHxD) (in)	2.2 x 70.5 x 2.2 (in)
Physical Dimensions - (WxHxD) (mm)	56 x 1791 x 56 (mm)
Material of Construction	Metal
Cord Retention Tray/Cord Organizers	Yes
Adjustable Mounting Brackets	1 set
Color	Black

PDU33110 | MONITORED PDU SERIES



SPECIFICATIONS CONT.

MANAGEMENT & COMMUNICATION

Monitoring Level	Input, Per Circuit
Software (Free Download)	PowerPanel® Business
Modular Expandability (Cascading)	Yes, via RJ45
Protocols	IPv4, TCP/IP, UDP, SNMPv1, HTTP, NTP, DNS, Telnet, DHCP, SMTP, FTP, IPv6, SNMPv3, HTTPs, SSH, SSL, TLS, LDAP(S), RADIUS, Syslog, CLI, Windows AD
Environmental Sensor	Optional, via RJ45
LED Indicators	Tx/Rx, LINK, Normal/Warning/Critical Status
Upgradeable firmware	Yes
LCD	Multifunction LCD

ENVIRONMENTAL

Operating Temperature	23 - 131 °F (-5 - 55 °C)
Operating Elevation	0 - 11480 ft (0 - 3499 m)
Operating Relative Humidity	0 - 95 % (non-condensing)

CERTIFICATIONS

Environmental	RoHS Compliant
Safety	UL60950-1 UL62368-1 FCC Class A

WARRANTY

Product Warranty	3 Year Limited Warranty
------------------	-------------------------