

Philips Signage Solutions C-Line Display

86"

Powered by Android 350 cd/m<sup>2</sup>

**Signage**Solutions



86BDL6051C

# Interactive meeting display

high-end capacitive multi-touch technology

Maximise engagement and inspire collaboration with an interactive Philips C-Line display. These Android-powered displays are made to withstand heavy daily usage and feature up to 10 touchpoints, edge-to-edge glass and a flush design.

### Interactive and collaborative

- · Wireless screen sharing and advanced collaboration
- HID Capacitive Touch with USB Plug and Play
- Operate, monitor and maintain with CMND and Control

### Smart and powerful

- Anti-glare toughened glass
- Install and use your preferred apps and features
- · Whiteboard mode built in
- · Fast and easy video conferencing
- Crestron Connected certified
- · OPS slot allows for PC embedding without cabling
- Android SoC processor. Native and web apps



## Highlights

### Wireless screen sharing

Display four feeds on the one screen. Wireless screen sharing allows you to connect multiple devices at the same time for quick content switching when you need it. Use your existing Wi-Fi network to instantly and securely connect devices or use our optional HDMI interact dongles to cast directly to the screen without needing to connect to your secured/protected network.

### **HID Capacitive Touch**

Capacitive Touch gives you the cutting edge appearance of edge to edge glass with a bezel width of just 1.5 mm! Create a memorable interactive experience with up to 10 touchpoints at the same time. Perfect for collaborative and competitive applications, this display connects your audience with any content — making it ideal for education, public venues, corporate, hospitality and retail settings.

### **CMND** and Control



Run your display network over a local (LAN) connection. CMND and Control allows you to

perform vital functions like controlling inputs and monitoring display status. Whether you're in charge of one screen or 100.

### Whiteboard mode built in

Inspire agile collaboration with whiteboard mode. Simply activate this feature to turn your display into a blank canvas that can be drawn on by multiple users by hand or with dedicated display markers. Everything on the screen can then be captured for easy printing or file sharing.

### Fast and easy video conference

Ready to use video conferencing software makes one-to-one or group video calls easier than ever. Simply use your own camera or add the optional Logitech Meetup bundle for an all-in-one ConferenceCam solution.

### **Crestron Connected certified**

Integrate this Philips Professional Display to your Crestron network for full remote control via your laptop, desktop or mobile device. Switch the display on and off, schedule content, manage settings and easily connect external devices. Crestron Connected<sup>®</sup> provides a fast, reliable and secure enterprise level solution for system control.

#### **OPS** slot



Integrate a full-power PC or Android-powered CRD50 module directly into your Philips Professional Display. The OPS slot contains all the connections you need to run your slot-in solution, including a power supply.

### **Powered by Android**

Control your display via an Internet connection. Android-powered Philips Professional Displays are optimised for native Android apps and you can install web apps directly to the display too. A new Android OS ensures the software is kept secure and stays up to date with the latest specification for longer.









Size 180 mm x 300 mm

Convenience

(12/7)

**Power** 

Sound

Accessories

VESA Mount: 600(H)x400(V) mm, M8

· Keyboard control: Hidden, Lockable · Signal loop through: RS232, IR Loop through

• Network controllable: RJ45, RS232

· Ease of installation: Smart Insert

• Consumption (Typical): 300 W

Consumption (Max): 500 W

**Operating conditions** 

· Energy Label Class: G

5~95% (storage) %

 Altitude: 0 ~ 3000 m • MTBF: 50,000 hour(s)

· DPMS power saving system

• Energy-saving functions: Smart Power

 Standby power consumption: <0.5 W</li> • Mains power: 100 ~ 240 VAC, 50 ~ 60 Hz

• Temperature range (operation): 0 ~ 40 °C

• Temperature range (storage): -20  $\sim$  60  $^{\circ}$ C

· Relative humidity: 20~80% (operating),

• Built-in speakers: 2 x 20 W RMS

• Smart Insert mount: 6\*M4\*L6, 100 mm pitch, Max.

• Placement: Landscape, Landscape (18/7), Portrait

Screen-saving functions: Pixel Shift, Low Bright

### **Specifications**

### Picture/Display

- Diagonal screen size: 85.6 inch / 217.42 cm
- Panel resolution: 3840 x 2160
- Optimum resolution: 3840 x 2160 @ 60 Hz
- Brightness: 350 cd/m<sup>2</sup>
- Contrast ratio (typical): 1000:1
- Dynamic contrast ratio: 500,000:1
- Aspect ratio: 16:9
- Response time (typical): 8 ms
- Pixel pitch: 0.4935 (H) x 0.4935 (V) mm
- Display colours: 1.07 billion
- Viewing Angle (H / V): 178 / 178 degree
- Picture enhancement: 3/2 2/2 motion pull down, Motion compens. deinterlacing, 3D MA deinterlacing, Dynamic contrast enhancement, Progressive scan
- Operating system: Android 9

### **Connectivity**

- Video input: Display Port1.2 (x 1), HDMI 2.0 (x 4), DVI-I (x 1), USB 2.0 (x 2), USB 3.0 (x 2), USB-C
- Video output: DisplayPort 1.2 (x 1), DVI D (x 1), HDMI 2.0 (x 2)
- Audio input: 3.5 mm jack
- Audio output: 3.5 mm Jack (x 2)
- Other connections: OPS, micro SD
- External control: RJ45, RS232C (in/out) 2.5 mm jack, IR (in/out) 3.5 mm jack

### **Supported Display Resolution**

Computer formats

Resolution	Refresh rate
1920 x 1200	60 Hz
$1920 \times 1080$	60 Hz
$1680 \times 1050$	60 Hz
1600 x 1200	60 Hz
$1600 \times 900$	60 Hz
1440 x 1050	60 Hz
$1440 \times 900$	60, 75 Hz
1400 x 1050	60, 75 Hz
$1366 \times 768$	60 Hz
$1360 \times 768$	60 Hz
$1280 \times 1024$	60, 67, 75 Hz
$1280 \times 960$	60 Hz
$1280 \times 800$	60, 75 Hz
$1280 \times 768$	60 Hz, 75 Hz
$1280 \times 720$	60, 70 Hz
$1152 \times 900$	66 Hz
1152 x 864	60, 70, 75 Hz
$1024 \times 768$	60, 70 Hz
$960 \times 720$	75 Hz
$848 \times 480$	60 Hz
$832 \times 624$	75 Hz
$800 \times 600$	56, 60, 72, 75 Hz
$720 \times 400$	70 Hz
$640 \times 350$	70 Hz
$640 \times 480$	60, 67, 72, 75 Hz

Video formats

Resolution	Refresh rate
1080 <sub>P</sub>	50, 60 Hz
576p	50 Hz
480p	60 Hz
1080i	50, 60 Hz
4K x 2K	50, 60 Hz
720 <sub>D</sub>	50, 60 Hz

• UHD Formats: 3840 x 2160, 24, 25, 30, 60 Hz,

### **Dimensions**

- Set dimensions (W x H x D): 1949.00 x 1120.00 x 77.50 (@wall mount), 93.00 (@max) mm
- Set dimensions in inch ( $W \times H \times D$ ): 76.73 x 44.09 x 3.05 (@wall mount), 3.66 (@max) inch
- · Bezel width: 1.50 mm(even)
- Product weight (lb): 172.18 lb
- Product weight: 78.1 kg

3840 x 2160, 50 Hz

### **Multimedia Applications**

USB Playback Audio: AAC, M4A, MP3, WMA

• Included Accessories: Philips logo (x 1), RS232 Daisy chain cable (x 1), AAA batteries (x 1),

Cleaning cloth (x 1), DVI-I Cable (1.8 m) (x 1)

(x 3), Quick start guide (x 1), Remote control

(x 1), RS232 cable (3 m) (x 1), Touch Pen (x 2),

USB A to B cable (3 m) (x 1), USB Cover (x 1)

HDMI Cable (3 m) (x 1), IR sensor cable (1.8 m) (x 1), M2 Screw (x 2), M3 screw (x 2), Power cable

- USB Playback Picture: BMP, JPEG, JPG, PNG
- · USB Playback Video: ASF, AVI, FLV, MKV, MP4, MPEG, MPG, TS, VOB, WEBM, WMV, DAT

### **Miscellaneous**

- On-Screen Display Languages: English, French, German, Spanish, Polish, Turkish, Russian, Italian, Simplified Chinese, Traditional Chinese, Arabic, Japanese, Danish, Dutch, Finnish, Norwegian, Portuguese, Swedish
- Regulatory approvals: CE, RoHS, CB, CU, EAC, EMF, ETL, FCC, Class A, PSB, VCCI
- · Warranty: 3 year warranty

### **Internal Player**

- CPU: MTK5680
- · Storage: 32 GB eMMc
- Micro SD Card: Support to 1TB
- RAM: DDR4 4 GB
- Wi-Fi: AP(WC0SR2511-88112BU), STA(WCT5GM2511MT7668AU)

### **Multi-touch Interactivity**

• Touch points: 10 simultaneous touch points





Issue date 2022-04-21

© 2022 Koninklijke Philips N.V. All Rights reserved.

or their respective owners.

Version: 3.1.1 Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V.

12 NC: 8670 001 70217 EAN: 87 12581 77088 4

www.philips.com