

## USB-C to HDMI over Cat6 Extender Kit with KVM Support, 4K 60Hz, 4:4:4, Transmitter/Receiver, USB, PoC, HDCP 2.2, up to 230 ft., TAA

MODEL NUMBER: B127A-1A1-BCBH



Transmitter/receiver kit extends a 4K signal via Cat6 cable from a USB-C source to an HDMI display up to 230 ft. away.

### Features

#### USB-C to HDMI Extender Kit Ideal for Digital Signage in Schools, Restaurants and Lecture Halls

This complete transmitter and receiver system is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow.

#### Supports USB DisplayPort Alternate Mode for Converting Audio/Video Signals

By connecting a USB-C cable to a source device that supports DisplayPort Alt Mode, you can output 4K video and digital audio to an HDMI monitor, television or projector without installing special software drivers.

#### Extends a 4K A/V Transmission up to 230 ft....or More

The B127A-1A1-BCBH extends 4K signals from a USB-C source device to an HDMI display up to 230 feet away via user-supplied Cat6 cabling. By adding a Tripp Lite B127A-010-H HDMI repeater or B127A-110-BH transceiver (sold separately) to the application, you can extend the signal up to 400 or 460 feet, respectively.

#### Dip Switch Extends Your Choice of Either USB or IR.

The DIP switches on both the transmitter and receiver can be adjusted to let you choose from the USB 1.1 or bi-directional IR functions. Choose to either control the source device via keyboard and mouse or IR remote control from the display end of the installation. Only one function can be extended at a time.

#### Transmits Crystal-Clear 4K Video with Multi-Channel Audio and 4:4:4 Color

The B127A-1A1-BCBH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz, as specified by HDMI 2.0, with full, rich uncompressed DTS-HD, Dolby TrueHD and 7.1-channel digital audio. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This extender kit also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. Built-in equalization allows you to fine-tune the image quality at the remote display.

#### Local HDMI Port on Transmitter Supports 4K @ 60 Hz Resolution

To monitor the video signal being extended to the receiver, connect a 4K display to the transmitter's local HDMI port with a user-supplied HDMI cable. This port does not support multi-resolution capabilities, so the connected monitor must also support 4K/60 Hz to function properly.

#### Built-In PoC Technology Provides Power to Avoid Bulky External Power Bricks

After you connect the included external power supply to either the transmitter or receiver, Power over Cable (PoC) technology powers the opposite unit over Cat6 cable. LEDs on both the transmitter and receiver will light up to indicate the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to place one unit where needed without worrying about finding a nearby AC outlet.

#### PD 3.0 Charging Port Powers the Source Device to Maintain a Clear Signal

### Highlights

- Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Power over Cable (PoC) technology provides power to either end via Cat6 cable
- USB-C PD 3.0 port charges source device to avoid battery drain and untimely shutdowns
- DIP switch selection allows bi-directional IR or USB function for controlling the source
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Applications

- Connect a MacBook Pro, Windows laptop or notebook to a 4K display in a large conference room or meeting room for a video or PowerPoint presentation
- Extend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codes
- Gain flexibility in where the receiver is placed, with the freedom to move and relocate it away from an AC outlet
- Improve the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location
- Stream Netflix, Amazon Prime, Hulu and other home



The USB-C Power Delivery port provides up to 20V 5A (90W, with 10W dedicated to the unit's power reserve) for powering the connected source device when using an E-Mark USB-C cable (such as Tripp Lite's U040-C13-C-5A). With a non-E-Mark cable, the USB-C PD 3.0 port provides up to 20V 3A (50W, with 10W to the power reserve). The other USB-C port connects the transmitter to the source.

**Plug-and-Play Operation for Quick Setup and Immediate Use**

The included transmitter and receiver units work right out of the box with no software required. Mounting hardware is included for installing both units on a wall, pole or 19-inch rack. Connect the transmitter to the source with a user-supplied USB-C cable. Then, connect the receiver to the display with a user-supplied HDMI cable (such as Tripp Lite's P568- or P569-Series). Finally, connect the two units with user-supplied Cat6 patch cable (such as Tripp Lite N202-Series).

**TAA-Compliant for GSA Schedule Purchases**

The B127A-1A1-BCBH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

entertainment channels to your HDTV or projector

**System Requirements**

- Source device with USB-C output (MacBook Pro, Windows laptop, tablet, smartphone) that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDTV, projector, monitor)

**Package Includes**

- Transmitter
- Receiver
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332258663
Product Type	Extender Kit
Technology	Cat5/5e; Cat6; HDMI; POC; USB
VIDEO	
Video Input	USB C (FEMALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	2
Video Ports	(2) HDMI (FEMALE)
Video Ports Detail	HDMI 2.0; HDCP 2.2



Resolutions Supported	3840 x 2160 (4K x 2K) @ 60 Hz (Both Local HDMI port and monitor connected to receiver unit via A/V over Cat6)
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 1920 x 1200 Range (ft)	230
Max 2560 x 1600 Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Transmitter Video Input	USB-C
Transmitter - Number of Video Outputs	1
Transmitter - Local Display Output	HDMI
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230
Signal Range (m)	70
Range Extension using other Tripp Lite product	170ft or 230ft
Recommended Cabling	Solid Wire Cat6 Cables (Tripp Lite's N202-Series)
Extended Mode	Yes
Extended Mode Details	x1 HDMI (4K/60 Hz)
Mirror Mode	Yes
Mirror Mode Details	x1 HDMI (4K/60 Hz)
Other Tripp Lite product used to extend range	B127A-010-H or B127A-110-BH
Max Supported Color Depth	36-bit True Color
HDR Support	No
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
<b>AUDIO</b>	
Audio Ports	HDMI (FEMALE)
Audio Ports Detail	Supports Pass-through of Audio format including LPCM2.0/5.1/7.1, and a built-in TOSLINK audio port on the receiver.
Audio Input	USB-C
Audio Output	Toslink; HDMI
Audio Specification	Pass-through audio (LPCM 2.0/5.1/7.1)



<b>INPUT</b>	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
Bus Powered	No
<b>POWER</b>	
Power Source	Transmitter or Receiver (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P; BS1363; CEE 7/16 Schuko; AS/NZS 3112
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.6A
External Power Supply Output Specs (V / A)	24V/1A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply Certifications	CE; FCC; CCC; GS; TUV; UL; cUL
Receiver Power Source	AC Adapter (Included); Power Over Cable
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	3.0; 100W; 20V/5A
Power Over Cable (PoC) Support	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	TX: Green (Power); RJ45 Port: Green (Connection), Orange (Activity); RX: Green (Power), RJ45 Port: Green (Connection), Orange (Activity)
<b>CHARGING</b>	
Charging Ports	Supports 60W (20V 3A) Power to Host Computer; USB-C: 100W (20V 5A) Power Delivery (PD 3.0)
Charging Port Type	USB C (FEMALE)
<b>PHYSICAL</b>	
Color	Black
Included Mounting Accessories	Wallmount
Material of Construction	Metal
Number of Displays	1
Form Factor/Mounting Options	Box; Wall-mount
Rackmountable	No



Receiver Unit Dimensions (hwd / cm.)	2.7 x 11.5 x 6.24
Receiver Unit Dimensions (hwd / in.)	1.063 x 4.528 x 2.457
Receiver Unit Weight (lbs.)	1
Transmitter Unit Dimensions (hwd / cm.)	2.7 x 11.5 x 6.24
Transmitter Unit Dimensions (hwd / in.)	1.063 x 4.528 x 2.457
Transmitter Unit Weight (lbs.)	1
Unit Packaging Type	Box
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104°F (0 to 40°C)
Storage Temperature Range	5 to 122°F (-15 to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	230
Signal Range (m)	70
Transmission Distance	230 ft.
EDID Compatible	Yes
IR Remote Extension Support	Yes
Consumer Electronics Control (CEC) Supported	Yes
Latency	Zero-Latency
USB Extension Support	Yes
<b>CONNECTIONS</b>	
Side A - Connector 1	(2) USB C (FEMALE)
Side A - Connector 2	HDMI (FEMALE)
Side A - Connector 3	RJ45 (FEMALE)
Side A - Connector 4	(2) 3.5MM (FEMALE); MICRO-USB B (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	(2) USB A (FEMALE)
Side B - Connector 4	TOSLINK (FEMALE); (2) 3.5MM (FEMALE)
Side B - Connector 5	(2) USB A (FEMALE)
Side A - Connector 5	HDMI (FEMALE)



<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4; 2.2
USB Specification	USB 1.1 (up to 12 Mbps)
Driver Required	No
Recommended Category Cable	Cat6
<b>SPECIAL FEATURES</b>	
MST Support	No
Included Mounting Accessory	Yes
Multi-Resolution Support	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, REACH, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>