


## Key Features

- Slim, freestanding design for modern settings
- Exceptional picture quality
- Superb processing power with built-in quad-core media player
- Total remote control with RS232 commands within Local Area Network
- Effortless integrated device and content management



## Product Description

Uber-sleek and slim, the freestanding ViewSonic EP5542 is the ideal digital ePoster kiosk for high-impact visual messaging. Designed with a scratch-proof glass faceplate for added durability, it delivers unsurpassable visibility regardless of dust or ambient light. The 4K UHD IPS panel is equipped with dual 10W stereo speakers, 178° wide-angle viewing, and 450 nits of brightness, projecting crisp, vivid images and videos to engage the crowd. The EP5542 allows seamless multimedia playback with its embedded Quad-core media player and 16GB worth of internal memory. Made for effortless remote control, manage settings of multiple devices wherever via the vController app integrated with RS232 and LAN command.



- 1. RJ45(LAN In)
- 2. RS232
- 3. Audio Out
- 4. SPDIF
- 5. PC In(Audio)
- 6. PC In(VGA)
- 7. USB 2.0(Type A)

- 8. HDMI In x3
- 9. DP In
- 10. AC Out
- 11. Power Switch
- 12. AC In
- 13. RJ45
- 14. USB 2.0(Type A) x2

- 15. Remote Sensor
- 16. Internal Speakers

Visit Us  [www.viewsonic.com](http://www.viewsonic.com)

## DISPLAY

Panel Size:	55"
Type/Tech:	TFT LCD (VA type,DLED Backlight)
Display Area (mm):	1209.6 (H) x 680.4 (V)
Aspect Ratio:	9:16
Native Resolution:	2160 x 3840
Colors:	1.07B
Brightness:	450 nits (typ.)
Contrast Ratio:	1300:1 (typ.)
Response Time:	9 ms (typ. G to G)
Viewing Angles:	H = 178, V = 178 typ.
Backlight Life:	30,000 Hours Typ.
Surface Treatment:	Anti-Glare 3H, Haze = 2%
Orientation:	Portrait

## INPUT

HDMI:	(2.0) x 3
RGB / VGA:	x1
DisplayPort:	(1.2) x 1
Audio:	x1 PC audio(3.5 mm)
RS232:	x1

## OUTPUT

Audio:	x1 (Earphone out)
SPDIF:	x1

## LAN

RJ45:	x1
-------	----

## USB

Type A:	x3 (2.0)
---------	----------

## SPEAKERS

10W x 2

## COMPATIBILITY

RGB PC/HDMI PC:	1920 x 1080 @60Hz
HDMI:	2160 x 3840 @60Hz
DisplayPort:	2160 x 3840 @60Hz

## ANDROID VERSION

8.0

## MULTIMEDIA

Image: JPG, BMP, PNG  
Video: MP4, MOV, MKV, DAT, MPG, MPEG, AVI, TS, WMV, RM, RMVB  
Audio: MP3, WAV, AAC

## BUNDLE SOFTWARE

Revel Digital, SureMDM(license sold separately)

## POWER

Voltage:	100-240VAC +/- 10% Wide Range
Consumption:	126 W (Normal), 149 W (Max.), < 0.5W (Off)

## OPERATING CONDITIONS

Temperature (° C):	0°C to 40°C
Humidity:	20% ~ 80% non-condensing

## DIMENSIONS (W X H X D)

Physical (inch / mm):	30.26 x 73.62 x 17.72 in / 768.5 x 1870 x 450 mm
Packaging (inch / mm):	38.19 x 80.08 x 23.98 in / 970 x 2034 x 609 mm

## WEIGHT

Net (lb / kg):	138.23 lbs / 62.7 kg
Gross (lb / kg):	164.69 lbs / 74.7 kg

## REGULATIONS

cTUVus, FCC, Energy Star 8.0, CE, CB, RoHS, ErP, EEI, WEEE, BSMI

## PACKAGE CONTENTS

1. Power Cord
2. Remote control with battery
3. Quick Start Guide
4. Key \*Actual content may differ from market to market