



DXZ4

PCoIP zero client

Benefits and Features

Key Features

- Supports high-resolution displays: quad video up to 1920x1200, dual video up to 3440x1440
- Connect multiple DXZ4 clients to support additional displays such as octal video up to 1920x1200 or quad video up to 3440x1440
- Exceptional performance including real-time video and demanding 3D graphics
- Connect to virtual desktops, cloud managed desktops or for the most demanding graphics, connect to remote physical or virtual workstations
- Easy to configure and manage
- Optional under the desk bracket available

Network connections

- Supports redundant network connections with dual network interfaces with options for SFP modules for copper or fiber optic cabling
- Supports remote connections that can be local, across country, or continent-to-continent

Security

- Only display pixels are sent to the client so no sensitive data ever reaches the client
- Zero Clients have no X86-processor, no Windows or Linux client OS, no client GPU and no local storage. This eliminates exploits common with other client endpoints
- Extensive security features including support for 256-bit AES encryption, NSA Suite-B ciphers, smart card, proximity card, SIPR tokens and much more

Compact and highly secure PCoIP zero client


The Amulet Hotkey DXZ4 is a quad video head PCoIP® zero client, designed to provide class leading, long-term performance in the most demanding of applications. The DXZ4 provides an extensive set of unique and advanced features not found in other remote computing solutions.

Connect a DXZ4 to a remote PCoIP host such as VMware Horizon, Amazon Workspaces or a range of Amulet Hotkey workstations. This provides quad video head, pixel perfect performance at the desktop, a very low noise and heat signature, and connection points for the widest range of USB and audio peripherals. Dual redundant network ports, locking power sockets and a configurable control panel enhance resilience where it is needed most.

UK Government Security Certification

The DXZ4-A and DXZ4-AM zero client have been certified as secure by CESG, the National Technical Authority for Information Assurance within the UK. The CESG assists Government Departments with cyber security and have certified and approved the DXZ4-A/AM for use at the 'OFFICIAL' level within Government and public sector organizations.

TEMPEST versions of this product, approved to NATO SDIP-27 Level A and Level B by our TEMPEST-certified CESG and NATO partners, are available on special request. Contact Amulet Hotkey sales for more information.



DXZ4-M rear view: 1 Network connections. 2 DisplayPort sockets. 3 USB ports. 4 Audio socket. 5 DC inlet. 6 SFP modules. 7 Under-desk bracket (optional).




Getting connected

DXZ4 zero clients support any user type from mainstream office desktops for task workers to the most demanding 3D performance workstations. Connection options include virtual desktops such as VMware Horizon, Cloud Managed Desktops such as Amazon Web Services Workspaces, or remote physical or virtual workstations for demanding users.

The PCoIP host can be implemented in hardware or in software, using VMware Horizon or Amazon Workspaces. The PCoIP host encodes USB, audio and video from the host and then compresses and encrypts the data for transmission across standard IP networks to the zero client.

The zero client decrypts and decompresses the data, and delivers it to the desktop. The zero client also passes user-generated USB and audio data to the PCoIP host. The result for the user is that the desktop looks and feels like it is at their desk. Because zero clients simply decode pixels to display images, they are simpler and more secure than a traditional PC and other thin client solutions.



Sales

EMEA Sales
+44 (0)20 7960 2400
emeasales@amulethotkey.com

N America Sales
+1 (212) 269 9300
ussales@amulethotkey.com

APJ Sales
+61 409 930 884
apsales@amulethotkey.com

LATAM Sales
latamsales@amulethotkey.com

Defence and Security
security@amulethotkey.com

Support



www.amulethotkey.com/support

DS-DXZ4-0001 v8.0 July 2022

©2022 Amulet Hotkey Ltd (AHK). All rights reserved. Contents must not be reproduced without prior permission. Information in this document is subject to change. AHK may have patents, patent applications, trademarks, copyrights or other intellectual property rights covering subject matter in this document. AHK is a registered trademark of Amulet Hotkey Ltd. Other product names and company names listed within this document may be trademarks of their respective owners.

Specifications

Processor	Teradici Tera2140 PCoIP processor
Memory	512MB DDR3 RAM
Video output	4 x DisplayPort connectors (dual mode)
Display support (quad)	Four monitors up to 1920 x 1200 maximum @ 60 Hz
Display support (dual)	Two 2560 x 1600 maximum with AHK KVM Extender Host @ 60 Hz, or; Two 3440 x 1440 maximum with VMware Horizon virtual workstations @ 60 Hz
Audio connections	Stereo headset/headphones, stereo line out, stereo mic. All 3.5mm jacks
Audio range	Output: 0Hz to 21.6kHz (48kHz sampling); 0Hz to 19.846kHz (44.1kHz sampling) Input: 10Hz to 21.6kHz (48kHz sampling); 10Hz to 19.846kHz (44.1kHz sampling)
USB connections	4 x USB 2.0
Network connections	DXZ4, DXZ4-A: Dual redundant RJ45 10/100/1000 for copper cabling DXZ4-M, DXZ4-AM: Dual redundant SFP slots for 100Mb/s or 1Gb/s fiber or copper modules
Cooling	Passive
Case	Robust enclosure
Power consumption	Less than 12W nominal (excluding USB devices)
Temperature range	Operating: 15° to 40° C (59° to 104° F) Storage: -10° to 60° C (14° to 140° F)
Size (H x W x D)	34 x 230 x 130 mm (1.3 x 9.1 X 5.1"). Weight: 0.9 kg (2 lbs)
Security	Strong encryption and authentication including 256-bit AES and NSA Suite-B ciphers. 2 factor authentication options including CAC/PIV cards, smart cards, prox-cards, e-tokens, SIPR tokens. IEEE 802.1X network authentication. Unique USB lockdown control. Kensington Lock slot
Compliance	TAA compliant. Conforms to relevant parts of EN55024, EN55022, FCC Part 15. TEMPEST versions of the DXZ4 are available, approved to NATO SDIP-27 Level A and Level B by our TEMPEST-certified CESG and NATO partners