

PERFORMANCE**Processor**

Intel® Core™ i5-1145GRE (4C / 8T, 1.5 / 4.1GHz, 8MB)

Graphics

Integrated Intel Iris® Xe Graphics

Chipset

Intel SoC Platform

Memory

16GB Soldered DDR4-3200

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

16GB soldered memory, not upgradable

Storage

512GB SSD M.2 2230 PCIe 3.0 NVMe

Storage Support

Up to two drives, 2x M.2 2230 SSD

- M.2 2230 SSD up to 1TB each

- RAID 0/1 support

Power Supply

65W 89% Adapter

DESIGN**Keyboard**

Calliope Wireless Keyboard, Black, French

Mouse

None

Case Color

Black

Mounting

None

Dimensions (WxDxH)

179 x 88 x 51.5 mm (7.05 x 3.46 x 2.03 inches)

Weight

Models Weight

ThinkEdge SE30 1.02 kg (2.25 lbs)

IO box 0.499 kg (1.10 lbs)

CONNECTIVITY**Ethernet**

1x Gigabit Ethernet + 1x 2.5 Gigabit Ethernet

Front Ports

- 1x USB-C 3.2 Gen 2 (support data transfer and display)
- 2x serial (RS232 / RS422 / RS485, BIOS selectable)
- 2x USB 3.2 Gen 2
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 1x DisplayPort™ 1.4a (for i5 models)
- 1x power connector
- 1x USB 3.2 Gen 2
- 1x Thunderbolt™ 4 / USB4™ 40Gbps (support data transfer, Power Delivery 5V@3A, and display)
- 2x Ethernet (RJ-45)

Monitor Cable

1x USB-C to HDMI®

SECURITY & PRIVACY**Security Chip**

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington® Security Slot

MANAGEABILITY**System Management**

vPro

SERVICE**Base Warranty**

3-year, Onsite

Included Upgrade

None

ENVIRONMENTAL**Operating Temperature**

Wide Temperature -20°C to 60°C (-4°F to 140°F)

CERTIFICATIONS**Green Certifications**

- PCF
- REACH
- ErP Lot 6
- RoHS compliant
- WEEE
- Low Halogen
- TED (ECO-declaration)

SOFTWARE**Operating System**

Windows® 10 IoT Enterprise, French

MODEL

TopSeller : Yes

Announce Date : 2021-04-27

EAN / UPC / JAN : 195890242248

End of Support : 2027-11-27



intel

WLAN + Bluetooth®

Intel 9260 11ac, 2x2 + BT5.1, vPro

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Recommended Services

BEST	-
BETTER	-
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WSOV07841)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference