

# **HPE PROLIANT DL345 GEN10 PLUS 7443P 2.85GHZ 24-CORE 1P 32GB-R 8SFF 800W PS SERVER (P39267-B21)**

## **ProLiant DL300 Servers**



---

### **WHAT'S NEW**

- Provide versatility and upgradeability for storage with one processor in a 2U rack enclosure.
- Powered by the 3rd Generation AMD EPYC™ 7000 Series Processor with more compute performance compared to the previous generation.
- Enhanced storage management with Tri-mode storage controllers supporting NVMe/SAS/SATA drives.

### **OVERVIEW**

Do you need a single socket server with a 2U rack storage capacity to address your data intensive workloads?

Building on HPE ProLiant as the intelligent foundation for hybrid cloud, the HPE ProLiant DL345 Gen10 Plus server offers the 3rd Generation AMD EPYC™ 7000 Series Processor, delivering excellent performance on a single socket design. Equipped with PCIe Gen4 capabilities, HPE ProLiant DL345 Gen10 Plus server offers improved data transfer rates and higher networking speeds. Enclosed in a 2U server chassis, this one-socket server improves storage capacity across SAS/SATA/NVMe storage options, making it an ideal solution for key applications such as structured/unstructured database management.

## FEATURES

### Workload Optimization

Harness major compute power: The HPE ProLiant DL345 Gen10 Plus server supports the 3rd Generation AMD EPYC™ 7000 Series 64-core 280W processors.

It provides up to 128 lanes of PCIe Gen4 improves I/O throughput and reduces latency.

Tri-mode storage controllers enhance storage management coupled with an advanced storage RAID solution.

It provides real-time operational feedback on server performance plus recommendations for fine-tuning BIOS settings to customize for changing business needs.

### 360 Degree Security

The HPE ProLiant DL345 Gen10 Plus server is tied into the silicon root of trust and the AMD Secure Processor, a dedicated security processor embedded in the AMD EPYC system on a chip (SoC) to manage secure boot, memory encryption, and secure virtualization.

HPE ProLiant security begins with the corruption-free manufacture of the server and auditing the integrity of every component – hardware and firmware – to provide verification that the server begins its lifecycle through an uncompromised supply chain.

HPE ProLiant servers provide rapid detection of a security-compromised server, even to the point of not allowing it to boot, identifies and contains malicious code, and protect healthy servers.

HPE ProLiant servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of operating system, application, and data connections, providing the fastest path to bring a server back online and into normal operations.

When it's time to retire or repurpose an Hewlett Packard Enterprise ProLiant server, one button secure erase speeds and simplifies the complete removal of passwords, configuration settings and data, preventing inadvertent access to previously secured information.

### Intelligent Automation

The HPE ProLiant DL345 Gen10 Plus server simplifies and automates management tasks, establishing a solid foundation for an open, hybrid cloud platform enabled by composability.

Embedded in HPE servers, HPE Integrated Lights-Out (iLO) is an exclusive core intelligence that monitors server status, providing the means for reporting, ongoing management, service alerting, and local or remote management to quickly identify and resolve issues.

Automation and software defined control reduces time spent on provisioning and maintenance, and reduces deployment time.

### Delivered as-a Service

The HPE ProLiant DL345 Gen10 Plus server supported by HPE GreenLake simplifies IT infrastructure management across your entire hybrid estate. With 24x7 monitoring and management, our experts do the heavy lifting to manage your environment with services built into consumption-based solutions.



Rapidly deploy a broad portfolio of cloud services such as machine learning operations (ML Ops), containers, storage, compute, virtual machines (VMs), data protection, and more. Workload-optimized, preconfigured solutions can be delivered to your facility quickly, decreasing your downtime.

Hewlett Packard Enterprise provides customers choice in how they acquire and consume IT beyond traditional financing and leasing, offering options that free trapped capital, accelerate infrastructure updates, and provide on-premises pay-per-use consumption with HPE GreenLake.

## Technical specifications

### **HPE ProLiant DL345 Gen10 Plus 7443P 2.85GHz 24-core 1P 32GB-R 8SFF 800W PS Server**

<b>Product Number (SKU)</b>	P39267-B21
<b>Processor Name</b>	AMD EPYC™ 7443P (24 core, 2.85 GHz, 128 MB, 200W)
<b>Processor core available</b>	24 core
<b>Processor cache</b>	128 MB L3
<b>Processor speed</b>	2.85 GHz
<b>Power supply type</b>	1x 800W HPE FlexSlot Power Supply
<b>Expansion slots</b>	4 maximum, for detailed descriptions refer to the QuickSpecs
<b>Memory, standard</b>	32 GB (1x 32 GB) RDIMMs
<b>Memory type</b>	HPE DDR4 Smart Memory
<b>Included hard drives</b>	None ship standard, 8 SFF supported
<b>Optical drive type</b>	Optional, None ship standard
<b>System fan features</b>	6 standard fans
<b>Network controller</b>	HPE 10GbE 2-port OCP3 Adapter plus choice of OCP or standup card
<b>Storage controller</b>	HPE Smart Array P408i-a SR Gen10 Controller
<b>Product Dimensions (metric)</b>	8.75 x 44.54 x 71.1 cm
<b>Weight</b>	16.33 kg
<b>Infrastructure management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download) HPE iLO Advanced, HPE iLO Advanced Premium Security Edition, and HPE OneView Advanced (require licenses)
<b>Warranty</b>	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of on-site support coverage. Additional information regarding worldwide limited warranty and technical support is available at: <a href="http://h20564.www2.hpe.com/hpsc/wc/public/home">http://h20564.www2.hpe.com/hpsc/wc/public/home</a> . Additional HPE support and service coverage for your product can be purchased locally. For information on availability of service upgrades and the cost for these service upgrades, refer to the HPE website at <a href="http://www.hpe.com/support">http://www.hpe.com/support</a> .
<b>Drive supported</b>	None ship standard, 8 SFF supported

Most, if not all IT organizations are on a digital transformation journey — each at a different stage. With over 11,000 IT projects conducted and 1.4 million customer interactions each year, HPE Pointnext Services' 15,000+ experts and its vast ecosystem of solution partners and channel partners are uniquely able to help you at every stage of your digital transformation. We bring together technology and expertise to help you drive your business forward and prepare for whatever is next.

Advisory and Professional Services help you accelerate your digital transformation. Operational Services help you remove complexity and respond rapidly to business demands.

### Operational Services from HPE Pointnext Services

HPE Pointnext Tech Care provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

- **HPE Datacenter Care** helps modernize and simplify IT operations. Partner with an assigned account team, access technical expertise, an enhanced call experience gives you priority access, choose hardware and software support, implement proactive monitoring to help stay ahead of issues, and access HPE IT best practices and IP.
- **HPE Proactive Care** offers an enhanced call experience and helps reduce problems with personalized proactive reports and advice. This also includes collaborative software support for Independent Software Vendors (ISVs), (Red Hat, VMWare, Microsoft, etc.). [Read more](#)
- **HPE Foundation Care** helps when there is a problem and has a choice of response levels. Collaborative software support is included and provides troubleshooting help for ISVs running on your server. [Read more](#).

### Other related services

**Defective Media Retention** is optional and applies only to Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

**HPE Service Credits** offers a menu of technical services, access additional resources, and specialist skills.

**HPE Education Services** delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation.

Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.

For additional technical information, available models and options, please reference the QuickSpecs


## HPE GREENLAKE

HPE Greenlake is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

**Make the right purchase decision.**  
Contact our presales specialists.

[Find a partner](#)



© Copyright 2021 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

AMD EPYC™ is a trademarks of Advanced Micro Devices, Inc. All third-party marks are property of their respective owners.

Image may differ from the actual product  
[PSN1013486036IEEN](#), August, 2021.

**Hewlett Packard  
Enterprise**