

4-Port HDMI over Cat6 Splitter - 4K 60 Hz, HDR, 4:4:4, PoC, HDCP 2.2, 230 ft. (70.1 m), TAA

MODEL NUMBER: **B127A-004-BH**



Works with Tripp Lite B127A-Series receivers to extend a 4K audio/video signal 230 ft. via Cat6 cable to 4 HDMI displays.

Features

HDMI Quad-Output Splitter Ideal for Digital Signage in Schools and Workplaces

This 4K transmitter/splitter is recommended for video presentations in conference rooms, schools, trade shows, meeting facilities, houses of worship, retail settings, hotels and other digital signage applications where the source and display are farther apart than conventional A/V cables allow.

Extends a 4K A/V Transmission up to 230 ft....or Even Farther

The B127A-004-BH connects to Tripp Lite B127A-Series receivers to extend 4K signals from an HDMI source to four HDMI displays up to 230 feet (70.1 meters) away via user-supplied Cat6 cabling. By adding Tripp Lite B127A-010-H signal repeaters or B127A-110-BH transceivers (each sold separately) to the application, you can extend the signal to each connected display up to 400 feet (121.9 meters) or 460 feet (140.2 meters), respectively.

Transmits Crystal-Clear 4K Video with Multi-Channel Audio, HDR and 4:4:4 Color

The B127A-004-BH supports Ultra HD resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz with true uncompressed 7.1-channel digital audio and Dolby TrueHD. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This splitter also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Multi-Resolution Support Allows Mixing and Matching of Displays of Different Resolutions

Say you have a brand new 4K/60 Hz HDTV in one room, but want to also connect your Blu-ray player or satellite box to an older 1080p TV in another room. The B127A-004-BH is backward compatible with 4K/30 Hz and 1080p resolutions via automatic switching, allowing each connected monitor to display video at its maximum resolution.

Local HDMI Port on Transmitter Supports 4K @ 60 Hz Resolution

To monitor the video signal being extended to the receiver, connect a 4K display to the splitter's local HDMI port with a user-supplied HDMI cable. This port does not support multi-resolution capabilities, so the connected monitor must also support 4K/60 Hz to function properly.

Built-In PoC Technology Provides Receiver Power to Avoid Bulky External Power Bricks

Highlights

Requires connection to Tripp Lite B127A-Series remote receivers (sold separately) Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0 Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy Power over Cable (PoC) technology provides power to receivers via Cat6 cable Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Extend video signals from one room to another using Cat6 cable, which can pass through conduit to meet building codes
- Gain flexibility in where the receivers are placed, with the freedom to move and relocate them away from an AC outlet
- Improve the line of sight for digital signage in a hotel, restaurant, theater, house of worship, trade show or other location

System Requirements

- Source device with HDMI output (Blu-ray player, cable box, laptop)
- Display device(s) with HDMI input (HDTV, projector, monitor)
- Tripp Lite B127A-Series receivers, such as B127A-1A0-FH, B127A-2A0-FH, B127A-1P0-PH and/or B127A-1A0-BH

Package Includes

- B127A-004-BH 4-Port HDMI over Cat6 Splitter
- External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 24V 1A)
- (4) International plug adapters (North America, U.K., Europe, Australia)
- HDMI cable (M/M), 1 ft. (0.3 m)
- Mounting hardware
- Owner's manual



Power over Cable (PoC) technology powers the connected receivers over Cat6 cable. LEDs indicate when the system is receiving power and a signal is being transmitted. PoC lets you avoid the hassle of a bulky power brick and gives you the freedom to place the receivers where needed without worrying about finding a nearby AC outlet.

Plug-and-Play Operation for Quick Setup and Immediate Use

The splitter works right out of the package with no software required. Mounting hardware is included for installing it on a wall, pole or 19-inch rack. Connect the splitter to an HDMI source device with a user-supplied HDMI cable (such as Tripp Lite's P568- or P569-Series). Then, connect the splitter to Tripp Lite B127A-Series remote receivers with user-supplied Cat6 cable (such as Tripp Lite's N202-Series).

TAA-Compliant for GSA Schedule Purchases

The B127A-004-BH is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332263377
Technology	Cat6; HDMI; HDR; POC; Stereo Audio
VIDEO	
Video Input	HDMI (FEMALE)
Video Output	HDMI (FEMALE)
Video Ports	HDMI (FEMALE); (4) RJ45 (FEMALE)
Video Ports Details	HDMI 2.0; HDCP 2.2
Max Supported Video Resolution	3840 x 2160 @ 60 Hz
Max. Distance (Between any 2 Units)	230ft.
Max 720P Range (ft)	230
Max 1080P Range (ft)	230
Max 1280 x 720 (720p) Range (ft)	230
Max 1920 x 1080 (1080p) Range (ft)	230
Max 3840 x 2160 (4K) Range (ft)	230
Max 3840 x 2160 (4K@30Hz) Range (ft)	230
Max 3840 x 2160 (4K@60Hz) Range (ft)	230
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	4
Transmitter - Local Display Output	HDMI
Signal Range (ft)	230



Extended Mode	Yes
Extended Mode Details	x4 RJ45 Ports (4K/60 Hz)When using a laptop/Macbook only the first display will be extended. The remaining 3 displays will be mirrored.When using a DVR/DVD/Blu-Ray player all four displays will be mirrored.
Mirror Mode	Yes
Mirror Mode Details	x4 RJ45 Ports (4K/60 Hz)When using a laptop/Macbook only the first display will be extended. The remaining 3 displays will be mirrored.When using a DVR/DVD/Blu-Ray player all four displays will be mirrored.
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
Maximum Signal Range (ft)	230
Maximum Signal Range (m)	70
AUDIO	
Audio Specification	True uncompressed 7.1 Channel digital audio
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
Bus Powered	No
POWER	
Power Over Cable (PoC) Support	Yes
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
External Power Supply Output Specs (V / A)	24V / 1A
External Power Supply Cord Length (ft.)	4.53
External Power Supply Cord Length (m.)	1.38
External Power Supply Certifications	CCC; CE; FCC; GS; TUV; UL; cUL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Splitter Unit: x4 RJ45 Ports (x4 Green = Power, x4 Orange = Transmitting video to connected receiver), Power (x1 Green = Powered by external power supply), Input (x1 Orange = Connected to video source), Local (x1 Orange = Display connected to local HDMI port), UTP (x1 Orange = Receiver unit(s) connected and receiving data)
PHYSICAL	
Color	Black
Material of Construction	Metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Rackmountable	Yes
Shipping Dimensions (hwd / cm)	5.51 x 35.20 x 16.41
Shipping Dimensions (hwd / in.)	2.17 x 13.86 x 6.46
Shipping Weight (kg)	1.03
Shipping Weight (lbs.)	2.27
Unit Dimensions (hwd / cm)	2.97 x 23.5 x 10
Unit Dimensions (hwd / in.)	1.169 x 9.252 x 3.937
Unit Packaging Type	Box
Unit Weight (kg)	0.65
Unit Weight (lbs.)	1.43
ENVIRONMENTAL	
Operating Temperature Range	32 to 104F (0 to 40C)
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	0 to 85% RH, Non Condensing
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	230
Signal Range (ft.)	230
Signal Range (m)	70
Max 480P Range (ft)	230
Transmission Distance	230 ft.
Max 1440 x 900 Range (ft)	230
Max 1080i Range (ft)	230
Max 4K UHD Range (ft)	230
Max 480i Range (ft)	230
Max 800 x 600 Range (ft)	230
Max 1600 x 1200 Range (ft)	230
EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
Consumer Electronics Control (CEC) Supported	No
Latency	Zero Latency
CONNECTIONS	
Ports	4



Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(4) RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
HDCP Specification	1.4; 2.2
Driver Required	No
Recommended Category Cable	24AWG Solid Wire Cat6
10/100 Ethernet Extension Support	No
DIN Mountable	No
Integrated/Removable Cable	No
MST Support	Yes
Mounting Accessory Included	Yes
Multi-Resolution Support	Yes
Built-In Equalizer	Yes
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>