

PERFORMANCE

Processor

Intel® Celeron® N5100 (4C / 4T, 1.1 / 2.8GHz, 4MB L3)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

4GB Soldered LPDDR4x-2933

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

4GB soldered memory, not upgradable

Storage

32GB eMMC 5.1

Storage Support

32GB eMMC 5.1 on systemboard

Card Reader

MicroSD Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® 5682I-CGT codec

Speakers

Stereo speakers, 2W x2

Camera

720p with Privacy Shutter + World Facing 5.0MP

Microphone

Mono

Battery

Integrated 42Wh

Max Battery Life

Google power load test: 12.1 hr

Power Adapter

65W USB-C (2-pin)

DESIGN

Display

11.6" HD (1366x768) IPS 250nits Glossy 50% NTSC, Glass, Touch

Touchscreen

10-point Multi-touch

Keyboard

Non-backlit, French / English

Case Color

Grey

Surface Treatment

Texture

Case Material

PC + ABS with Rubber Bumper (Top), PC + ABS (Bottom)

Pen

Lenovo® USI Pen (Garaged)

Dimensions (WxDxH)

289.6 x 202.4 x 19.9 mm (11.4 x 7.97 x 0.78 inches)

Weight

Starting at 1.33 kg (2.93 lbs)

Others

Buttons: power key, volume key

SOFTWARE

Operating System

Chrome OS

Bundled Software

None

CONNECTIVITY

Ethernet

None

WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.0

WWAN

None

SIM Card

None

Standard Ports

- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader
- 2x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)

SECURITY & PRIVACY

Security Chip

Google Security Chip H1

Fingerprint Reader

None

Physical Locks

Kensington® Nano Security Slot

Other Security

Camera privacy shutter

SERVICE

Base Warranty

1-year, Mail-in

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Silver
- ErP Lot 3
- RoHS compliant
- TCO Certified 8.0

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes

Announce Date : 2021-05-28

EAN / UPC / JAN : 195713975865

End of Support : N/A



intel

· Product image on this page is a sample, it may not match the real color of this model

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.



Lenovo Powered USB-C Travel Hub

4X90S92381

Travel-Ready Productivity Powerhouse; One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo Powered USB-C Travel Hub fits unlimited...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference