

**PERFORMANCE****Processor**

Intel® Core™ i7-1165G7 (4C / 8T, 2.8 / 4.7GHz, 12MB)

**Graphics**

NVIDIA® Quadro® T500 4GB GDDR6

**Chipset**

Intel SoC Platform

**Memory**

8GB Soldered DDR4-3200 non-ECC

**Memory Slots**

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

**Max Memory**

Up to 40GB (8GB soldered + 32GB SO-DIMM) DDR4-3200

**Storage**

256GB SSD M.2 2280 PCIe x4 NVMe Opal2

**Storage Support**

One drive, up to 2TB M.2 2280 SSD

**Card Reader**

MicroSD Card Reader

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2, Dolby® Audio™

**Camera**

720p with Privacy Shutter

**Microphone**

2x, Array

**Battery**

Integrated 50Wh

**Max Battery Life**

MobileMark® 2018: 9.7 hr

JEITA 2.0: 16 hr

**Power Adapter**

65W USB-C Slim (2-pin)

**DESIGN****Display**

14" FHD (1920x1080) IPS 300nits Anti-glare

**Touchscreen**

None

**Color Calibrator**

None

**Keyboard**

Backlit, English

**Case Color**

Black

**Case Material**

PC + ABS (Top), PC + ABS / Talc15 + Magnesium Alloy (Keyboard Cover), PA / 50% GF (Bottom)

**Dimensions (WxDxH)**

329 x 227 x 17.9 mm (12.95 x 8.94 x 0.70 inches)

**Weight**

1.469 kg (3.24 lbs)

**SOFTWARE****Operating System**

Windows® 10 Pro 64, English

**Bundled Software**

None

**CONNECTIVITY****Ethernet**

100/1000M

**WLAN + Bluetooth®**

Intel AX201 11ax, 2x2 + BT5.2

**WWAN**

WWAN Upgradable to 4G

**SIM Card**

None

**NFC**

None

**Standard Ports**

- 1x Side docking connector
- 1x Ethernet (RJ-45)
- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader
- 1x HDMI® 2.0
- 2x Thunderbolt™ 4 / USB4™ 40Gbps / USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)

**Optional Ports (configured)**

- 1x Nano-SIM card slot (WWAN model)
- 1x Smart card reader

**Monitor Cable**

None

**SECURITY & PRIVACY****Smart Card Reader**

None

**Security Chip**

Discrete TPM 2.0

**Fingerprint Reader**

Touch Style, Match-on-Chip

**Physical Locks**

Kensington® Security Slot

**Other Security**

Camera privacy shutter

**MANAGEABILITY****System Management**

None

**SERVICE****Base Warranty**

3-year, Depot

**Included Upgrade**

3Y Premier Support Upgrade from 3Y Courier/Carry-in (5WSOV07092)

**ACCESSORIES****Bundled Accessories**

None

**CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 8.0
- EPEAT™ Gold
- TCO Certified Notebooks 8
- RoHS compliant

**Mil-Spec Test**

MIL-STD-810H military test passed

**ISV Certifications**Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)**MODEL**

TopSeller : Yes

Announce Date : 2021-08-10

EAN / UPC / JAN : 196118532080

End of Support : 2027-09-23

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Technical Account Managers for proactive relationship and escalation management



Priority on service delivery and repair parts



Lenovo Service Connect Portal for customized reporting and product support

## Recommended Accessories

### ThinkPad 14-inch Professional Slim Topload

4X40W19826

The ThinkPad 14-inch Professional Slim Topload is a sleek, thin-and-light case for the minimalist professional. This compact design carries, protects and organizes your laptop and everyday work essentials, while prem...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + ADP + KYD + 3Y SBTY + International Upg) (5PS1D67024)
BETTER	3Y Lenovo Protect (ADP + KYD + SBTY + International Upg) (5PS1D67023)
GOOD	3Y Lenovo Support (KYD + SBTY + International Upg) (5PS1D67026)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference