



# Chill-Its® 6015

## HEAVY-DUTY POP-UP TENT – 10FT X 20FT / 3M X 6M



The SHAX® 6015 Heavy-Duty Pop-Up Tent is a durable portable shelter providing fast, long-lasting relief from the sun, wind and rain with a big 10ft x 20ft / 3m x 6m footprint.

### Features

- 200 square feet of shaded area
- Powder-coated steel frame built to withstand tough conditions
- Rugged 300D polyester canopy with PU coating and UV treatments; double-vented top for maximum air flow
- Reinforced corners on the canopy to withstand harsh conditions
- Easy to adjust ABS plastic sliders on legs; 3 height settings from 10ft - 14ft / 3m - 4m

### Application

- Construction
- Trades
- Landscaping/Grounds
- Utility Crews
- Survey Crews
- And more

ITEM #	SIZE	COLOR	DESCRIPTION
12915	10' x 20'	Hi-vis Lime	Heavy-Duty Tent
12995	—	Hi-vis Lime	Optional Side Panel
12916	10' x 20'	Hi-vis Lime	Replacement Canopy
12917	—	Black	Replacement Bag
12915-Pallet		Hi-vis Lime	Heavy-Duty Tent-Pallet Qty.

Order in Multiples of: 1

### UPGRADE YOUR SHADE: SHAX® MISTING SYSTEM



Cool the area under your canopy by up to 30°F (14°C) below ambient air temperature with a super fine mist.

### ALSO AVAILABLE: SHAX® 6097 POP-UP TENT SIDEWALLS



The SHAX® 6097 Pop-Up Tent Sidewalls let you add privacy and protection from the sun, wind and rain. Sold individually. Compliments the 20ft side of the SHAX® 6015 Pop-Up Tent.

**GET FULL PRODUCT INFO, IMAGES, VIDEOS AND MORE AT [ERGODYNE.COM](http://ERGODYNE.COM)**