### **CyberPower**

# SM040KAMFA | SMART APP ONLINE 3-PHASE MODULAR UPS SYSTEM

## Safeguard mission-critical applications with seamless, double-conversion power protection

The CyberPower SM040KAMFA Smart App Online 3-Phase Modular UPS System brings flexibility, space savings, and efficiency to 3-Phase power protection technology. Configurable for N+N system or N+1 power module redundancy, the system can intelligently manage individual modules to achieve higher efficiency. The customizable modular design can be configured as a tower, side-by-side, or integrated within a rack. The high-density, scalable 10kVA/10kW power modules are 2U in height, saving space while providing more options for capacity expansion.

The SMO40KAMFA features double-conversion topology for seamless power protection and a pre-installed RMCARD205 for remote management. The user-friendly 7" color touchscreen displays key status indicators at-a-glance. Three-stage Smart Battery Management (SBM) equalizes battery voltages and reduces excessive heat to extend battery life. Plus, hot-swappable power modules, battery and, bypass allow for rapid replacement and



minimal impact to system operation. Ideal for high-end data centers, the SMO40KAMFA 3-Phase Modular UPS System assures reliable, high-quality AC power and includes a One-Year Limited Warranty.

#### **SPECIFICATIONS**

GENERAL	
Dual Power Inputs	Yes
Energy Saving	Online ECO Mode Efficiency >97.5%
Hot Swappable Bypass Module	Yes
Hot Swappable Power Module	Yes
Power Module Capacity	5
Parallel Expansion	Yes
Power Module Redundancy Capability	Yes
UPS Topology	Online Double Conversion

BATTERY	
Battery Bus Voltage	Nominal: ±120 VDC, one-side range: 120 VDC - 132 VDC
Battery Cabinet	Modular External Cabinet
Charger Voltage Tolerance	≤1% Float
Extended Battery Cabinet	BCT6L9N225
Hot Swappable Battery Module	Yes
Recharge Power	Default 10% x UPS Power
Recharge Power (Selectable)	1% - 20 %
Ripple Current	≤5% C10
Ripple Voltage	≤1% VDC Float
Temperature Compensation (Per Cell)	-3 mV/°C

## SM040KAMFA SMART APP ONLINE 3-PHASE MODULAR UPS SYSTEM

### **SPECIFICATIONS CONT.**

INPUT	
Backfeed Protection	Yes
Bypass Input Voltage Range	-20% - +15%
Bypass Input Voltage Range (Selectable)	Lower limit: -10%, -20%, -30%, -40% Higher limit: +10%, +15%, +20%, +25%
	110% - 130% Load for 5 min 130% - 150% Load for 1 min >150% Load for 300 ms
Bypass Rated Current	111 A@ 208 V
Bypass Frequency Tolerance (Default)	±10%
Bypass Frequency Tolerance (Selectable)	±2.5%, ±5%, ±10%, ±20%
Bypass to Inverter Switch Time	Synchronized switch: ≤1 ms
Current rating of bypass neutral cable (A)	1.7 x Input Rated Current
Input Connector	Hardwire (L1, L2, L3, N, G)
Input Frequency Range	40 Hz - 70 Hz
Input Power Factor	0.99
Input Voltage	208/120 V 220/127 V
Input Voltage Range	-40% - +25% or 124.8 VAC - 260 VAC
Phase	3-Phase
Synchronization Window	Rated frequency: ± 2 Hz
Synchronization Window (Selectable)	±0.5 Hz - ±5 Hz
THDI (%)	<4% (Full Linear Load)
OUTPUT	
	±1 (Balanced Load) ±1.5 (100% Unbalanced Load)
	Internal Bypass (Automatic and Manual)
Crest Factor	3:1
FILICIENCY	92.5% (Battery Mode) 93% (Normal Mode)
Harmonic Distortion	< 1.5% at Linear Load < 6% at Non-Linear Load
Built-in Maintenance Bypass	Yes

OUTPUT CONT.	
Max Change Rate of Synch Frequency	1 Hz/s
Max Change Rate of Synch Frequency (Selectable)	0.1 - 5 Hz/s
Maximum Capacity (VA)	40,000 VA
Maximum Watts Capacity	40,000 W
Neutral Current Capability	170 %
Non-Linear Load Capability	100 %
Outlet Type	1 - Hardwire Terminal Block
Output Connector	Hardwire (L1, L2, L3, N, G)
Output Frequency	50 Hz / 60 Hz (auto-sensing/configurable)
Output Power Factor	1
Output Voltage	208/120 V 220/127 V
Output Voltage Range	±5% VAC
Overload Protection	110% Load, 10 min 125% Load, 1 min 150% Load, 30 sec >150% Load, 200 ms
Short Circuit Protection	300% - 200 ms
Synchronization Window (Rated)	±2 Hz
Synchronization Window (Selectable)	±1 - ±5 Hz
Transient Voltage Response	±5%
Typical Transfer Time	0 ms
VA	40,000 VA
Watts	40,000 W

## SM040KAMFA SMART APP ONLINE 3-PHASE MODULAR UPS SYSTEM

### **SPECIFICATIONS CONT.**

MANAGEMENT AND COMMUNICATIONS		
Dry Contacts	Yes	
Emergency Power Off (EPO) Port	Yes	
LCD	Multifunction LCD, Touch Screen, Color	
LED Status Indicators	Rectifier, Battery, Bypass, Inverter, Output	
SNMP / HTTP Remote Monitoring	Yes - RMCARD205 pre-installed	
Communication Port/Protocols	1 x RS-232 DB9 Serial 1 x RS-485 Modbus (2-wire Twisted Pair)	
Software (Free Download)	PowerPanel® Business	
PHYSICAL		
Color	Black	
Form Factor	Modular	
Material of Construction	Metal	
Mounting Hardware	Yes	
Rack Height	19U	
PHYSICAL DIMENSIONS		
Physical Dimensions - WxHxD (cm)	48.51 x 94.23 x 77.47 cm	
Physical Dimensions - WxHxD (in.)	19.1 x 37.1 x 30.5 in.	
Weight (kg)	80.6 kg	
Weight (lb)	177.7 lbs.	
SHIPPING DIMENSIONS		
Shipping Dimensions - WxHxD (cm)	63.2 x 112.4 x 98.81 cm	
Shipping Dimensions - WxHxD (in)	24.88 x 44.25 x 38.9 in.	
Weight (kg)	121.97 kg	
Weight (lb)	268.9 lbs.	

POWER MODULE DIMENSIONS		
Individual Power Module - Rack Units	2U	
Individual Battery Module - Rack Units	3U	
ENVIRONMENTAL		
Audible noise at 1m from surface of unit	56 dBA	
Ingress Protection	IP20	
Maximum Air Exchange	3.02 m3/min	
Online Thermal Dissipation	11,430.2 BTU/hr	
Operating Elevation	0 - 10,000 ft (0 - 3,048 m)	
Operating Elevation Note	At ≤1,000m above sea level, de-rate power by 1% per 100m between 1,000m and 3,048m	
Operating Relative Humidity	0 - 95 % (non-condensing)	
Operating Temperature	32 - 104°F (0 - 40°C)	
Operating Temperature Note	Battery life is halved for every 50°F (10°C) increase above 68°F (20°C)	
Storage Battery Temperature Note	Optimum battery storage between 5 - 68°F (-15 - 20°C)	
Storage Relative Humidity	0 - 95% (non-condensing)	
Storage Temperature	-4 - 158°F (-20 - 70°C)	
CERTIFICATIONS		
Environmental	RoHS Compliant	
Safety	cTUVus UL1778, CSA C22.2, No. 107.3-14 CFR 47 FCC Part 15, Subpart B, Class A IEC62040-2	
WARRANTY		
Product Warranty	One-Year Limited Warranty	